# HIGH FREQUENCY FLAT COIL PLANAR TRANSFORMERS

Pulse Electronics

PH08XXCNL Series (up to 160W)





*Power Rating:* up to 160 W

Height: 9.1mm to 10.1mm Max


Footprint: 24.7mm x 21.6mm Max
Frequency Range: 200kHz to 700kHz


Isolation (Primary to Secondary): 1500 VDC


Patented: US Pat 9378885

Electrical Specifications @ 25°C – Operating Temperature –40°C to +125°C										
	Turns				Primary <sup>1</sup>	Leakage <sup>2</sup>	$ m DCR~(m\Omega~MAX)$			Maximum
Part³ Number	Primary A	Primary B	Secondary	Schematic	Inductance (µ MIN)	Inductance (μ MAX)	Primary A	Primary B	Secondary	<b>Height</b> (mm)
PH0801CNL	4T	4T	4T (1T:1T:1T:1T)	Al	153	0.45	8.5	8.5	7	9.1
PH0802CNL	4T	5T			194	0.45	8.5	12.5		
PH0803CNL	5T	5T			240	0.55	12.5	12.5		
PH0804CNL	5T	6T			290	0.60	12.5	14.2		9.6
PH0805CNL	6T	6T			345	0.65	14.2	14.2		
PH0806CNL	4T	4T	17 & 17	A2	153	0.45	8.5	8.5	1.0 & 1.0	9.1
PH0807CNL	4T	5T			194	0.55	8.5	12.5		
PH0808CNL	5T	5T			240	0.55	12.5	12.5		
PH0809CNL	5T	6T			290	0.90	12.5	14.2		9.6
PH0810CNL	6T	6T			345	1.00	14.2	14.2		
PH0811CNL	4T	4T	2T & 1T	A3	153	0.45	8.5	8.5	1.75 & 1.75	9.1
PH0812CNL	4T	5T			194	0.45	8.5	12.5		
PH0813CNL	5T	5T			240	0.55	12.5	12.5		9.6
PH0814CNL	5T	6T			290	0.65	12.5	14.2		
PH0815CNL	6T	6T			345	0.85	14.2	14.2		10.1

### **Mechanicals**







Weight	11.8 grams
Tape & Reel	180/reel
Tray	40/tray
Dimensions: Inches	5
mm	-

Unless otherwise specified,

all tolerances are  $\pm \frac{.010}{0.25}$ 


### HIGH FREQUENCY FLAT COIL PLANAR TRANSFORMERS

PH08XXCNL Series (up to 160W)



### **Schematics**

### PH08XXCNL




#### **Notes:**

- 1. Inductance is measured with both primary windings connected in services (2 to 5, with 3 and 4 shorted).
- 2. Leakage inductance is measured on winding (2-5) with (3-4) and (7, 8, 9, 10, 11) shorted.
- 3. The "NL" suffix indicates an RoHS-compliant part number.
- 4. It is possible to add a primary side aux.winding to any of the above configurations as shown in the schematics. Transformers with primary side aux. winding are non-standard and can be made available upon request. The primary aux. winding can be between 2 and 16 turns. To add a primary aux. winding to a given base, use the

extension .xxx. For example, to add a 4T aux. winding to the base part number PH0801CNL, use the part number PH0801.004CNL. The height increases to 10.1mm MAX for PH0810.xxxCNL. For the other part numbers there is no change to the height.. 5. Optional Tape & Reel packaging can be ordered by adding a "T" suffix to the complete number (i.e. **PH0801.009CNL** becomes **PH00801.009CNLT**).

6. To determine if the transformer is suitable for your application, it is necessary to ensure that the temperature rise of the component (ambient plus temperature rise) not exceed its operating temperature. To determine the approximate temperature rise of the transformer, refer to the graphs below.




## HIGH FREQUENCY FLAT COIL PLANAR TRANSFORMERS

PH08XXCNL Series (up to 160W)



### **Temperature Rise vs. Power (W) Dissipation**



For More Information								
Pulse Worldwide Headquarters 15255 Innovation Drive Ste 100 San Diego, CA 92128 U.S.A.	Pulse Europe Pulse Electronics GmbH Am Rottland 12 58540 Meinerzhagen Germany	Pulse China Headquarters Pulse Electronics (ShenZhen) CO., LTD D708, Shenzhen Academy of Aerospace Technology, The 10th Keji South Road, Nanshan District, Shenzhen, P.R. China 518057	Pulse North China Room 2704/2705 Super Ocean Finance Ctr. 2067 Yan An Road West Shanghai 200336 China	Pulse South Asia 3 Fraser Street 0428 DUO Tower Singapore 189352	Pulse North Asia 1F., No.111 Xiyuan Rd Zhongli City Taoyuan City 32057 Taiwan (R.O.C)			
Tel: 858 674 8100 Fax: 858 674 8262	Tel: 49 2354 777 100 Fax: 49 2354 777 168	Tel: 86 755 33966678 Fax: 86 755 33966700	Tel: 86 21 62787060 Fax: 86 2162786973	Tel: 65 6287 8998 Fax: 65 6280 0080	Tel: 886 3 4356768 Fax: 886 3 4356820			

Performance warranty of products offered on this data sheet is limited to the parameters specified. Data is subject to change without notice. Other brand and product names mentioned herein may be trademarks or registered trademarks of their respective owners. © Copyright, 2018. Pulse Electronics, Inc. All rights reserved.