CMR1-02M CMR1-06M CMR1-04M CMR1-10M

SURFACE MOUNT SILICON GENERAL PURPOSE RECTIFIERS 1.0 AMP, 200 THRU 1000 VOLT



Central Semiconductor

www.centralsemi.com

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CMR1-02M series 1.0 Amp surface mount silicon rectifier is a well constructed, highly reliable component designed for use in all types of commercial, industrial, entertainment, computer, and automotive applications where small size is required. The SMA case occupies 30% less board space than the SMB case.

MARKING CODE: SEE MARKING CODE TABLE ON FOLLOWING PAGE

FEATURES:

- · High reliability
- · Glass passivated chip
- · Special selections available

MAXIMUM RATINGS: (T_A=25°C unless otherwise noted)

	SYMBOL	CMR1-02M	CMR1-04M	<u>CMR1-06M</u>	CMR1-10M	UNITS
Peak Repetitive Reverse Voltage	V _{RRM}	200	400	600	1000	V
DC Blocking Voltage	VR	200	400	600	1000	V
RMS Reverse Voltage	V _{R(RMS)}	140	280	420	700	V
Average Forward Current (TL=100°C)	I _O		1	.0		А
Peak Forward Surge Current, tp=8.3ms	IFSM		÷	30		А
Operating and Storage Junction Temperature	T _J , T _{stg}		-65 t	o +150		°C
Thermal Resistance	Θ _{JL}		:	30		°C/W


ELECTRICAL CHARACTERISTICS: (T_A=25°C unless otherwise noted)

SYMBOL	TEST CONDITIONS	ТҮР	MAX	UNITS
I _R	V _R =Rated V _{RRM}		5.0	μΑ
I _R	V _R =Rated V _{RRM} , T _A =125°C		50	μA
VF	I _F =1.0A		1.1	V
СJ	V _R =4.0V, f=1.0MHz	8.0		pF

CMR1-02M CMR1-06M CMR1-04M CMR1-10M



SURFACE MOUNT SILICON GENERAL PURPOSE RECTIFIERS 1.0 AMP, 200 THRU 1000 VOLT



SMA CASE - MECHANICAL OUTLINE

DEVICE	MARKING CODE		
CMR1-02M	C02M		
CMR1-04M	C04M		
CMR1-06M	C06M		
CMR1-10M	C10M		

DIMENSIONS					
	INCHES		MILLIMETERS		
SYMBOL	MIN	MAX	MIN	MAX	
А	0.030	0.060	0.76	1.52	
В	0.002	0.008	0.05	0.20	
С	0.006	0.012	0.15	0.30	
D	0.078	0.103	1.98	2.62	
E	0.188	0.220	4.78	5.59	
F	0.090	0.115	2.29	2.92	
G	0.050	0.070	1.27	1.78	
Н	0.157	0.181	3.99	4.60	

SMA (REV:R3)

R6 (02-June 2023)

OUTSTANDING SUPPORT AND SUPERIOR SERVICES

PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- · Consolidated shipping options

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities

ss your design challenges.

· Custom product packing

- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- · Application and design sample kits

Custom bar coding for shipments

Custom product and package development

REQUESTING PRODUCT PLATING

- 1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
- If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp. 145 Adams Avenue Hauppauge, NY 11788 USA Main Tel: (631) 435-1110 Main Fax: (631) 435-1824 Support Team Fax: (631) 435-3388 www.centralsemi.com

Worldwide Field Representatives: www.centralsemi.com/wwreps

Worldwide Distributors: www.centralsemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: <u>www.centralsemi.com/terms</u>

