2A, 400V ESD Capability Rectifier

FEATURES

- High ESD capability
- Glass passivated chip junction
- Ideal for automated placement
- Low forward voltage drop
- High surge current capability
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters ٠
- Lighting application
- Converter

MECHANICAL DATA

- Case: DO-214AA (SMB)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.090g (approximately)

KEY PARAMETERS			
PARAMETER	VALUE	UNIT	
I _F	2	А	
V _{RRM}	400	V	
I _{FSM}	50	А	
T _{J MAX}	175	°C	
Package	DO-214AA (SMB)		
Configuration	Single die		





DO-214AA (SMB)



SOLUTE MAXIMUM RATINGS ($T_A = 25^{\circ}C$ unless otherwise noted)			
PARAMETER	SYMBOL	TSD2G	UNIT
Marking code on the device		TSD2G	
Repetitive peak reverse voltage	V _{RRM}	400	V
Reverse voltage, total rms value	V _{R(RMS)}	280	V
Forward current	I _F	2	А
Surge peak forward current, 8.3ms single half sine-wave superimposed on rated load	I _{FSM}	50	A
Junction temperature	TJ	- 55 to +175	°C
Storage temperature	T _{STG}	- 55 to +175	°C







THERMAL PERFORMANCE			
PARAMETER	SYMBOL	ТҮР	UNIT
Junction-to-lead thermal resistance	R _{ƏJL}	26	°C/W
Junction-to-ambient thermal resistance	R _{ØJA}	73	°C/W
Junction-to-case thermal resistance	R _{ejc}	27	°C/W

Thermal Performance Note: Units mounted on PCB (10mm x 10mm Cu pad test board)

ELECTRICAL SPECIFICATIONS ($T_A = 25^{\circ}C$ unless otherwise noted)					
PARAMETER	CONDITIONS	SYMBOL	ТҮР	MAX	UNIT
Forward voltage ⁽¹⁾	$I_F = 1A, T_J = 25^{\circ}C$		0.87	0.95	V
	$I_F = 2A, T_J = 25^{\circ}C$	V _F	0.90	1.00	V
	$I_F = 1A, T_J = 125^{\circ}C$		0.80	0.90	V
	$I_F = 2A, T_J = 125^{\circ}C$		0.75	0.85	V
Reverse current @ rated $V_R^{(2)}$	$T_J = 25^{\circ}C$	I _R	-	1	μA
	T _J = 125°C		-	50	μA
Junction capacitance	$1MHz, V_{R} = 4.0V$	CJ	20	-	pF

Notes:

1. Pulse test with PW = 0.3ms

2. Pulse test with PW = 30ms

IMMUNITY TO ELECTRICAL STATIC DISCHARGE TO THE FOLLOWING

STANDARDS ($T_A = 25^{\circ}C$ unless otherwise noted)

STANDARD	TEST TYPE	TEST CONDITION	SYMBOL	CLASS	VALUE	TYPICAL
AEC-Q101-001	Human body model(contact mode)	C=100pF,R=1.5kΩ		НЗВ	≥8kV	N/A
	Contact mode	C=150pF,R=330Ω		4	≥8kV	25kV
IEC 61000-4-2	Air-discharge mode	C=150pF,R=330Ω	Vc	4	≥15kV	30kV
100 40005	Contact mode	C=330pF,R=330Ω]	L4	≥15kV	25kV
ISO 10605	Air-discharge mode	C=330pF,R=330Ω		L4	≥25kV	30kV

ORDERING INFORMATION		
ORDERING CODE	PACKAGE	PACKING
TSD2G	DO-214AA (SMB)	3,000 / Tape & Reel



CHARACTERISTICS CURVES

 $(T_A = 25^{\circ}C \text{ unless otherwise noted})$





Fig.1 Forward Current Derating Curve

Fig.2 Typical Junction Capacitance

Fig.3 Typical Reverse Characteristics


Fig.4 Typical Forward Characteristics






TSD2G Taiwan Semiconductor


PACKAGE OUTLINE DIMENSIONS





DIM.	Unit (mm)		Unit (nit (inch)	
	Min.	Max.	Min.	Max.	
A	1.95	2.65	0.077	0.104	
A1	0.05	0.20	0.002	0.008	
b	1.95	2.20	0.077	0.087	
с	0.15	0.31	0.006	0.012	
D	3.30	3.95	0.130	0.156	
E	5.10	5.60	0.201	0.220	
E1	4.05	4.60	0.159	0.181	
L	0.75	1.60	0.030	0.063	

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	2.30	0.091
В	2.50	0.098
С	4.30	0.169
D	1.80	0.071
E	6.80	0.268

MARKING DIAGRAM



P/N	= Marking Code
-----	----------------

G = Green Compound

YW = Date Code

F = Factory Code



Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.