



电气指标:

1. 频率范围: DC~6GHz
2. 接触电阻
 内导体: $\leq 3 \text{ m}\Omega$
 外导体: $\leq 2 \text{ m}\Omega$
3. 绝缘电阻: $\geq 5000 \text{ M}\Omega$
4. 介质耐压: 1000V(rms)
5. 使用寿命: 500次

执行标准: GB681 (MIL-C-39012)

材料&镀层

1. 中心接触件: 黄铜, 镀金
2. 外壳: 黄铜, 镀金
3. 绝缘子: PTFE

Electrical Characteristics:

1. Frequency range: DC~6GHz
2. Contact resistance
 Center conductor: $\leq 3 \text{ m}\Omega$
 Out conductor: $\leq 2 \text{ m}\Omega$
3. Insulation resistance: $\geq 5000 \text{ M}\Omega$
4. Insulator withstanding: 1000V(rms)
5. Durability: 500cycles

Application: GB681 (MIL-C-39012)

Material&Finishing

1. Center pin: **Brass, gold plated**
2. Body :brass, gold plated
3. Insulators:PTFE

Tel : Lee +86-28-85589664

Web: www.hltchips.com

FIRST ANGLE PROJECTION		SCALE	SMA-JJA	UNITS	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE mm, TOLERANCES ARE: FRACTIONS DECIMALS ANGLES
THIRD ANGLE PROJECTION		2:1		mm	
	NAME	DATE	SMA male to male adaptor	REV	
DRAWN	H.wei	08-01-12		V1.0	.X± .20 ± 1° .XX± .10 .XXX±
CHECKED	L.yu	08-01-12			
APPROVED	W.yi	08-01-12			