


This document contains proprietary information and such information may not be disclosed to others for any purposes, not used for sales/marketing/procurement purposes without written permission

REV	DESCRIPTION OF REVISION	ECN NO.	BY	DATE	APPROVED
A	Initial Release	—	H.wei	01/09/15	01/09/15

1. Electrical
  - 1.1 Impedance: 50ohm
  - 1.2 Frequency: DC-6GHz
  - 1.3. Insulation resistance:  $\geq 5000M\Omega$
  - 1.4 Dielectric withstanding voltage: 500V(rms)
  - 1.5 VSWR: 1.20:1

2 Material&Finish

- 2.1 Inner Contact: Brass, gold plated
- 2.2 Outer Contact: Bronze, gold plated
- 2.3 Insulators: PTFE



Tel:Lee +86-28-85589664  
Web:www.hltchips.com

Notes:

1. ALL SPECIFICATIONS ARE SUBJECT TO CHANGE NOTICE AT ANY TIME
2. CUSTOMER OUTLINE DRAWING FOR REFERENCE ONLY

DRAWN:	H.wei 01/09/15
ENGINEER:	L.yu 01/09/15
APPROVED:	W.yi 01/09/15
TOLERANCES UNLESS OTHERWISE SPECIFIED	
X	$\pm 0.50$
.X	$\pm 0.20$
.XX	$\pm 0.10$
ANGLES	$\pm 1^\circ$

TITLE:  
RF Adaptor  
SMA Male to Female Adaptor



DIMENSION IN MILLIMETERS (mm)

PART NO:	HL-SMA-JKB	SIZE:	A4	SCALE:	N/A	SHEET:	1/1	REV:	A
----------	------------	-------	----	--------	-----	--------	-----	------	---