


Thin Film Pyroelectric Flame Sensor

Introduction

Broadcom® thin film pyroelectric infrared flame detectors offer exceptionally high responsivity, a wide field of view of typically 100° (*subject to filter band pass specification) and class leading rapid recovery from thermal and electrical shocks (typically <1 second downtime). This current mode sensor has excellent signal to noise at the signature 8-10 Hz flicker range of a flame, and can provide accurate discrimination of flame sources in triple IR flame detection systems. The sensor element is built into a low noise circuit that has an internal CMOS op amp with a $10G\Omega$ feedback resistor outputting a voltage signal centred around half the supply rail.





Sensor Characteristics				
Filter aperture	5.2 mm x 4.2 mm			
Element size	1000 μm x 1000 μm			
Package	TO39			
Responsivity 1	150,000 V/W			
D* 1	3.5 x 10 ⁸ cm√Hz/ W			
Noise ¹	Mean 70 μV√Hz			
Field of View	Typical 100° ²			


¹10 Hz, 500 K, room temperature, without window and optics

Electrical Character	ristics			
Max. Voltage (+V) ³	8.0 V			
Min. Voltage (+V)	2.7 V			
Output voltage normalised around mid-rail				
Microphonics	S _{vib} ~2 μV/νHz at 10 Hz			
Time Constant	~12 ms			
Operating Temperature	-40 to +85 °C			
Storage Temperature	-40 to +110 °C			
Op-Amp with 10 GΩ feedback resistor				
Filter	As per Filters Available table			

Frequency Characteristics










Note: Normalised polar plots show max FoV achievable along x,y axis and diagonal without any filter applied.

²With reference to filter used in AFBR-S6PY0573

³ Absolute maximum operating voltage



Package Information



Note: Ensure that the sensor base is not in contact with the PCB in order to avoid shorts.

Filters Available

Part number	AFBR-	AFBR-	AFBR-	AFBR-	AFBR-	AFBR-
	S6PY3200	S6PY0575	S6PY0573	S6PY0574	S6PY2341	S6PY1601
Filter name	2.77 µm	3.91 µm	4.35 µm	4.55 µm	4.64 µm	5.0 µm
	bandpass	bandpass	bandpass	bandpass	bandpass	cut on
Cut on wavelength typical (µm)	2.425	3.865	4.05	4.34	4.55	5.0
Cut off wavelength typical (µm)	3.115	3.955	4.65	4.76	4.73	_

Note: An additional window is required to provide high wavelength blocking (above 8.0 μ m) and thermal shielding. Search terms: current mode, voltage mode, infrared detector, infrared sensor, MIR, mid-IR, thermopile, photodiode

Copyright © 2022 Broadcom. All Rights Reserved. The term "Broadcom" refers to Broadcom Inc. and/or its subsidiaries. For more information, go to www.broadcom.com . All trademarks, trade names service marks, and logos referenced herein belong to their respective companies.
Broadcom reserves the right to make changes without further notice to any products or data herein to improve reliability, function, or design. Information furnished by Broadcom is believed to be accurate and reliable. However, Broadcom does not assume any liability arising out of the application or use of this information, nor the application or use of any product or circuit described herein, neither does it convey any license under its patent rights nor the rights of others. AFBR-S6ATO1FL-DS100