

6

5

4

3






2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	01/17/07	
A		REVISED COLOR	6/21/10	
B		REDRAWN	05/25/12	



RECOMMENDED PCB LAYOUT

SPECIFICATIONS:
Material:
 Insulator: Nylon 66, rated UL 94V-0
 Insulator color: Natural
 Contacts: Brass
Plating:
 Tin over Nickel underplate overall
Electrical:
 Operating voltage: 125 VAC max
 Current rating: 1 Amps max
 Contact resistance: 20 mohms max
 Insulation resistance: 100 Mohms min
 Dielectric withstanding voltage: 250 VAC for 1 minute
Temperature Rating:
 Operating temperature: -40°C to +85°C
 Environmental:
 Lead free, RoHS compliant.

Positions: 02 thru 15
 A = .049 [1.25] x No. of Spaces
 B = .049 [1.25] x No. of Spaces + .070 [1.80]
 C = .049 [1.25] x No. of Spaces + .118 [3.00]

ADAM TECH

909 Rahway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: MX 1.25mm WAFER DIP 180°

UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED
 INCHES HOLEES
 .X ± .10 ØXX ± .10
 .XX ± .020 ØXXX ± .015
 .XXX ± .015 ØXXXX ± .010

APPROVALS	DATE
DRAWN	BW
CHECKED	
APPROVED	

SIZE	PART NO.	125SH-B-XX-TS	REV.
X			B
REF:	S00124T	SCALE: NTS	SHEET 1 OF 1



A

B

C

D

A

B

C

D

6

5

4

3

2

1