


CTCMD4D06F Series

From 2.2 μ H to 47 μ H



SPECIFICATIONS

Parts are available in $\pm 20\%$ inductance tolerance only.
 *Rated Current: Inductance drop = 10% typ.

Part Number	Inductance (μ H $\pm 20\%$)	L Test Freq. (kHz)	DCR Max. (Ω)	*Rated Current Max. (A)
CTCMD4D06F-2R2M	2.2	100	0.116	0.95
CTCMD4D06F-3R3M	3.3	100	0.174	0.77
CTCMD4D06F-4R7M	4.7	100	0.216	0.75
CTCMD4D06F-6R8M	6.8	100	0.296	0.62
CTCMD4D06F-100M	10	100	0.457	0.5
CTCMD4D06F-150M	15	100	0.676	0.4
CTCMD4D06F-220M	22	100	1.066	0.3
CTCMD4D06F-330M	33	100	1.647	0.24
CTCMD4D06F-470M	47	100	2.843	0.18

PHYSICAL DIMENSIONS

Size	A Max.	B Max.	C Max.	D	E	F	G	H
mm	6.3	5.8	0.8	3.5	4.1	3.2	0.5	0.4
inches	0.248	0.228	0.031	0.138	0.161	0.126	0.020	0.016

CHARACTERISTICS

- Description:** SMD power inductor
- Applications:** Power supplies for VTR, OA equipment, LCD televisions, PC notebooks, portable communication equipment, DC/DC converters, etc.
- Operating Temperature:** -25°C to +85°C
- Inductance Tolerance:** $\pm 20\%$
- Testing:** Tested on a HP4285A at 100kHz, 1V
- Packaging:** Tape & Reel
- Marking:** Parts are marked with inductance code
- Miscellaneous:** RoHS Compliant
- Additional Information:** Additional electrical & physical information available upon request
- Samples available. See website for ordering information.**

PAD LAYOUT

