







APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/19/07	
A		REDRAWN	11/18/13	KW/TW
B		REDRAWN	2/10/15	HR/NP
C		REVISED SPEC.	7/15/15	HR/YC



Positions: 02 thru 15

A = .049 [1.25] x No. of Spaces

B = .049 [1.25] x No. of Spaces + .118 [3.00]

C = .049 [1.25] x No. of Spaces + .071 [1.80]

D = .049 [1.25] x No. of Spaces + .230 [5.85]

PACKAGED ON TAPE & REEL

SPECIFICATIONS:

Material:
 Insulator: Hi-Temp Thermoplastic, rated UL 94V-0
 Insulator color: Natural
 Contacts: Brass
 Solder nail: Brass
 Plating:
 Tin over Nickel underplate overall
 Electrical:
 Current rating: 1 A AC/DC
 Contact resistance: 20 mohms max
 Insulation resistance: 100 Mohms min
 Dielectric withstanding voltage: 250 VAC for 1 minute
 Temperature Rating:
 -40°C to +85°C
 Environmental:
 Lead free, RoHS compliant.



UNLESS OTHERWISE SPECIFIED
 ALL DIMENSIONS ARE INCHES [MM]
 TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	± .10
.XX	± .020	Ø.XX	± .015
.XXX	± .015	Ø.XXX	± .010

ADAM TECH
 INTERCONNECTS
 909 Rahway Avenue,
 Union, NJ 07083
 Phone: 908-687-5000
 Fax: 908-687-5710

APPROVALS		DATE
DRAWN	BW	01/17/07
CHECKED		
APPROVED		

TITLE			
MX 1.25mm WAFER 90° SMT			
SIZE	PART NO.	REV.	
X	125SH-B-XX-TR-SMT-T/R	C	
REF:	S00124T	SCALE:	NTS
		SHEET 1 OF 1	