

Control Transformer Class 2

TCT40-02E07K

Description:

Triad control transformers come with tamper resistant shrouds for safety and a steel bracket welded to the bottom of the transformer for ease of mounting. These transformers are design and have the safety agency recognition for application where a Class 2 transformer is necessary. Some of the applications would include, but not limited to HVAC, Control boards, Lighting, etc.

Electrical Specifications (@25C):

1. Maximum Power: 40VA

2. Input (BLK-RED): 240V, 50/60 Hz 3. Output (YEL-YEL): 24V @ 1.67Amps

4. Voltage Regulation: 15% TYP @ full load to no load

5. Temperature Rise: <40°C TYP

6. Hipot: 1500VAC - Input to Output, Input & Output to Core

7. Inherently Limited. No fusing required.

Construction:

Three flange bobbin construction with primaries and secondaries wound side by side for low capacitive coupling. Unit weight is 1.5 lbs.

Agency File:

UL: File E65390, UL 5085-3 (1585), Class 2 Transformer cUL: File E65390, UL 5085-3 (1585) For Canadian Use (CSA 22.2, No.66.3-06)




Connections:

Input: 12±1" (305mm) insulated leads, stripped and tinned 0.20±0.08", stranded 18 AWG. UL 1015 lead wire.

Output: 12±1" (305mm) insulated leads, stripped and tinned 0.20±0.08",

stranded 18 AWG, UL 1015 lead wire.

Schematic:



RoHS Compliance: As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.

As of April 7, 2008, UL standards 506 and 1585 will be migrated to UL 5085-2 and 5085-3, respectively.

* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.



