# SBS®X-75A



# Sealed Connector Series

- Industrial / Commercial Power Equipment Material Handling / Automation
- Agricultural / Construction Lawn / Garden Equipment Marine









#### SBS<sup>®</sup>X-75A

The SBS®X-75A sealed waterproof connectors come in a multiple of configuration offerings with up to a maximum of 140A of power and the durability of up to 5,000 mating cycles. Positive metal latches help safeguard against accidental disconnects that may be caused by vibration, while the built-in cable clamp allows for strain relief on wires.

The compact sleek high-power design of these environmentally rugged connectors makes them ideal for outdoor applications. The IP68 weatherproof rating ensures that the connector will be free of water for full protection up to 30 minutes at 6 feet in the mated conditions, or with the use of covers in unmated condition.











600 Volts / 140A

5,000 Mating Cycles

Operating Temperature -20°C to 105°C / -4 °F to 221°F

Dust - Water - Shock

#### **SPECIFICATIONS**

<b>Current Rating A</b>	mperes <sup>1</sup>	Power	Power Only		4 Pole		6 Pole	
Wire to Wire		No Signals		Signals Energized 20 AWG - 10 amps		Signals Energized Using PPMX Contacts (20 AWG - 3 amps)		
AWG	mm²	UL	CSA	UL	CSA	UL	CSA	
4 AWG	25	140	85	135	80	125	75	
6 AWG	16	100	65	95	60	N/A	N/A	
8 AWG	10	95	58	93	53	93	53	
10 AWG	6	75	45	75	45	N/A	N/A	
Wire to Wire & V 6 AWG (16 mm²)	<b>Wire to Panel Mount with Gro</b> Wire	<b>und*</b> 90	65	N/A	N/A	N/A	N/A	
Wire Plug to Pan	el Mount Receptacle							
4 AWG (25 mm	²) Wire	145	90	140	85	N/A	N/A	
Panel Mount Plu	g to Panel Mount Receptacle							
4 AWG (25 mm	²) Wire	140	85	135	80	N/A	N/A	
Voltage Rating A	C/DC							
UL 1977		600V		600V		600V		
Dielectric Withst	anding Voltage							
Volts AC		2,200		2,200		2,200		
Average Mated (	Contact Resistance Milliohms	1						
Power 1/4 in. of	f 4 AWG (25 mm²) Wire	$0.16m~\Omega$		0.16m C	)	$0.16m~\Omega$		
Ground 1/4 in.	of 6 AWG (16 mm²) Wire	$0.22m~\Omega$		N/A		N/A		
Auxiliary 14 AW	/G (1.0 to 1.5 mm²) Wire	2.50m Ω		2.50m Ω	)	20 AWG (.25m	m²) 3 amps - 9.0 Ω	
UL Hot Plug Current Rating Amperes		250 cycles at 120	250 cycles at 120V DC		es at 120V D	С		
4 AWG (25 mm	²) Wire	50A		50A				
Ground Short Tin	ne Current Test							
1530 Amps (6 A	AWG / 16mm²) Wire	6 Seconds						
Touch Safe	Per UL 60	950-1, UL 62368-1 & I	EC 60529 <sup>3</sup>		Per UL 609	50-1, UL 62368	-1 & IEC 60529 <sup>3</sup>	

MECHANICAL	4 Pole		6 Pole		
Wire Size Range					
Power Contacts	10 to 4 AWG (2.5 to 25	5.0 mm²)	10 to 4 AWG (2.5 to 2	5.0 mm²)	
Auxiliary Contacts	14 to 24 AWG (1.5 mn	n² to 0.50)	24 to 20 AWG (0.50 to 0.75 mm <sup>2</sup> )		
Pre-Mate Contacts Ground Only 12	to 6 AWG (2.5 to 16mm <sup>2</sup>	2)			
Maximum Wire Insulation Diameter					
Power/Ground	0.44 in. (11.18 mm)		0.44 in. (11.18 mm)		
Auxiliary	0.44 in.(11.18 mm)		Discrete Wires- 20 AW 6 Cond. Jacketed Cabl	/G; 0.09 in. (2.29 mm) e- 0.021 in. (5.33 mm)	
Operating Temperature <sup>2</sup>	-20° to 105°C (-4 to 22	21°F)	-20° to 105°C (-4 to 22	21°F)	
Mating Cycles No Load by Plating	5,000		5,000		
Average Mating / Unmating Force					
Wire = Lbs / Kg	4 AWG (25 mm²) = 6.5	5 Lbs (2.95 Kg)	4 AWG (25 mm²) = 6.5	4 AWG (25 mm²) = 6.5 Lbs (2.95 Kg)	
Ground Wire = Lbs / Kg 6 AWG (16	5mm²) / 12 Lbs (5.44 Kg)				
Minimum Creepage / Clearance Dist	ance				
	Creepage	Clearance	Creepage	Clearance	
Power to Power	1.50 in. (38.1 mm)	0.900 in. (22.86 mm)	1.50 in. (38.1 mm)	0.900 in. (22.86 mm)	
Power to Signal	1.12 in. (28.4 mm)	0.640 in. (16.26 mm)	1.727 in. (43.87 mm)	0.397 in. (10.08 mm)	
Pin to Pin	0.097 in. (2.46 mm)	0.097 in. (2.46 mm]	0.194 in. (4.93 mm)	0.194 in. (4.93 mm)	
Socket to Socket	0.352 in. (8.94 mm)	0.352 in. (8.94 mm)	0.157 in. (3.99 mm)	0.157 in. (3.99 mm)	
Pin to Socket	1.15 in. (29.21 mm)	0.485 in. (12.3 mm)	0.535 in. (13.59 mm)	0.337 in. (8.56 mm)	
Power to Ground <b>Creepage</b> = 1.20"	(30.5mm) <b>Clearance</b> =0	).28" (7.1mm)			
Pull Out Force with Cable Clamp	60 lb. [267N]		60 lb. [267N]		
Pull Out Force with Cable Clamp Gro	und Only 60lb. [267N]				
Push Out Retention Force Auxiliary	35 lb. [156N]		35 lb. [156N]		
Pull Out Retention Contact Holder (p	part no. 2-8859P1)		20 lb. [89N]		
Drop Test	Per UL 486A-486B		Per UL 486A-486B		
Drop Test Ground	Per UL 486A-486B				
IP68	Per UL50E <sup>4</sup>		Per UL50E <sup>4</sup>		



**IP68 Ground** 

# 600 Volts / 140A

Per UL50E4

MATERIALS		
Housing, Cable Clamps, Covers	PC/PBT	PC/PBT
Signal / Ground Housing	PC	PC
Latches, Spring, Screws	Stainless Steel	Stainless Steel
O-Rings, Grommets	Silicone	Silicone
Panel Mount Gasket	NBR	NBR
Housing Flammability Rating	UL94 V0	UL94 V0
Glow Wire (1.0 mm)	960°C per 60695-2-12	960°C per 60695-2-12
Wire Power Contact	Silver Plated Copper Alloy	Silver Plated Copper Alloy
SBS® 75X Auxiliary Contacts		
Pin	Copper Alloy, Au over Ni	Gold Plated Copper Alloy
Socket	Be Cu, Au over Ni	Gold Plated Copper Alloy
Socket Body	Copper Alloy, Tin Bright over Ni	Copper Alloy, Tin Bright over Ni
Retention Clip	Stainless Steel	Stainless Steel


#### NOTES:


- 1 Current amperage ratings are based on 105°C rated or better cable of the largest wire size using properly calibrated Anderson recommended tooling, and a 25°C ambient temperature, or CSA rating below a 30°C temperature rise. UL rating not to exceed the maximum operating temperature. Connector to be assembled and installed according to the manufacturer's instructions.
- 2 Operating Temperatures are limited by the thermal properties of the connector's plastic housing.
- 3 Sealed Connector Series offers protection against electric shock for finger safety both in mated and unmated condition. The Sealed SBS®X-75A Connector Series was tested for IP Code 1X-2X per clause 12- & 13 of IEC 60529, Edition 2.2, issued 2013-8 + Corr. 1:2013-10 + Corr. 2:2015-01. The connector was tested for IP1X and IP2 in mated and unmated condition, which is representative of protection against access to energized parts contained in UL 60950-1 2nd Edition, 2011-12-19 and UL 62368-1 3rd Edition, 2021-10-22.
- 4 The Sealed SBS®X-75A Connector Series was subjected to submersion test, covered by UL 50E Standard for Enclosures for Electrical Equipment Environmental Considerations, 3rd Edition, with a pressure equivalent to 6 feet of water and for a duration of 30 minutes for the equivalent IP68 compliance. Note panel mount-to-panel mount configuration has not been tested for ingress protection rating: contact manufacturer to determine if it will work for your application.
- 5 6 position auxiliary housing utilizes PPMX contacts.
- 6 It is recommended that for SBS®X-75A, customers use individual discrete wires for power, and jacketed cables for signaling to limit strain on smaller auxiliary wires.




# Operating Temperature -20°C to 105°C / -4 °F to 221°F


#### **TEMPERATURE CHARTS**








SBS®X-75A 6-Position Auxiliary Contacts at 3A Temperature Rise at Constant Current






SBS®X-75A 4-Position Auxiliary Contacts at 10A Derating vs. Ambient Temperature




SBS®X-75A 6-Position Auxiliary Contacts at 3A Derating vs. Ambient Temperature




## **COMPONENTS - \***Center Signal housings are available in 4 or 6 positions. See ordering section for details.


## Wire-to-Wire



## **Wire-to-Panel Mount**




#### **Panel Mount-to-Panel Mount**




## **COMPONENTS - \*Center Ground Housing & Contact**


# Wire-to-Wire



#### **Wire-to-Panel Mount**



## **Panel Mount-to-Panel Mount**



**ORDERING INFORMATION -** Color denotes signal or ground housings only. All other housings are black. Signal housings are available in 4 or 6 position styles. 6 position utilizes PPMX contacts. Ground utilizes ground contacts.

Step 1: Select the Housing Kit - Packaged as Individual Kits. Contacts and Grommets Sold Separately, See Step 2 & 3

Image	Part Number	Description - Sealed SBS®X-75A	Kit Includes- Housing, Signal Housing and Below Parts	
	Minimum Quantity		1	
	SBSX75A-PLUG-KIT-RED	Male Plug - Red	Latches, Cable Clamp, Hardware & Front O-Rings	
	SBSX75A-PLUG-KIT-BLU	Male Plug - Blue	Latches, Cable Clamp, Hardware & Front O-Rings	
X	SBSX75A-PLUG-KIT-GRA	Male Plug - Gray	Latches, Cable Clamp, Hardware & Front O-Rings	
	SBSX75A-PLUG-KIT-BLK	Male Plug - Black	Latches, Cable Clamp, Hardware & Front O-Rings	
The second secon	SBSX75A-6AUX-PLUG-KIT-WHT	6 Position Auxiliary Male Plug - White	6 Position Signal Housing, Contact Holder, Latches, Cable Clamp, Hardware & Front O-rings	
	SBSX75A-PLUG-KIT-GRN	Male Plug- Green (Ground)	Ground Housing, Latches, Cable Clamp, Hardware & Front O-Rings	
44	SBSX75A-REC-KIT-RED	Female Receptacle - Red	Cable Clamp, Hardware	
	SBSX75A-REC-KIT-BLU	Female Receptacle - Blue	Cable Clamp, Hardware	
	SBSX75A-REC-KIT-GRA	Female Receptacle - Gray	Cable Clamp, Hardware	
1	SBSX75A-REC-KIT-BLK	Female Receptacle - Black	Cable Clamp, Hardware	
	SBSX75A-6AUX-REC-KIT-WHT	6 Position Auxiliary Female Receptacle - White	6 Position Signal Housing, Contact Holder, Cable Clamp, Hardware	
	SBSX75A-REC-KIT-GRN	Female Receptacle - Green (Ground)	Ground Housing, Cable Clamp, Hardware	
	SBSX75A-PMREC-KIT-RED	Panel Mount Receptacle - Red *	Panel Gasket, Mounting O-Rings	
	SBSX75A-PMREC-KIT-BLU	Panel Mount Receptacle - Blue *	Panel Gasket, Mounting O-Rings	
%	SBSX75A-PMREC-KIT-GRA	Panel Mount Receptacle - Gray *	Panel Gasket, Mounting O-Rings	
	SBSX75A-PMREC-KIT-BLK	Panel Mount Receptacle - Black *	Panel Gasket, Mounting O-Rings	
	SBSX75A-6AUX-PMREC-KIT- WHT	6 Position Auxiliary Panel Mount Receptacle - White	6 Position Signal Housing, Contact Holder, Panel Gasket, Mounting O-Rings	
	SBSX75A-PMREC-KIT-GRN	Panel Mount Receptacle - Green (Ground)*	Ground Housing, Panel Gasket, Mounting O-Rings	
- 8 -				

Step 1: Continue	d		
Image	Part Number	Description - Sealed SBS®X-75A	Kit Includes- Housing, Signal Housing and Below Parts
	Minimum Quantity		1
9	SBSX75A-PMPLUG-KIT-RED	Panel Mount Plug - Red *	Front O-Ring, Panel Gasket, Mounting O-Rings
	SBSX75A-PMPLUG-KIT-BLU	Panel Mount Plug - Blue *	Front O-Ring, Panel Gasket, Mounting O-Rings
<b>%</b>	SBSX75A-PMPLUG-KIT-GRA	Panel Mount Plug - Gray *	Front O-Ring, Panel Gasket, Mounting O-Rings
	SBSX75A-PMPLUG-KIT-BLK	Panel Mount Plug - Black *	Front O-Ring, Panel Gasket, Mounting O-Rings
	SBSX75A-6AUX-PMPLUG-KIT- WHT	6 Position Auxiliary Panel Mount Plug - White	6 Position Signal Housing, Contact Holder, Front O-Ring, Panel Gasket, Mounting O-Rings
	SBSX75A-PMPLUG-KIT-GRN	Panel Mount Plug - Green (Ground) *	Ground Housing, Front O-Ring, Panel Gasket, Mounting O-Rings

# Bulk Component Ordering Information - All components sold separately. For grommets and contacts, see step 2 & 3.

Image	Part Number	Description - Sealed SBS®X-75A	Includes
	Minimum Quantity		100
	SBSX75A-PLUG-BLK	Male Plug Housing	Housing, Latches & O-Rings
	SBSX75A-REC-BLK	Female Receptacle Housing	Housing
	SBSX75A-PMREC-BLK	Panel Mount Receptacle Housing	Housing
	SBSX75A-PMPLUG-BLK	Panel Mount Plug Housing *	Housing, Front O-Ring

<sup>\*</sup> Panel Mount Plug mates with Panel Mount Receptacle for Panel-to-Panel applications. Please note that this configuration has not been tested for Ingress protection ratings, please contact the manufacturer for further details on this requirement to see if it will work for your application needs. Panel Mount hardware not included.

Step 1 Continued - Bulk Components Continued

	Minimum Quantity		200
	2-8840P1	Signal Housing - Red	Housing
	2-8840P2	Signal Housing - Blue	Housing
	2-8840P3	Signal Housing - Gray	Housing
	2-8840P4	Signal Housing - Black	Housing
	B02893G1	Ground Housing- Green	Housing
	2-8860P1	6 Position Signal Housing- White	Housing
	2-8859P1	6 Position Contact Holder- Black	Contact Holder
	2-8841P1	Cable Clamp	Cable Clamp (set of two)
	2-8863P1	Ground Cable Clamp	Cable Clamp (set of two)
Comple	H1120P62	#4 to 20 5/8" (15.88 mm) Plastite Head Screws - Cable Clamp	Screws
· · · · · · · · · · · · · · · · · · ·	108G1	Panel Mount Hardware Kit	Panel Mount Gasket, Mounting O-Rings

Covers - Use When Parts are Unmated for IP68 Protection						
Image	Part Number	Description- Sealed SBS®X-75A	Includes			
	Minimum Quantity		1			
Andrew Andrews	SBSX75A-PLUG-COVER	Plug Cover *	Housing, Lanyard			
	SBSX75A-REC-COVER	Receptacle Cover	Housing, Latches, O-Ring, Lanyard			
	SBSX75A-PMREC-COVER	Panel Mount Receptacle Cover	Housing, Latches, O-Ring, Lanyard			

<sup>\*</sup> Inquire with Manufacturer or Sales Representative regarding panel mount plug covers



# **Dust - Water - Shock Protection**

#### **Step 2: Grommets Sold Separately**

To select proper grommet size, you will need to know the outer diameter of jacketed cable for each of the Power and Signal cables. Find your overall power size, then determine appropriate outer dimension for both Power and Signal cables. Not using signal, then select NS grommet that matches your power only size. Panel mount housings do not require grommets.

#### **Discrete Wires**



Discrete Wire Power & Signal

#### Wire Size Wire Size Power Wire Signal Cable / Wire Size Part Number AWG mm<sup>2</sup> Diameter Range (mm²) Diameter Range (mm²) D-150-060 10 to 12 2.5 to 6 0.15 to 0.18 (3.81 to 4.57) 0.08 to 0.10 (2.03 to 2.54) D-310-060 6 to 4 16 0.31 to 0.34 (7.87 to 8.64) 0.08 to 0.10 (2.03 to 2.54)

#### **Jacket Cable**



Jacket Cable Power & Signal



Power Only

		Wire Size	Power Wire	Signal Cable / Wire Size
Part Number	Wire Size AWG	mm²	Diameter Range (mm²)	Diameter Range (mm²)
Minimum Quantity 1				
J-150-150	10 to 12	2.5 to 6	0.15 to 0.18 (3.81 to 4.57)	0.15 to 0.18 (3.81 to 4.57)
J-150-180	10 to 12	2.5 to 6	0.15 to 0.18 (3.81 to 4.57)	0.18 to 0.21 (4.57 to 5.33)
J-150-320	10 to 12	2.5 to 6	0.15 to 0.18 (3.81 to 4.57)	0.32 to 0.35 (8.13 to 8.89)
J-150-350	10 to 12	2.5 to 6	0.15 to 0.18 (3.81 to 4.57)	0.35 to 0.38 (8.89 to 9.65)
J-150-380	10 to 12	2.5 to 6	0.15 to 0.18 (3.81 to 4.57)	0.38 to 0.41 (9.65 to 10.41)
J-150-410	10 to 12	2.5 to 6	0.15 to 0.18 (3.81 to 4.57)	0.41 to 0.44 (10.41 to 11.18)
NS-150	10 to 12	2.5 to 6	0.15 to 0.18 (3.81 to 4.57)	No Signal
J-240-150	8	10	0.24 to 0.27 (6.10 to 6.86)	0.15 to 0.18 (3.81 to 4.57)
J-240-180	8	10	0.24 to 0.27 (6.10 to 6.86)	0.18 to 0.21 (4.57 to 5.33)
J-240-240	8	10	0.24 to 0.27 (6.10 to 6.86)	0.24 to 0.27 (6.10 to 6.86)
J-240-320	8	10	0.24 to 0.27 (6.10 to 6.86)	0.32 to 0.35 (8.13 to 8.89)
J-240-350	8	10	0.24 to 0.27 (6.10 to 6.86)	0.35 to 0.38 (8.89 to 9.65)
J-240-380	8	10	0.24 to 0.27 (6.10 to 6.86)	0.38 to 0.41 (9.65 to 10.41)
J-240-410	8	10	0.24 to 0.27 (6.10 to 6.86)	0.41 to 0.44 (10.41 to 11.18)
NS-240	8	10	0.24 to 0.27 (6.10 to 6.86)	No Signal
J-310-150	6	16	0.31 to 0.34 (7.87 to 8.64)	0.15 to 0.18 (3.81 to 4.57)
J-310-180	6	16	0.31 to 0.34 (7.87 to 8.64)	0.18 to 0.21 (4.57 to 5.33)
J-310-310	6	16	0.31 to 0.34 (7.87 to 8.64)	0.31 to 0.34 (7.87 to 8.64)
J-310-320	6	16	0.31 to 0.34 (7.87 to 8.64)	0.32 to 0.35 (8.13 to 8.89)
J-310-350	6	16	0.31 to 0.34 (7.87 to 8.64)	0.35 to 0.38 (8.89 to 9.65)
J-310-380	6	16	0.31 to 0.34 (7.87 to 8.64)	0.38 to 0.41 (9.65 to 10.41)
J-310-410	6	16	0.31 to 0.34 (7.87 to 8.64)	0.41 to 0.44 (10.41 to 11.18)
NS-310	6	16	0.31 to 0.34 (7.87 to 8.64)	No Signal
J-410-150	4	25	0.41 to 0.44 (10.41 to 11.18)	0.15 to 0.18 (3.81 to 4.57)
J-410-180	4	25	0.41 to 0.44 (10.41 to 11.18)	0.18 to 0.21 (4.57 to 5.33)
J-410-320	4	25	0.41 to 0.44 (10.41 to 11.18)	0.32 to 0.35 (8.13 to 8.89)
J-410-350	4	25	0.41 to 0.44 (10.41 to 11.18)	0.35 to 0.38 (8.89 to 9.65)
J-410-380	4	25	0.41 to 0.44 (10.41 to 11.18)	0.38 to 0.41 (9.65 to 10.41)
J-410-410	4	25	0.41 to 0.44 (10.41 to 11.18)	0.41 to 0.44 (10.41 to 11.18)
NS-410	4	25	0.41 to 0.44 (10.41 to 11.18)	No Signal

NOTE: Don't see your cable size requirements? Speak to Manufacturer or your local Representative about other options regarding custom grommets.


## Step 3: Contacts Sold Separately for Power, Ground and Signal


#### **Silver Plated Primary Power Wire Contacts**

SBS®X-75A housings use two silver plated contacts per housing for the best electrical performance and durability up to 10,000 mating cycles.

					Diam - A	
Description	AWG	mm²	Part Number	rs- Loose Piece	inches	mm
Minimum Quantity			1,000	100		
Standard	4	25	1339G4-BK	1339G4 *	0.28	7.11
	6	16	1339G2-BK	1339G2 *	0.22	5.60
	8	10	1339G5-BK	1339G5 *	0.19	4.70
	12 to 10	2.5 to 6	1339G3-BK	1339G3 *	0.14	3.50

<sup>\*</sup> Are sold as pairs. 2 contacts ship for every 1 ordered.






#### **Silver Plated Pre-Mate Wire Contacts**

Pre-Mate contacts used for grounding are for the center Pre-Mate position on the SBS\*-X75A wire housings.

Wile Headings.						
					Diam	
Description	AWG	mm²	Part Number	rs- Loose Piece	inches	mm
Minimum Quantity			500	50		
Pre-Mate	6	16	1340G1-BK	1340G1	0.22	5.60
Pre-Mate	8	10	1340G2-BK	1340G2	0.19	4.70
Pre-Mate	12 to 10	2.5 to 6	1340G3-BK	1340G3	0.14	3.50



#### **Pin Contacts for Auxiliary 4 Positions**


Gold plated contacts are available in 3 lengths to allow sequencing of circuits.

Description	AWG	mm²	Part Numbers
Minimum Quantity			500
Standard Length 7.7 mm	16 to 14	1.0 to 1.5	PM16P1416S30
	20 to 16	0.75 to 1.0	PM16P1620S30
	24 to 20	0.50 to 0.75	PM16P2024S30
Pre-Mate 9.3 mm	16 to 14	1.0 to 1.5	PM16P1416A30
	20 to 16	0.75 to 1.0	PM16P1620A30
	24 to 20	0.50 to 0.75	PM16P2024A30
Post-Mate 6.4 mm	16 to 14	1.0 to 1.5	PM16P1416C30
	20 to 16	0.75 to 1.0	PM16P1620C30
	24 to 20	0.50 to 0.75	PM16P2024C30

## **Auxiliary Pin Contact Lengths**

	-	L-	- L1-		
	in.	mm	in.	mm	
Standard Length 7.7 mm	0.77	19.6	0.30	7.7	
Pre-Mate 9.3 mm	0.83	21.2	0.37	9.3	
Post-Mate 6.4 mm	0.72	18.3	0.25	6.4	

See drawings on website for further details.




#### **Socket Contacts 4 Position Auxiliary**

Selective gold plated contacts offer low resistance and durability up to 10,000 mating cycles.

	,	0 /	
Description	AWG	mm²	Part Numbers
Minimum Quantit	У		500
Socket Contacts	16 to 14	1.0 to 1.5	PM16S1416S32
	20 to 16	0.75 to 1.0	PM16S1620S32
	24 to 20	0.50 to 0.75	PM16S2024S32

# **Auxiliary Socket Contacts Crimp Barrel ID**

AWG	in.	mm.
16 to 14	0.08	2.1
20 to 16	0.07	1.7
24 to 20	0.04	1.1




See drawings on website for further details.

#### Pin & Socket Contacts PPMX 6 Position Auxiliary Connector

Gold plated contacts are ideal for signal or low power use with durability up to 5,000 mating cycles.

Description	AWG	mm²	Part Numbers		
Minimum Quantity			2,000	50	
Pin Contacts	24 to 20	0.50 to 0.25	4803G3-BK	4803G3	
Socket Contacts	24 to 20	0.50 to 0.25	4802G3-BK	4802G3	



NOTE: Contacts sold individually, not sold as a set of two.

#### SBS® TOOLING INFORMATION 5



Wii	e Size	Power Contacts													
AWG	mm²	Power Contact Part Number	Pnenumatic Bench Tool	+	Die	+	Locator	Number of Crimps	OR	Hand Tool					
4	25.0	1339G4	1387G1		1388G7		1389G9	Single		N/A					
6	13.3	1339G2			100005		120000	120000	120000	120000					
8	8.4	1339G5	1387G1		1388G6		1389G9	Single		1309G4					
10 to 12	5.3 to 3.3	1339G3			1388G7										

Wi	re Size						Ground Contact			
AWG	mm²	Contacts	Pneumatic Bench Tool	+	Die	+	Locator	Number of Crimps	OR	Hand Tools
6	13.3	1340G1			120000					
8	8.4	1340G2	1387G1		1388G6		1389G20	Single		1309G4
10 to 12	5.3 to 3.3	1340G3			1388G7					

Wir	e Size			Auxiliary Contacts - 4 Position									
AWG	mm²	Contacts	Pneumatic Bench Tool <sup>6</sup>	+	Die	+	Locator for: TM0001 & TP0001	Mil Std. Hand Tool <sup>6</sup> M22520/1- 01	Number of Crimps	OR	APP® Hand Tool w/ Integral Locator		
14 to 24	1.5 to	All Crimp Pins	TP0001		N/A		TL0001	TM0001	Single		PM1000G1		
14 (0 24	0.50	All Crimp Sockets			IV/A		TL0002	11010001	Siligic		1 W1000G1		
	Tools												
Auxiliary (	Contact Insert	tion Tool: PM1002G1	-	Wire Sizes 24 to 16 AWG (0.50 to 1.00mm²)									
Auxiliary (	Contact Insert	tion Tool: 11038G3		Wire Size 14 AWG ( 1.5mm²)									
Auxiliary Contact Extraction Tool: PM1003G1													
Auxiliary Contact Insertion Inspection Tool: PM1003GX													
Signal Hou	using Extracti	on Tool: $116081$ P1 $^7$											

Wi	re Size				PPMX	Au	xiliary Conta	cts - 6 Position		
AWG	mm²	Contacts	Pneumatic Bench Tool	+	Die	+	Locator	Number of Crimps	OR	Hand Tools
20 to 24	0.50 to 0.25	4803G3	TP0001*		N/A	A	TL0005	Single		TM0001* or
	480		11.0001		, i					PM1000G1

<sup>\*</sup> TP0001 and TM0001 tools require locators to properly position contacts.

#### NOTES:

- 6 The use of Anderson Power tooling is strongly recommended. The use of alternate tools may adversely affect the performance of our connectors along with UL and CSA recognition.
- 7 TP001 and TM0001 tools require locators TL001 for Pins and TL002 for Sockets. The Auxiliary contacts used with wire sizes 14 to 24 AWG (1.5 to 0.50) cannot be properly inserted without the insertion tool. Properly installed Auxiliary contacts of all wire gauges cannot be removed from the housing without the extraction tool. It is highly recommended that inspection tool be used to ensure the auxiliary contacts are seated properly in the housing.
- 8 The Signal Housing Extraction Tool must be used in order to remove the signal housing from the main housing should position be inserted incorrectly for mating. See assembly instructions for further information.



# 5,000 Mating Cycles

## **BUILD YOUR PART NUMBER**

Step 1	Step 2
Housings (including signal) - Center signal housings available in 4 or 6 positions or ground housings.	Grommets
	Step 3
Cable Clamp	Power / Ground Contacts
Screw	
	Signal Contacts (4 or 6 Position)
Panel Mount Kit	
Covers	Tooling

2023-0077 DS-SBSX75A REV 3 Your Best Connection™ All Data Subject to Change Without Notice

Anderson will use reasonable efforts to include accurate and up-to-date content in the data sheet. All product information contained in the data sheet including ordering information, illustrations, specifications, and dimensions, are believed to be reliable as of the date of publishing, but is subject to change without notice. Anderson™ makes no warranty or representation as to its accuracy. Content in the data sheet may contain technical inaccuracies, typographical errors and may be changed or updated without notice. Anderson™ may also make improvements and/or changes to the products and/or to the programs described in the content at any time without notice. Current sales drawings and specifications are available upon request.

©2023 Anderson Power Products, Inc. All rights reserved. A®, SBS® and Anderson Power Products\* are registered trademarks of Anderson Power Products, Inc. Anderson™, Anderson Power™, Anderson Power™ logo, and Your Best Connection™ are trademarks of Anderson Power Products, Inc.



HEADQUARTERS: Anderson Power Products®, 13 Pratts Junction Road, Sterling, MA 01564-2305 USA T: +1 978-422-3800 F: +1 978-422-0128 • EUROPE: Anderson Power Products® and Power Products® Ltd., Unit 3, Europa Court, Europa Boulevard, Westbrook, Warrington, Cheshire, WA5 7TN United Kingdom T: +44 (0) 1925 428390 F: +44 (0) 1925 520203 • GERMANY: IDEAL® Industries Germany GmbH, Esslinger Strasse 7, D – 70771 Leinfelden-Echterdingen, T: +49 (0) 711 – 997606666 • ASIA / PACIFIC: IDEAL® Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong T: +(852) 2636 0836 F: +(852) 2635 9036 • INDIA: IDEAL® INDUSTRIES India Private Limited, 229-230, SPAZEDGE, Tower B, Sector 47, Sohna Road, Gurgaon – 122018, Haryana, India T: +(91) 956-0075905 T: +(91) 124-4495101 • CHINA: IDEAL® Anderson Technologies (Shenzhen) Ltd., Block A8 Tantou Western Industrial Park, Songgang Baoan District, Shenzhen, PR. China 518105 T: +(86) 755 2768 2118 F: +(86) 755 2768 2128 • <u>www.ideal-Industries.in</u> • <u>www.andersonpower.com</u>