
# LINEAR SYSTEMS

## Improved Standard Products<sup>®</sup>

FEATURES							
REVERSE BREAKDOWN VOLTAGE	BV <sub>R</sub> ≥ -30V						
REVERSE CAPACITANCE	C <sub>rss</sub> ≤ 2.0pF						
ABSOLUTE MAXIMUM RATINGS <sup>1</sup>							
@ 25 °C (unless otherwise stated)							
Maximum Temperatures							
Storage Temperature	-55 to +150 °C						
Operating Junction Temperature	-55 to +150 °C						
Maximum Power Dissipation <sup>2</sup>							
Continuous Power Dissipation	300mW						
Maximum Currents							
Forward Current	10mA						

## **PAD-DFN SERIES**

MINIATURE/NON MAGNETIC 8-PIN DFN PACKAGE LOW LEAKAGE DIODE



#### COMMON ELECTRICAL CHARACTERISTICS @ 25 °C (unless otherwise stated)

SYMBOL	CHARACTERISTIC	MIN	TYP	MAX	UNITS	CONDITIONS
BV <sub>R</sub>	Reverse Breakdown Voltage	-30			V	I <sub>R</sub> = -1μΑ
VF	Forward Voltage		0.8	1.5		$I_F = 5 m A$
Crss	Total Reverse Capacitance		1.5		pF	$V_{R} = -5V, f = 1MHz$

#### SPECIFIC ELECTRICAL CHARACTERISTICS @ 25 °C (unless otherwise stated)

SYMBOL	CHARACTERISTIC			UNITS	CONDITIONS
I <sub>R</sub>	Maximum Reverse Leakage Current	PAD5DFN	-5	pА	V <sub>R</sub> = -20V
		PAD50DFN	-50		

#### **Figure 1. Operational Amplifier Protection**


Input Differential Voltage limited to 0.8V (typ) by DFNs  $D_1$  and  $D_2$ . Common Mode Input voltage limited by DFNs  $D_3$  and  $D_4$  to ±15V.


#### Figure 2. Sample and Hold Circuit

Typical Sample and Hold circuit with clipping. DFN diodes reduce offset voltages fed capacitively from the JFET switch gate.



#### **FIGURE 2**





#### **NOTES**

- 1. Absolute maximum ratings are limiting values above which serviceability may be impaired.
- 2. Derate 2.8 mW/°C above 25°C
- The PAD type number denotes its maximum reverse current value in pico amperes. Devices with I<sub>R</sub> values intermediate to those shown are available upon request.

Information furnished by Linear Integrated Systems is believed to be accurate and reliable. However, no responsibility is assumed for its use; nor for any infringement of patents or other rights of third parties which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Linear Integrated Systems.

Linear Integrated Systems develops and produces the highest performance semiconductors of their kind in the industry. Linear Systems, founded in 1987, uses patented and proprietary processes and designs to create its high performance discrete semiconductors. Expertise brought to the company is based on processes and products developed at Amelco, Union Carbide, Intersil and Micro Power Systems by company founder John H. Hall.

### Linear Integrated Systems