

Note:

1. Material:
 - * Insulation: Nylon 6T UL 94V-0
Color Nature(Halogen-Free)
 - * Contact: Brass




2. For Lead Free Wave flow Process

Ordering Code:

CI01 ** P 1 V K0 -NH
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② No. of Circuits:
- ③ P= Pin header
- ④ Plating:
1 = 3.05μm(120μ") Min. Tin over
0.76μm(30μ") Nickel(Matte Tin Finish)
- ⑤ Type:V= Straight
- ⑥ Other option: K0= With Pin Kinked
- ⑦ -NH= For Lead Free Wave flow Process and Halogen-Free



Recommended P.C. Board Layout

Circuits	Dimension		
	A	B	C
2	2.0(.079)	6.0(.236)	4.9(.193)
3	4.0(.157)	8.0(.315)	6.9(.272)
4	6.0(.236)	10.0(.394)	8.9(.350)
5	8.0(.315)	12.0(.472)	10.9(.429)
6	10.0(.393)	14.0(.551)	12.9(.508)
7	12.0(.472)	16.0(.630)	14.9(.587)
8	14.0(.551)	18.0(.709)	16.9(.665)
9	16.0(.630)	20.0(.787)	18.9(.744)
10	18.0(.709)	22.0(.886)	20.9(.823)
11	20.0(.787)	24.0(.945)	22.9(.902)
12	22.0(.886)	26.0(1.024)	24.9(.980)
13	24.0(.945)	28.0(1.102)	26.9(1.059)
14	26.0(1.024)	30.0(1.181)	28.9(1.138)
15	28.0(1.102)	32.0(1.256)	30.9(1.217)
16	30.0(1.181)	34.0(1.339)	32.9(1.295)

Halogen-Free
 Lead Free Process
 RoHS Compliant

④						UNIT: mm / inch	TITLE: 2.00MM(.079") STRAIGHT HEADER	 瀚荃股份有限公司 CviLux Corporation			
③						TOLERANCE UNLESS OTHERWISE SPECIFIED	MATERIAL:		DRAWING NO. CI0124AB	PART NO. CI01**P*VK0-NH	
②						.X ± 0.30/.012 X: ± 1'	CUSTOMER:	SCALE 4 / 1	SHEET 1 OF 1		
①	Enya	3/7-13'	ECN13056-0/ECR13007-1			.XX ± 0.20/.008 X: ±					
SYM	NAME	DATE	REVISIONS	APPROVED BY:	DATE	.XXX ± 0.10/.004 XX: ±					

CIVILUX CORP
 2013.05.16
 ISSUED