CMSD4448

SURFACE MOUNT HIGH SPEED SILICON SWITCHING DIODE





www.centralsemi.com

DESCRIPTION:

The CENTRAL SEMICONDUCTOR CMSD4448 type is a ultra-high speed silicon switching diode manufactured by the epitaxial planar process, in an epoxy molded SUPERmini™ surface mount package, designed for high switching applications.

MARKING CODE: ADA

| MAXIMUM RATINGS: (T _A =25°C) | SYMBOL | | UNITS |
|--|-----------------------------------|-------------|-------|
| Continuous Reverse Voltage | V_{R} | 75 | V |
| Peak Repetitive Reverse Voltage | V_{RRM} | 100 | V |
| Continuous Forward Current | ΙF | 250 | mA |
| Peak Repetitive Forward Current | I _{FRM} | 500 | mA |
| Peak Forward Surge Current, tp=1.0µs | I _{FSM} | 4.0 | Α |
| Peak Forward Surge Current, tp=1.0s | I _{FSM} | 1.0 | Α |
| Power Dissipation | P_{D} | 275 | mW |
| Operating and Storage Junction Temperature | T _J , T _{stg} | -65 to +150 | °C |
| Thermal Resistance | $\Theta_{\sf JA}$ | 455 | °C/W |

ELECTRICAL CHARACTERISTICS: $(T_A=25^{\circ}C \text{ unless otherwise noted})$


| SYMBOL | TEST CONDITIONS | MIN | MAX | UNITS |
|-----------------|--|------|------|-------|
| I_{R} | V _R =20V | | 25 | nA |
| BV_R | I _R =5.0μA | 75 | | V |
| BV_R | I _R =100μA | 100 | | V |
| V_{F} | I _F =5.0mA | 0.62 | 0.72 | V |
| V_{F} | I _F =100mA | | 1.0 | V |
| C_T | $V_R=0$, f=1.0MHz | | 4.0 | pF |
| t _{rr} | $I_F = I_R = 10$ mA, $I_{rr} = 1.0$ mA, $R_L = 100$ Ω | | 4.0 | ns |


CMSD4448

SURFACE MOUNT HIGH SPEED **SILICON SWITCHING DIODE**




SOT-323 CASE - MECHANICAL OUTLINE





PIN CONFIGURATION



| LEAD | CODE: |
|------|-------|

- 1) Anode
- 2) No Connection3) Cathode

MARKING CODE: ADA

| DIMENSIONS | | | | | | |
|------------|--------|-------|-------------|------|--|--|
| | INCHES | | MILLIMETERS | | | |
| SYMBOL | MIN | MAX | MIN | MAX | | |
| Α | 0.002 | 0.008 | 0.05 | 0.20 | | |
| В | 0.004 | - | 0.10 | - | | |
| С | - | 0.004 | - | 0.10 | | |
| D | 0.031 | 0.043 | 0.80 | 1.10 | | |
| E | 0.071 | 0.087 | 1.80 | 2.20 | | |
| F | 0.051 | | 1.30 | | | |
| G | 0.026 | | 0.65 | | | |
| Н | 0.045 | 0.053 | 1.15 | 1.35 | | |
| J | 0.079 | 0.087 | 2.00 | 2.20 | | |
| K | 0.008 | 0.016 | 0.20 | 0.40 | | |

SOT-323 (REV: R3)

OUTSTANDING SUPPORT AND SUPERIOR SERVICES



PRODUCT SUPPORT

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- · Inventory bonding
- · Consolidated shipping options

- · Custom bar coding for shipments
- · Custom product packing

DESIGNER SUPPORT/SERVICES

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free guick ship samples (2nd day air)
- Online technical data and parametric search
- SPICE models
- · Custom electrical curves
- · Environmental regulation compliance
- · Customer specific screening
- · Up-screening capabilities

- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- · Application and design sample kits
- · Custom product and package development

REQUESTING PRODUCT PLATING

- 1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
- 2. If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

CONTACT US

Corporate Headquarters & Customer Support Team

Central Semiconductor Corp. 145 Adams Avenue Hauppauge, NY 11788 USA

Main Tel: (631) 435-1110 Main Fax: (631) 435-1824

Support Team Fax: (631) 435-3388

www.centralsemi.com

Worldwide Field Representatives: www.centralsemi.com/wwreps

Worldwide Distributors:

www.centralsemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: www.centralsemi.com/terms

www.centralsemi.com (001)