



## **SMALL SURFACE MOUNT SUPER FAST DIODES**

VOLTAGE 100 to 600 Volt CURRENT 1 Ampere

### **FEATURES**


- For surface mounted applications in order to optimize board space
- · Ideal for automated placement
- · Glass passivated
- High temperature soldering : 260°C / 10 seconds at terminals
- · Lead free in compliance with EU RoHS 2.0
- Green molding compound as per IEC 61249 standard

#### **MECHANICAL DATA**

- · Case: SOD-123FL, Plastic
- Terminals: Solderable per MIL-STD-750, Method 2026
- Weight: 0.0006 ounces, 0.0173 grams
- Polarity: Color band denotes cathode end



Cathode



### **ABSOLUTE RATINGS**

Ratings at 25°C ambient temperature unless otherwise specified.

Parameter	Test condition	Symbol	ES1001FL	ES1002FL	ES1004FL	ES1006FL	Units
Marking Code		-	E1B	E1D	E1G	E1J	-
Maximum repetitive peak reverse voltage		VRRM	100	200	400	600	٧
Maximum RMS voltage		VRMS	70	140	280	420	٧
Maximum DC blocking voltage		VDC	100	200	400	600	V
Maximum average forward current	TL=120°C	I F(AV)	1				А
Peak forward surge current 8.3ms single half sine-wave	TL=25°C	IFSM	30			А	
Maximum instantaneous forward voltage	1.0A	VF	0.95		1.25	1.7	V
Maximum DC reverse current at rated DC blocking voltage	TJ=25°C TJ=100°C	IR	0.5 10				μΑ
Reverse recovery time	I F=0.5A I R=1A I RR=0.25A	Trr	35				ns
Typical capacitance	4V,1MHz	Сл	7			pF	

## **ELECTRICAL CHARACTERISTICS**

Ratings at 25°C ambient temperature unless otherwise specified.


Parameter		Symbol	ES1001FL	ES1002FL	ES1004FL	ES1006FL	Units
Typical Thermal Resistane	(Notes 1) (Notes 2)	R <sub>eJA</sub> R <sub>eJC</sub>		°CW			
Operating junction and storage temperature range		$T_{J}, T_{STG}$	-55 to +150		°C		

NOTES: 1. Mounted on a FR4 PCB, single-sided copper, mini pad.


2. Mounted on a FR4 PCB, single-sided copper, with 10cm\*10cm copper pad area.







**Fig.1 Forward Current Derating Curve** 



**Fig.2 Typical Junction Capacitance** 




Fig.3 Typical Reverse Characteristics






Fig.4 Typical Reverse Characteristics




**Fig.5 Typical Reverse Characteristics** 




**Fig.6 Typical Forward Characteristics** 







**Fig.7 Typical Forward Characteristics** 




**Fig.8 Typical Forward Characteristics** 





### **MOUNTING PAD LAYOUT**



## **ORDER INFORMATION**

· Packing information

T/R - 10K per 13" plastic Reel

T/R - 3K per 7" plastic Reel





# Part No\_packing code\_Version

ES1001FL\_R1\_00001 ES1001FL\_R2\_00001

# For example:



Packing Code XX					Version Code XXXXX			
Packing type	1 <sup>st</sup> Code	Packing size code	2 <sup>nd</sup> Code	HF or RoHS	1 <sup>st</sup> Code	2 <sup>nd</sup> ~5 <sup>th</sup> Code		
Tape and Ammunition Box (T/B)	Α	N/A	0	HF	0	serial number		
Tape and Reel (T/R)	R	7"	1	RoHS	1	serial number		
Bulk Packing (B/P)	В	13"	2					
Tube Packing (T/P)	Т	26mm	X					
Tape and Reel (Right Oriented) (TRR)	S	52mm	Y					
Tape and Reel (Left Oriented) (TRL)	L	PANASERT T/B CATHODE UP (PBCU)	U					
FORMING	F	PANASERT T/B CATHODE DOWN (PBCD)	D					





# **Disclaimer**

- Reproducing and modifying information of the document is prohibited without permission from Panjit International Inc..
- Panjit International Inc. reserves the rights to make changes of the content herein the document anytime without notification. Please refer to our website for the latest document.
- Panjit International Inc. disclaims any and all liability arising out of the application or use of any product including damages incidentally and consequentially occurred.
- Panjit International Inc. does not assume any and all implied warranties, including warranties
  of fitness for particular purpose, non-infringement and merchantability.
- Applications shown on the herein document are examples of standard use and operation.
   Customers are responsible in comprehending the suitable use in particular applications.
   Panjit International Inc. makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.
- The products shown herein are not designed and authorized for equipments requiring high level of reliability or relating to human life and for any applications concerning life-saving or life-sustaining, such as medical instruments, transportation equipment, aerospace machinery et cetera. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Panjit International Inc. for any damages resulting from such improper use or sale.
- Since Panjit uses lot number as the tracking base, please provide the lot number for tracking when complaining.