

Power Transformer PC Mount: Flat Pack TM

FP34-340

Electrical Specifications (@25C)

1. Maximum Power: 12.0 VA

2. Primary Voltage:

Series: 230V@50/60 Hz Parallel: 115V@50/60Hz

3. Secondary:

Series: 34.0VCT @ 0.340Amps Parallel: 17.0V @ 0.680Amps

Description:

The FP34-340 is part of a series which has a long history of reliable service in the field, made from a proven design and constructed with UL recognized materials.

Construction:

Wound on two dual channel nylon bobbin. Materials are UL recognized, Class B (130° C) rated.

Safety:

These products are 100% hipot tested with an insulation of 2000V between primary and secondary windings and 1500V between the primary / secondary windings and the core.

Agency File:

UL: File E53148, UL 506, Class B General Purpose Transformer, cUL: File E53148, UL 506, Class B General Purpose Transformer, Canadian Use



Dimensions:


Α	В	С	D	Е	F
2.500	2.00	1.062	0.267	0.500	2.00

Units: In inches

Weight: 11.0 oz

Pin Dimension: .020 x .041 in

Schematic:




RoHS Compliance: As of manufacturing date February 2016, all standard products meet the requirements of 2015/863/EU, known as the RoHS 3 initiative.


*Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics website for the most current version. For soldering and washing information please see http://www.triadmagnetics.com/faq.html

Web: www.TriadMagnetics.com Phone 951-277-0757

Fax 951-277-2757

460 Harley Knox Blvd. Perris, California 92571





Publish Date: May 30, 2019