

6

5

4

3





2

1

Rev	AWO #	Description	Date	Appr
-	8367	RELEASED	3/17/08	

APPROVED: _____

DATE: _____ TITLE: _____



PCB LAYOUT

A=.060 [1.50] X No. of Positions -1
 B=.060 [1.50] X No. of Positions + .051 [1.30]

PACKAGED ON TAPE & REEL

SPECIFICATIONS:

Material:
 Insulator: Hi-temp thermoplastic, rated UL 94V-0
 Insulator color: Ivory
 Contacts: Brass

Plating:
 Tin over Nickel underplate overall

Electrical:
 Operating voltage: 100 VAC max
 Current rating: 1.5 Amps max
 Contact resistance: 20 mohms max
 Insulation resistance: 500 Mohms min
 Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:
 Operating temperature: -25°C to +85°C

Environmental:
 Lead free, RoHS compliant.



ADAM TECH

909 Railway Avenue, Union, NJ 07083
 Phone: 908-687-5000 Fax: 908-687-5710

TITLE: MX1.5mm WAFER 180°
 SMT, TAPE & REEL

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]		TOLERANCES: EXCEPT AS NOTED	
INCHES	±.10	ØXX	±.015
.XX	±.020	ØXXX	±.010
.XXX	±.015	ØXXXX	±.010
APPROVALS		DATE	
DRAWN	SS	3/17/08	
CHECKED			
APPROVED			
SIZE	PART NO.	SCALE:	REV.
X	15SH-B-XX-TS-SMT-T/R	NTS	-
REF:		SHEET	1 OF 1

6

5

4

3

2

1