Crystal Clock Oscillator



Application

For Smartphone, Wireless LAN, WiMAX, Bluetooth For Wearable devices

Features


- Ultra compact and light. Dimensions : 1.6 x 1.2 x 0.6 mm, weight : 0.01 g.
- Supports low frequencies starting from 2MHz.
- Supports a wide temperature range from -40 to +125°C.
- Low phase jitter (Typ. 100fs (Frequency Offset : 12kHz to 20MHz)@80MHz, 3.3V)
- Taped units enable automatic mounting IR Reflow (lead free) is possible.
- Lead-free.




Absolute maximum rating Supply Voltage (Vcc) –0.3 to +4.0 V Storage Temperature Range –55 to +125 $^\circ C$


Specifications

Item			Model	NZ1612SH			
Output Specification				CMOS			
Nominal Frequency Range			(MHz)	2 < F ≤ 80			
Overall Frequency Tolerance			(×10 ⁻⁶)	±100	±50	±50	±25
Operating Temperature Range		(°C)	-40 to +125	-40 to +105	-40 to +85	-20 to +70	
Supply Voltage			(V)	+1.8 to +3.3			
Current Consumption Max.	During Operation	+25 °C	(mA)	2.5 to 9.0			
	During Standby	+25 °C	(µA)	20			
V _{OL} Max. / V _{OH} Min.			(V)	0.1 V _{cc} / 0.9 V _{cc}			
Tr Max. / Tf Max.			(ns)	6 / 6 (at 0.1 V $_{CC}$ to 0.9 V $_{CC}$)			
Symmetry Min. to Max.			(%)	45 to 55 (at 0.5 V $_{\rm CC}$)			
Load (C∟) Max.			(pF)	15			
Start-up Time Max.			(ms)	4			
Standby function				Available (Three-state)			





Output Waveform <CMOS>



Standby Function

#1 Input	#3 Output		
Level H (0.7 $V_{CC} \le V_{H} \le V_{CC}$) or OPEN is selected.	Oscillation output ON		
Level L (V _{IL} ≤ 0.3 V _{CC}) is selected.	High impedance		



Standard Type

Crystal Clock Oscillator



NZ1612SH

Standard Type

Specification Number

Overall Frequency	Operating Temperature Range (°C)	Supply Voltage (V)			
Tolerance		+1.8±0.18	+2.5±0.25	+3.0±0.3	+3.3±0.33
± 100 × 10-6	-40 to +125	NSC5152A	NSC5152B	NSC5152C	NSC5152D
± 50 × 10-6	-40 to +105	NSC5103A	NSC5103B	NSC5103C	NSC5103D
± 50 × 10-6	-40 to +85	NSC5101A	NSC5101B	NSC5101C	NSC5101D
± 25 × 10-6	-20 to +70	NSC5100A	NSC5100B	NSC5100C	NSC5100D

Please specify the model name, frequency, and specification number when you order products.

For further questions regarding specifications, please feel free to contact us.