

Vibration Monitoring and Machine Protection Systems

1010 East Main Street, League City, TX 77573 Phone:281.334.0766 Fax: 281.334.4255 www.stiweb.com / www.stiwebstore.com

CMCP787T Premium Dual Output Side Entry Accelerometer with Temperature 3 Pin MS Connector



Features:

- Dual Output Accelerometer with Temperature
- 100mV/g ±5% and 10mV/°C (0-150°C)
- 150°C Max Temperature Range
- ±80g Dynamic Range
- 3 Pin MS 5015 Connector
- Class 1 Division 2 Approved
- Class 1 Division 1 Approved with IS Barrier or Isolator
- ¼"-28 UNF or M8x1.25 Captive Mounting Bolt
- Sealed to IP68

Typical Applications

Fans, Motors, Pumps, Compressors, Centrifuges, Conveyors, Air Handlers, Gearboxes, Rolls, Dryers, Presses, Cooling, HVAC, Spindles, Machine Tooling, Process Equipment and many more.

Technical Performance

Mounted Base Resonance: 27 kHz (nominal)

Sensitivity (Acceleration): 100mV/g ±10% Nominal 80Hz at 22°C

Sensitivity (Temperature): 10mV/°C (0-150°C Range)

Frequency Response: 1.5 Hz to 12 kHz \pm 5% (90cpm to 720kcpm) 1.0 Hz to 13 kHz \pm 10% (60cpm to 780kcpm)

0.8 Hz to 15 kHz ±3dB (48cpm to 900kcpm)

Measurement Range: ±80 g
Transverse Sensitivity: Less than 5%

Electrical

Electrical Noise: 0.1mg max
Current Range: 0.5mA to 8mA
Bias Voltage: 10-12 Vdc
Settling Time: 1 Second
Output Impedance: 200 Ohms max.

Case Isolation: >108 Ohms at 500 Volts

Environmental

Operating Temperature Range: -67 to 302°F (-55 to 150°C)
Sealing: IP68 / Hermetically Sealed

Maximum Shock: 5000 g

Approvals: CE Approved

CSA/UL Class 1 Division 2, Groups B, C and D

Mechanical

Case Material: Stainless Steel
Sensing Element: PZT/Shear
Mounting Torque: 5.9ft. lbs (8Nm)
Weight: 6.5 Oz (185 grams)

Mating Connector: 3 Pin MIL 5015 MS Connector


Mounting Thread:

CMCP787T: 1/4"-28 UNF Captive Bolt Supplied with Sensor CMCP787T-M8: M8x1.25 Captive Bolt Supplied with Sensor

Hazardous Location Ratings

Class I, II, III, Division 1 and 2, Groups A-G, T4, -55°C to + 110°C IP65 Class 1, Zone 0, AEx, ia, IIC, T4, Ga, -55°C to + 110°C Zone 20, AEx, ia, IIIC, T130°C, IP65, Da, -55°C to + 110°C Class I, II, III, Division 1, 2, Groups A-G, T6, -55°C to + 110°C Zone 20, AEx, ia, IIIX, T80°C, IP65, DA, -55°C to + 110°C

Dimensions



Ordering Information:

CMCP787T Premium Dual Output Side Entry Accelerometer with Temperature, 100mV/g, ¼-28 UNF Mount CMCP787T-M8 Premium Dual Output Side Entry Accelerometer with Temperature, 100mV/g, M8x1.25 Mount

Alternative Sensitivity Ordering Information:

CMCP787T-XXX Specify Sensitivity in Place of –XXX

50mV/g (-050), 250mV/g (-250) and 500mV/g (-500)

Recommended Cable Assemblies:

General Purpose TPE Jacketed Cable (Rated to 120°C)

CMCP603L Series 3 Socket MS Connector, Locking Collar, IP67 CMCP603LST Series 3 Socket MS Connector, Push On Seal Tight, IP68

High Temperature FEP Jacketed Cable (Rated to 200°C)

CMCP603H Series 3 Socket MS Connector, Locking Collar, IP67 CMCP603HST Series 3 Socket MS Connector, Push On Seal Tight, IP68

Similar Products



M12 Connector CMCP787T-M12



Submersible CMCP787T-IP



Integral Armored Cable CMCP787T-I