







A B C D E F G

1





1

2




2

3



Electrical schematic diagram without lights
无灯电气原理图



Installation View
安装视图

3

4

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL	B ALEN

PRODUCT NAME:
MODEL NO: TP92501P2S
Https: www.rocpu.tw

ROCPCU TECHNOLOGY CO., LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission



A B C D E F G

5

5

NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注
1	Key 按键	SUS 不锈钢	1	
2	Housing 外壳	SUS 不锈钢	1	
3	Oring O型圈	Silica gel 硅胶	1	
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍
5	LED Base LED基座	PC 塑胶	1	
6	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银
7	Pin 引脚	Brass 黄铜	1	gold-plating 镀金
8	Base 底座	PA46	1	

材质参数

A4				 ROCPCU	<table border="1"> <tr> <th colspan="2">COMMON TOLERANCE</th> </tr> <tr> <td>X.XX</td> <td>± 0.10</td> </tr> <tr> <td>X.X</td> <td>± 0.15</td> </tr> <tr> <td>X</td> <td>± 0.25</td> </tr> <tr> <td colspan="2">ANGULAR</td> </tr> </table>	COMMON TOLERANCE		X.XX	± 0.10	X.X	± 0.15	X	± 0.25	ANGULAR		UNIT	MM	PROJECTED		PRODUCT NAME:
COMMON TOLERANCE																				
X.XX	± 0.10																			
X.X	± 0.15																			
X	± 0.25																			
ANGULAR																				
A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92501P2S												
A2				DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw												
A1				ROCPCU TECHNOLOGY CO.,LTD																
REV	DATE	REVISION	DESCRIPTION	ISSUE	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission															