CTCDRH2D11/HPF Series

Series From 1.5µH to 10µH



CHARACTERISTICS

Description: SMD (shielded) power inductor

Applications: Power supplies for OA equipment, LCD televisions, PC notebooks, portable communication equipment,

DC/DC converters, etc.

Operating Temperature: -40°C to +85°C

IDC: The current when the inductance becomes 35% lower than

its normal value (Ta=20°C). **Inductance Tolerance:** ±30%

Testing: Tested on an HP4285A at 100KHz, 0.25Vrms, 0Adc

Packaging: Tape & Reel

Marking: Parts are marked with inductance code

Miscellaneous: RoHS Compliant.

Additional Information: Additional electrical & physical

information available upon request.

Samples available. See website for ordering information.


SPECIFICATIONS

Part are available in ±30% inductance tolerance only.

Part Number	Inductance (µH)	L Test Freq. (kHz)	DCR Max. (mΩ)	IDC (A)
CTCDRH2D11/HPF-1R5N	1.5	100	80	1.35
CTCDRH2D11/HPF-2R2N	2.2	100	120	1.10
CTCDRH2D11/HPF-3R3N	3.3	100	135	0.90
CTCDRH2D11/HPF-4R7N	4.7	100	238	0.75
CTCDRH2D11/HPF-6R8N	6.8	100	371	0.63
CTCDRH2D11/HPF-100N	10	100	559	0.52

PHYSICAL DIMENSIONS

Size	A	В	C
	Max.	Max.	Max
mm	3.2	3.2	1.2
inches	0.126	0.126	0.047



PAD LAYOUT

