



"H"

1

PARTS ON TAPE

NOTES:

- 1. MATERIAL:
 - (A). TERMINAL: COPPER
 - PLATING: ELECTRO-TIN (.0003 MIN.)
 - (B). TIN-PLATED BRASS FUNNEL FERRULE
 - (C). INSULATION: NYLON (YELLOW)
- 2. MWID: MAXIMUM WIRE INSULATION DIAMETER
- 3. WIRE SIZE: 12-10 AWG
 - 4.0 -6.0 MM²
- 4. "UL" LISTING #E32244

 - "CSA" LISTING #18689
- 5. ALL DIMENSIONS IN INCHES/[MM].
- 6. PARTS ARE ROHS COMPLIANT.
- 7. DIMS. SHOWN ARE FOR REFERENCE ONLY.

DOCUMENT STATUS P1 RELEASE DATE 2019/08/05 20:29:46

0,440010	THIS DRAWIN	G CONTA	INS INFO	ORMATION THAT	IS PROPRIETA	ARY TO MOLEX E	LECTRONIC TECH	NOLOGIES, LLC AND SHO	OULD NOT BE US	ED WITI	HOUT WRI	TTEN PER	RMISSION	i
	DIMENSION UNITS SCALE				C: MIGRATIO							1		
= 0	INCH/MM NTS		ECTR/NX			molex								
E = 0	GENERAL TOLERANCES (UNLESS SPECIFIED)							-						1
▼ = 0	, L	MM	INCH	EC NO:	620952			S	NAP SPADI	E SHO	DRT			
\ <u>\</u> \ = 0	4 PLACES ±		±	DRWN:	DRWN: ABENJAMINLW 2019/06/27 TONGUE TERMINAL AVIKRIMP - 800 SE						SERIE	ES		
**************************************	3 PLACES ±		± .00	5 CHK'D:	GROJAS	S01	2019/07/19							
= 0	2 PLACES ± 0.13 ± .01			1 APPR:	APPR: JMACNEIL			PRODUCT CUSTOMER DRAWING						1
₹ = 0	1 PLACE ± 0.25 ±			INITIAL	INITIAL REVISION:			DOCUMENT NUMBER DOC TYPE DOC PART REVI					REVISION	1 ,
⋈ = 0	0 PLACES ±		±	DRWN:	GZ		1985/04/05	191150046			DCD	000	Λ.	
	ANGULAF	RTOL	± 0.5	APPR:	APPR: JMACNEIL			19113		PSD	000	A		
= 0	DRAFT WHERE APPLICABLE			THIRD ANGLE	THIRD ANGLE PROJECTION DRAW		SERIES	MATERIAL NUMBER	CUSTOMER			SHEET NUMBER		1
	MUST REMAIN WITHIN DIMENSIONS					C-SIZE	19115	SEE TABLE	GENERA	L MAI	MARKET 1 OF 1)F 1	
	5				4		3	2		1				_