MSKSEMI 美森科







TVC



TSS



MOV



GDT



PIFF

MMBT3904-MS

Product specification





TRANSISTOR (NPN)

FEATURES

Complementary to MMBT3906-MS

Reference News

PACKAGE OUTLINE		MARKING
1 2	1. BASE 2. EMITTER 3.COLLECTOR	1AM
SOT-23		

MAXIMUM RATINGS (Ta=25℃ unless otherwise noted)

Symbol	Parameter	Value	Unit
V _{CBO}	Collector-Base Voltage	60	V
V _{CEO}	Collector-Emitter Voltage	40	V
V _{EBO}	Emitter-Base Voltage	6	V
lc	Collector Current	200	mA
Pc	Collector Power Dissipation	200	mW
R _{. JA}	Thermal Resistance From Junction To Ambient	625	°C/W
T _J ,T _{stg}	Operation Junction and Storage Temperature Range	-55∼+150	℃

ELECTRICAL CHARACTERISTICS (Ta=25℃ unless otherwise specified)


Parameter	Symbol	Test conditions	Min	Тур	Max	Unit
Collector-base breakdown voltage	V _{(BR)CBO}	lc=10μA, I _E =0	60			V
Collector-emitter breakdown voltage	V _{(BR)CEO}	lc=1mA, l _B =0	40			V
Emitter-base breakdown voltage	V _{(BR)EBO}	l∈=10μA, Ic=0	6			V
Collector cut-off current	Icex	V _{CE} =30V, V _{EB(off)} =3V			50	nA
Collector cut-off current	Ісво	V _{CB} = 60V, I _E =0			100	nA
Emitter cut-off current	I _{ЕВО}	V _{EB} =5V, I _C =0			100	nA
	h _{FE(1)}	V _{CE} =1V, I _C =10mA	100		300	
DC current gain	h _{FE(2)}	V _{CE} =1V, I _C =50mA	60			
J	h _{FE(3)}	V _{CE} =1V, I _C =100mA	30			
Collector-emitter saturation voltage	V _{CE(sat)}	l _C =50mA, I _B =5mA			0.3	V
Base-emitter saturation voltage	V _{BE(sat)}	lc=50mA, Iв=5mA			0.95	V
Transition frequency	f⊤	V _{CE} =20V,I _C =10mA, f=100MHz	300			MHz
Delay time	t d	V _{CC} =3V, V _{BE(off)} =-0.5V I _C =10mA, I _{B1} =1mA			35	ns
Rise time	t _r	V_{CC} =3V, $V_{BE(off)}$ =-0.5V I_C =10mA, I_{B1} =1mA			35	ns
Storage time	ts	Vcc=3V, Ic=10mA, I _{B1} = I _{B2} =1mA			200	ns
Fall time	t _f	V _{CC} =3V, I _C =10mA, I _{B1} = I _{B2} =1mA			50	ns

CLASSIFICATION OF h_{FE(1)}

HFE	100-300		
RANK	L	н	
RANGE	100 - 200	200 - 300	





Typical Characteristics






PACKAGE MECHANICAL DATA








Cumbal	Dimensions In Millimeters		Dimensions In Inches		
Symbol	Min	Max	Min	Max	
Α	0.900	1.150	0.035	0.045	
A1	0.000	0.100	0.000	0.004	
A2	0.900	1.050	0.035	0.041	
b	0.300	0.500	0.012	0.020	
С	0.080	0.150	0.003	0.006	
D	2.800	3.000	0.110	0.118	
E	1.200	1.400	0.047	0.055	
E1	2.250	2.550	0.089	0.100	
е	0.950 TYP		0.037	7 TYP	
e1	1.800	2.000	0.071	0.079	
L	0.550 REF		0.022	2 REF	
L1	0.300	0.500	0.012	0.020	
θ	0°	8°	0°	8°	

Suggested Pad Layout



Note:

- 1.Controlling dimension:in millimeters.
- 2.General tolerance:± 0.05mm.
- 3. The pad layout is for reference purposes only.

REEL SPECIFICATION

P/N	PKG	QTY
MMBT3904-MS	SOT-23	3000



Attention

- Any and all MSKSEMI Semiconductor products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your MSKSEMI Semiconductor representative nearest you before using any MSKSEMI Semiconductor products described or contained herein in such applications.
- MSKSEMI Semiconductor assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all MSKSEMI Semiconductor products described or contained herein.
- Specifications of any and all MSKSEMI Semiconductor products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer'sproducts or equipment.
- MSKSEMI Semiconductor. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with someprobability. It is possiblethat these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents—or events cannot occur. Such measures include but are not limited to protective circuits anderror prevention circuitsfor safedesign, redundant design, and structural design.
- In the event that any or all MSKSEMI Semiconductor products (including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from theauthorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of MSKSEMI Semiconductor.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. MSKSEMI Semiconductor believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. Whendesigning equipment, referto the "Delivery Specification" for the MSKSEMI Semiconductor productthat you intend to use.