



SPECIFICATIONS
 Rated Current:1.5AMP
 Contact Resistance:20mΩ Max
 Withstand Voltage:500V AC/DC
 Insulation Resistance:1000MΩ Min
 Operation Temperature:-40°C to +105°C

Contact Material:Brass
 Contact Plating:Au or Sn Over Ni
 Insulator Material:Polyester(UL94V-0)
 Standard: PA6T
 Max.Processing Temp: 230°C for 30-60 seconds
 (260°C for 5 seconds)



Dimension antitheses list				
ITEM	PA	PB	W	L
Standard	3.80	2.50	6.50	6.30
Alternate				

Ordering Information

XDZ 200 - * - N - S - * - ** - P

No. of Rows
1=Single Row
2=Dual Row

No. of Pins
02-50 Pin

Type
Z=直针
W=弯针
S=插板
WS=母板

Length
英寸

Contact Plating
G0:Gold Flash
G1:0.8μ' Gold
G2:3μ' Gold
G3:5μ' Gold
G4:10μ' Gold
G5:15μ' Gold
G6:30μ' Gold
S0:Gold Rash/Tin
S1:Tin

默认=W/O Post
无柱
P=With Post
带柱

			GENEAL TOLERANCE	制图 DRAWING	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK				
			X.X ±0.30	批准 APPROVAL	产品名称 TITLE	2.00 双排 贴片 排针 (塑高2.0)	版本 REV.	A
			X.XX ±0.20	比例 SCALE	产品料号 PART NO.	XDZ200-2-N-S-2.0-G1	单位 UNITS	mm
			X.XXX ±0.10	投影 Projection	材料 MATERIAL		页次 SHEET	1/1
1	初版发行		Angle ±3.0°					
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE						