





Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)



SPECIFICATIONS

Rated Current:1.5AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°c to +105°c

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 5 seconds)

| Dimension antitheses list | | | | |
|---------------------------|------|------|------|------|
| ITEM | PA | PB | PC | L |
| Standard | 4.00 | 2.80 | 3.15 | 6.80 |
| Alternate | | | | |

Ordering Information

XDZ 200 - * - N - W - * - **

No. of Rows
1=Single Row
2=Dual Row

No. of Pins
01-40 Pin

Type
Z=直针
W=弯针
S=半插
WS=弯插

Length
英寸

Contact Plating
G0:Gold Flash
G1:0.8u' Gold
G2:3u' Gold
G3:5u' Gold
G4:10u' Gold
G5:15u' Gold
G6:30u' Gold
S0:Gold Flash/Tin
S1:Tin

| | | | GENERAL TOLERANCE | 制图 DRAWING | 深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd | | | |
|-----------|------------------------|-------------------|-------------------|------------------|---|---------------------|-------------|-----|
| | | | DIM TOL | 审核 CHECK | | | | |
| | | | X.X ±0.30 | 批准 APPROVAL | 产品名称 TITLE | 2.00 单排 弯排针 (塑高2.0) | 版本 REV. | A |
| | | | X.XX ±0.20 | 比例 SCALE | 产品料号 PART NO. | XDZ200-1-N-W-2.0-G1 | 单位 UNITS | mm |
| | | | X.XXX ±0.10 | 投影 Projection | 材料 MATERIAL | | 页次 SHEET | 1/1 |
| | | | Angle ±3.0° | | | | | |
| 序号 No. | 变更内容 MODIFY CONTENT | 日期 MODIFY DATE | | | | | | |