



Recommended P.C.B Layout(Top Side)  
(PCB BOARD TOLERANCE±0.05)






SPECIFICATIONS

Rated Current:1.0AMP  
 Contact Resistance:20mΩ Max  
 Withstand Voltage:500V AC/DC  
 Insulation Resistance:1000MΩ Min  
 Operation Temperature:-40°C to +105°C

Contact Material:Brass  
 Contact Plating:Au or Sn Over Ni  
 Insulator Material:Polyester(UL94V-0)  
 Standard: PA6T  
 Max.Processing Temp: 230°C for 30-60 seconds  
 (260°C for 10 seconds)

Dimension antitheses list				
ITEM	PA	PB	W	L
Standard	4.00	1.50	5.50	5.50
Alternate				



Ordering Information

XDZ 127 - \* - N - S - \* - \*\* - P

- No. of Rows: 1=Single Row, 2=Dual Row
- No. of Pins: 02-50 Pin
- Type: Z=直针, W=弯针, S=塑壳, WS=铝壳
- Length: 塑壳
- Contact Plating: G0:Gold Flash, G1:0.8μ' Gold, G2:2μ' Gold, G3:5μ' Gold, G4:10μ' Gold, G5:15μ' Gold, G6:30μ' Gold, S0:Gold Flash/Tin, S1:Tin
- 默认=W/O Post, 无柱, P=With Post, 带柱

			GENERAL TOLERANCE	制图 DRAWING	深圳讯答科技有限公司 ShenzhenXundaTechnology Co.,Ltd			
			DIM TOL	审核 CHECK	产品名称 TITLE	1.27 双排 贴片 排针 (塑高1.0)	版本 REV.	A
			X.X ±0.30	批准 APPROVAL	产品料号 PART NO.	XDZ127-2-N-S-1.0-G1	单位 UNITS	mm
			X.XX ±0.20	比例 SCALE	材料 MATERIAL		页次 SHEET	1/1
			X.XXX ±0.10	投影 Projection				
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	Angle ±3.0°					