

6 5 4 3 2 1

used for: DIN 41617

(b)

Polzahl No. of pos.	A ±0.2	B ±0.1	C ±0.1	D ±0.1	Art.-Nr. Part-No
13	45.6	12x2.5=30	12x2.5=30	40	101A10079X
21	65.6	20x2.5=50	20x2.5=50	60	101A10099X
31	90.6	30x2.5=75	30x2.5=75	85	101A10119X

NOTES:

- INSULATOR: PC GF UL 94 V-1, GREY
- CONTACTS: COPPER ALLOY
PLATING: GOLD OVER NICKEL
50 MATING CYCLES
- CONNECTOR IS PART MARKED: PART-NÖ CONEC ABC

(b)

P.C.B. HOLE DRILLINGS

RoHS compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL

CUSTOMER APPROVAL DATE:

NAME: TITLE:

COMPANY NAME:

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.

OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
1 x d	Ä23-0990	23.06.2023	JLE
1 x c	Ä4688	15.03.2013	E.Mick
3 x b	Ä3087	21.08.2008	Sonne
a	Origin		

tolerance

dim. in mm

2006 date name

drawn 15.11 Schwenker

appd. 16.11 Lehmenkühler

norm DIN 41617

d-old

CONEC

scale: 2:1

material: SEE NOTES

title: MALE CONNECTOR
(b) 13pos.-31pos. / 2.5mm with angled solder pins

dwg no: AutoCAD 2006 10K1A014

part no: SEE TABLE (b)

DIN-A 3 sh: 1/1

6 5 4 3 2 1