


Features

- 30V/-39A,
 $R_{DS(ON)} = 11m\Omega(max.) @ V_{GS} = -10V$
 $R_{DS(ON)} = 18m\Omega(max.) @ V_{GS} = -4.5V$
- Reliable and Rugged
- Lead Free and Green Devices Available (RoHS Compliant)
- ESD protection pass 3KV


Applications

- Load Switch.
- Battery Pack Power Management.

Pin Description



PDFN3x3-8



P-Channel MOSFET

Absolute Maximum Ratings ($T_A = 25^\circ C$ Unless Otherwise Noted)

Symbol	Parameter	Rating	Unit	
Common Ratings				
V_{DSS}	Drain-Source Voltage	-30	V	
V_{GSS}	Gate-Source Voltage	± 20		
T_J	Maximum Junction Temperature	150	$^\circ C$	
T_{STG}	Storage Temperature Range	-55 to 150		
I_S	Diode Continuous Forward Current	$T_C = 25^\circ C$	A	
I_D	Continuous Drain Current	$T_C = 25^\circ C$		-39
		$T_C = 100^\circ C$		-25
I_{DM}	Pulsed Drain Current	$T_C = 25^\circ C$	-70 *	
P_D	Maximum Power Dissipation	$T_C = 25^\circ C$	32.9	W
		$T_C = 100^\circ C$	13.2	
$R_{\theta JC}$	Thermal Resistance-Junction to Case	Steady State	3.8	$^\circ C/W$
I_D	Continuous Drain Current	$T_A = 25^\circ C$	-12 ^b	A
		$T_A = 70^\circ C$	-9.8 ^b	
P_D	Maximum Power Dissipation	$T_A = 25^\circ C$	3.1	W
		$T_A = 70^\circ C$	2	
$R_{\theta JA}$	Thermal Resistance-Junction to Ambient	$t \leq 10s$	40	$^\circ C/W$
		Steady State	75	
I_{AS}^a	Avalanche Current, Single pulse	$L = 0.5mH$	18	A
E_{AS}^a	Avalanche Energy, Single pulse	$L = 0.5mH$	81	mJ

Note *: Current limited by bond wire.

Note a: UIS tested and pulse width are limited by maximum junction temperature $150^\circ C$ (initial temperature $T_J = 25^\circ C$).

Note b: $t < 10s$.

Electrical Characteristics (T = 25°C Unless Otherwise Noted)


Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Unit
Static Characteristics						
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_{DS}=-250\mu A$	-30	-	-	V
I_{DSS}	Zero Gate Voltage Drain Current	$V_{DS}=-24V, V_{GS}=0V$	-	-	-1	μA
		$T_J=85^\circ C$	-	-	-30	
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS}=V_{GS}, I_{DS}=-250\mu A$	-1.3	-1.8	-2.3	V
I_{GSS}	Gate Leakage Current	$V_{GS}=\pm 25V, V_{DS}=0V$	-	-	± 10	μA
$R_{DS(ON)}^c$	Drain-Source On-state Resistance	$V_{GS}=-10V, I_{DS}=-20A$	-	11	14	m Ω
		$V_{GS}=-4.5V, I_{DS}=-10A$	-	18	24	
Diode Characteristics						
V_{SD}^c	Diode Forward Voltage	$I_{SD}=-1A, V_{GS}=0V$	-	-0.7	-1	V
t_{rr}^d	Reverse Recovery Time	$I_{SD}=-20A, di_{SD}/dt=100A/\mu s$	-	20	-	ns
Q_{rr}^d	Reverse Recovery Charge		-	8	-	nC
Dynamic Characteristics ^d						
R_g	Gate Resistance	$V_{GS}=0V, V_{DS}=0V, F=1MHz$	-	9	-	Ω
C_{iss}	Input Capacitance	$V_{GS}=0V, V_{DS}=-15V, Frequency=1.0MHz$	-	1380	-	pF
C_{oss}	Output Capacitance		-	280	-	
C_{rss}	Reverse Transfer Capacitance		-	217	-	
$t_{d(ON)}$	Turn-on Delay Time	$V_{DD}=-15V, R_L=15\Omega, I_{DS}=-1A, V_{GEN}=-10V, R_G=6\Omega$	-	11	-	ns
t_r	Turn-on Rise Time		-	11	-	
$t_{d(OFF)}$	Turn-off Delay Time		-	101	-	
t_f	Turn-off Fall Time		-	60	-	
Gate Charge Characteristics ^d						
Q_g	Total Gate Charge	$V_{DS}=-15V, V_{GS}=-10V, I_{DS}=-20A$	-	30	-	nC
Q_{gs}	Gate-Source Charge		-	1.2	-	
Q_{gd}	Gate-Drain Charge		-	11	-	

Note c: Pulse test ; pulse width $\leq 300\mu s$, duty cycle $\leq 2\%$.


Note d: Guaranteed by design, not subject to production testing.

Typical Operating Characteristics


Power Dissipation




Drain Current



Safe Operation Area




Thermal Transient Impedance




Typical Operating Characteristics (Cont.)


Output Characteristics




Drain-Source On Resistance



Gate-Source On Resistance




Gate Threshold Voltage




Typical Operating Characteristics (Cont.)


Drain-Source On Resistance




Source-Drain Diode Forward





Capacitance





Gate Charge



Avalanche Test Circuit and Waveforms




Switching Time Test Circuit and Waveforms



Package Information

PDFN3x3-8



SYMBOL	DFN3x3-8			
	MILLIMETERS		INCHES	
	MIN.	MAX.	MIN.	MAX.
A	0.80	1.00	0.031	0.039
A1	0.00	0.05	0.000	0.002
A3	0.10	0.25	0.004	0.010
b	0.24	0.35	0.009	0.014
D	2.90	3.10	0.114	0.122
D1	2.25	2.45	0.089	0.096
E	3.10	3.30	0.122	0.130
E1	2.90	3.10	0.114	0.122
E2	1.65	1.85	0.065	0.073
E3	0.56	0.58	0.022	0.023
e	0.65 BSC		0.026 BSC	
K	0.475	0.775	0.019	0.031
L	0.30	0.50	0.012	0.020

RECOMMENDED LAND PATTERN

