



SFF1602 THRU SFF1606

Superfast Recovery Rectifiers

FEATURES

- ◆ Ultrafast 35 Nanosecond Recovery Time
- ◆ 150° C Operating Junction Temperature
- ◆ Popular ITO-220 & TO-220 Package
- ◆ Epoxy Meets UL94 ,V0 @ 1/8"
- ◆ High Temperature Glass Passivated Junction
- ◆ Low Forward Voltage
- ◆ Low Leakage Current
- ◆ Reverse Voltage to 600 Volts
- ◆ Pb-Free Packages are Available

MECHANICAL DATA

- Case: Epoxy, Molded
- Finish: All External Surfaces Corrosion Resistant and Terminal Leads are Readily Solderable
- Lead Temperature for Soldering Purposes: 260° C Max. for 10 Seconds
- Shipped 50 units per plastic tube

ITO-220AB



TO-220AB



Maximum Ratings and Electrical Characteristics

Ratings at 25°C ambient temperature unless otherwise specified.
Single phase, half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

Type Number	Symbol	SFF1602	SFF1604	SFF1606	Units
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	200	400	600	V
Maximum RMS Voltage	V_{RMS}	140	280	420	V
Maximum DC Blocking Voltage	V_{DC}	200	400	600	V
Maximum Average Forward Rectified Current @ $T_C = 100^\circ C$	$I_{(AV)}$	16			A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I_{FSM}	100			A
Maximum Instantaneous Forward Voltage @ 8.0A	V_F	0.975	1.30	1.70	V
Maximum DC Reverse Current @ $T_A=25^\circ C$ at Rated DC Blocking Voltage @ $T_A=100^\circ C$	I_R	10 400			uA uA
Maximum Reverse Recovery Time (Note 1)	T_{rr}	35			nS
Typical Junction Capacitance (Note 2)	C_j	80	60		pF
Typical Thermal Resistance (Note 3)	$R_{\theta JC}$	1.5			°C/W
Operating Temperature Range	T_J	-65 to +150			°C
Storage Temperature Range	T_{STG}	-65 to +150			°C

- Notes: 1. Reverse Recovery Test Conditions: $I_F=0.5A$, $I_R=1.0A$, $I_{RR}=0.25A$
2. Measured at 1 MHz and Applied Reverse Voltage of 4.0 V D.C.
3. Mounted on Heatsink Size of 3" x 5" x 0.25" Al-Plate.



SFF1602 THRU SFF1606

Superfast Recovery Rectifiers

Characteristic Curves ($T_A=25^\circ\text{C}$ unless otherwise noted)

FIG.1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.2- TYPICAL REVERSE CHARACTERISTICS




FIG.3- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT PER LEG




FIG.5- TYPICAL FORWARD CHARACTERISTICS PER LEG




FIG.4- TYPICAL JUNCTION CAPACITANCE PER LEG






FIG.6- REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM






SFF1602 THRU SFF1606

Superfast Recovery Rectifiers

PACKAGE OUTLINE

ITO-220AB



TO-220AB

