


SURFACE MOUNT HIGH SPEED SILICON SWITCHING DIODE





www.centralsemi.com

# DESCRIPTION:

The CENTRAL SEMICONDUCTOR CMHD4448 type is a ultra-high speed silicon switching diode manufactured by the epitaxial planar process, epoxy molded in a SOD-123 surface mount package, designed for high speed switching applications.

# MARKING CODE: C48

| MAXIMUM RATINGS: (T <sub>A</sub> =25°C)    | SYMBOL                            |             | UNITS |
|--|-----------------------------------|-------------|-------|
| Continuous Reverse Voltage                 | VR                                | 75          | V     |
| Peak Repetitive Reverse Voltage            | V <sub>RRM</sub>                  | 100         | V     |
| Continuous Forward Current                 | ١ <sub>F</sub>                    | 250         | mA    |
| Peak Repetitive Forward Current            | IFRM                              | 500         | mA    |
| Peak Forward Surge Current, tp=1.0µs       | IFSM                              | 4.0         | А     |
| Peak Forward Surge Current, tp=1.0s        | IFSM                              | 1.0         | А     |
| Power Dissipation                          | PD                                | 400         | mW    |
| Operating and Storage Junction Temperature | T <sub>J</sub> , T <sub>stg</sub> | -65 to +150 | °C    |
| Thermal Resistance                         | ΘJΑ                               | 312.5       | °C/W  |

# **ELECTRICAL CHARACTERISTICS:** (T<sub>A</sub>=25°C unless otherwise noted)

| SYMBOL          | TEST CONDITIONS  | MIN  | MAX  | UNITS |
|-----------------|--|------|------|-------|
| I <sub>R</sub>  | V <sub>R</sub> =20V  |      | 25   | nA    |
| I <sub>R</sub>  | V <sub>R</sub> =20V, T <sub>C</sub> =25°C  |      | 50   | μA    |
| IR              | V <sub>R</sub> =75V  |      | 5.0  | μA    |
| BVR             | Ι <sub>R</sub> =100μΑ  | 100  |      | V     |
| V <sub>F</sub>  | I <sub>F</sub> =5.0mA  | 0.62 | 0.72 | V     |
| VF              | I <sub>F</sub> =100mA  |      | 1.0  | V     |
| CT              | V <sub>R</sub> =0, f=1.0MHz  |      | 4.0  | pF    |
| t <sub>rr</sub> | $V_R$ =6.0V, I <sub>F</sub> =10mA, I <sub>R</sub> =1.0mA, R <sub>L</sub> =100 $\Omega$ |      | 4.0  | ns    |


R7 (5-August 2010)




## CMHD4448

### SURFACE MOUNT HIGH SPEED SILICON SWITCHING DIODE

# SOD-123 CASE - MECHANICAL OUTLINE





R5

LEAD CODE 1) Cathode 2) Anode

MARKING CODE: C48

| DIMENSIONS       |        |       |             |      |  |  |  |
|------------------|--------|-------|-------------|------|--|--|--|
|                  | INCHES |       | MILLIMETERS |      |  |  |  |
| SYMBOL           | MIN    | MAX   | MIN         | MAX  |  |  |  |
| А                | 0.037  | 0.053 | 0.95        | 1.35 |  |  |  |
| В                | 0.000  | 0.005 | 0.00        | 0.12 |  |  |  |
| С                | -      | 0.008 | -           | 0.20 |  |  |  |
| D                | 0.055  | 0.071 | 1.40        | 1.80 |  |  |  |
| Е                | 0.098  | 0.110 | 2.50        | 2.80 |  |  |  |
| F                | 0.142  | 0.154 | 3.60        | 3.90 |  |  |  |
| G                | 0.016  | -     | 0.40        | -    |  |  |  |
| Н                | 0.020  | 0.028 | 0.50        | 0.70 |  |  |  |
| J                | 0.010  | -     | 0.25        | -    |  |  |  |
| SOD-123 (REV:R5) |        |       |             |      |  |  |  |

R7 (5-August 2010)

www.centralsemi.com

# **OUTSTANDING SUPPORT AND SUPERIOR SERVICES**

#### **PRODUCT SUPPORT**

Central's operations team provides the highest level of support to insure product is delivered on-time.

- Supply management (Customer portals)
- Inventory bonding
- · Consolidated shipping options

#### **DESIGNER SUPPORT/SERVICES**

Central's applications engineering team is ready to discuss your design challenges. Just ask.

- Free quick ship samples (2<sup>nd</sup> day air)
- Online technical data and parametric search
- SPICE models
- Custom electrical curves
- Environmental regulation compliance
- Customer specific screening
- Up-screening capabilities

ss your design challenges.

· Custom product packing

- Special wafer diffusions
- PbSn plating options
- Package details
- Application notes
- · Application and design sample kits

Custom bar coding for shipments

Custom product and package development

## **REQUESTING PRODUCT PLATING**

- 1. If requesting Tin/Lead plated devices, add the suffix "TIN/LEAD" to the part number when ordering (example: 2N2222A TIN/LEAD).
- If requesting Lead (Pb) Free plated devices, add the suffix "PBFREE" to the part number when ordering (example: 2N2222A PBFREE).

# CONTACT US

## **Corporate Headquarters & Customer Support Team**

Central Semiconductor Corp. 145 Adams Avenue Hauppauge, NY 11788 USA Main Tel: (631) 435-1110 Main Fax: (631) 435-1824 Support Team Fax: (631) 435-3388 www.centralsemi.com

Worldwide Field Representatives: www.centralsemi.com/wwreps

Worldwide Distributors: www.centralsemi.com/wwdistributors

For the latest version of Central Semiconductor's **LIMITATIONS AND DAMAGES DISCLAIMER**, which is part of Central's Standard Terms and Conditions of sale, visit: <u>www.centralsemi.com/terms</u>

