

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL	B

PRODUCT NAME:	
MODEL NO: TP94002P2S	
Https: www.rocpu.tw	

ROCPU TECHNOLOGY CO., LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission



性能参数

1. Heating current: Ui: AC250V, Ith: 5A
发热电流: Ui: AC250V, Ith: 5A
2. Rated current:3A/DC36V
额定电流:3A/DC36V
3. Power-frequency withstand voltage:2000V/1min
工频耐压:2000V/1min
4. Insulation resistance:≥1000MΩ
绝缘电阻 :≥1000MΩ
5. Contact resistance:≤50mΩ
接触电阻 :≤50mΩ
6. Pressing stroke:2.50mm ± 0.10
按压行程:2.50mm ± 0.10
7. Contact stroke:1.50mm±0.10
接触行程 :1.50mm±0.10
8. welding temperature: 320 °C± 20 °C
焊接温度: 320 °C± 20 °C
9. Welding duration: Less than 3 seconds in duration
焊接时长: Less than 3 seconds in duration
10. Nut assembly torque:5-14N.m
螺帽装配力矩:5-14N.m
11. Protection level:IP67
防护等级:IP67
12. Explosion prevention level: IK10
防暴等级: IK10

13. Working environment temperature: -20 °C~+55 °C
工作环境温度: -20 °C~+55 °C
14. Compression torque: ≤ 2.5N
按压扭力: ≤2.5N
15. Electrical life: 50,000 cycles
电气寿命: 50,000 cycles
16. Mechanical: 500,000cycles
机械寿命: 500,000cycles
17. Operation method:self repeating form
操作方式: 自复式
18. NO reverse thrust foot torque: ≤30N
NO反推脚扭力: ≤30N



连接形式

1. Welding temperature of wire: 320 ± 20 °C
线材焊接温度: 320±20°C
Wire welding duration: less than 3 seconds
线材焊接时长: 时长3秒以下
2. Can be used with dedicated connectors:
可配专用接插件使用:
 - 2.1 Switch function wire: Green Line (C) Blue Line (NO) Yellow Line (NC)
开关功能线材: 绿线 (C) 蓝线 (NO) 黄线 (NC)

A4				 台普 ROCPU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO:TP94002P2S	
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw	
A1					X	± 0.25	ROCPU TECHNOLOGY CO.,LTD					
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR						Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission
A		B		C		D		E		F		G

NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注
1	Key 按键	SUS 不锈钢	1	
2	Housing 外壳	SUS 不锈钢	1	
3	Oring O型圈	Silica gel 硅胶	1	
4	Arm nut 固定螺帽	Brass 黄铜	1	nickeling 镀镍
5	Contact material 接触材质	silver alloy 银合金	1	Silvering 镀银
6	NOPin NO引脚	Brass 黄铜	1	gold-plating 镀金
7	Base 底座	PA46	1	Silvering 镀银
8				
9				

材质参数

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3					X.XX	± 0.10	DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP94002P2S
A2					X.X	± 0.15	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
A1					X	± 0.25	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	ANGULAR					