SIEMENS

Data sheet

US2:17CUB92NJ10



Non-reversing motor starter, Size 0, Three phase full voltage, Solid-state overload relay, OLR amp range 0.75-3.4A, 24VAC 50-60Hz coil, Combination type, 30A fusible disconnect, 30A/250V fuse clip, Enclosure NEMA type 4/12, Water/dust tight for outdoors, Standard width enclosure

Fi	g	ur	e	si	m	ilar

product brand name	Class 17		
design of the product	Non-reversing motor starter with fusible disconnect		
special product feature	ESP200 overload relay		
General technical data	·		
weight [lb]	34 lb		
Height x Width x Depth [in]	24 × 11 × 8 in		
touch protection against electrical shock	NA for enclosed products		
installation altitude [ft] at height above sea level maximum	6560 ft		
ambient temperature [°F]			
 during storage 	-22 +149 °F		
 during operation 	-4 +104 °F		
ambient temperature			
 during storage 	-30 +65 °C		
 during operation 	-20 +40 °C		
country of origin	USA		
Horsepower ratings			
yielded mechanical performance [hp] for 3-phase AC motor			
• at 200/208 V rated value	0.5 hp		
• at 220/230 V rated value	0.75 hp		
• at 460/480 V rated value	0 hp		
 at 575/600 V rated value 	0 hp		
Contactor			
size of contactor	NEMA controller size 0		
number of NO contacts for main contacts	3		
operating voltage for main current circuit at AC at 60 Hz maximum	600 V		
operational current at AC at 600 V rated value	18 A		
mechanical service life (switching cycles) of the main contacts typical	1000000		
Auxiliary contact			
number of NC contacts at contactor for auxiliary contacts	0		
number of NO contacts at contactor for auxiliary contacts	1		
number of total auxiliary contacts maximum	8		
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)		
Coil			
type of voltage of the control supply voltage	AC		
control supply voltage			

at AC at 60 Hz rated value holding power at AC minimum apparent pick-up power of magnet coil at AC apparent holding power of magnet coil at AC operating range factor control supply voltage rated value	24 V 24 V 8.6 W 218 VA 25 VA 0.85 1.1		
holding power at AC minimum apparent pick-up power of magnet coil at AC apparent holding power of magnet coil at AC operating range factor control supply voltage rated value	8.6 W 218 VA 25 VA 0.85 1.1		
apparent pick-up power of magnet coil at AC apparent holding power of magnet coil at AC operating range factor control supply voltage rated value	218 VA 25 VA 0.85 1.1		
apparent holding power of magnet coil at AC operating range factor control supply voltage rated value	25 VA 0.85 1.1		
operating range factor control supply voltage rated value	0.85 1.1		
of magnet coil			
percental drop-out voltage of magnet coil related to the input voltage	50 %		
ON-delay time	19 29 ms		
OFF-delay time	10 24 ms		
Overload relay			
product function			
overload protection	Yes		
phase failure detection	Yes		
asymmetry detection	Yes		
ground fault detection	Yes		
test function	Yes		
external reset	Yes		
reset function	Manual, automatic and remote		
trip class	CLASS 5 / 10 / 20 (factory set) / 30		
	0.75 3.4 A		
	3 s		
	1 %		
	Yes		
	1		
	1		
operational current of auxiliary contacts of overload relay			
	5 A		
	1 A		
	5A@600VAC (B600), 1A@250VDC (R300)		
insulation voltage (Ui)			
	600 V		
	300 V		
Disconnect Switch			
	30A / 250V		
	Class R fuse clips		
	Class R		
Enclosure			
	4 12		
	4, 12 dustarsof waterpress 8 weatherpress		
5 5	dustproof, waterproof & weatherproof		
Mounting/wiring			
	vertical		
	Surface mounting and installation		
	Box lug		
	35 35 lbf·in		
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (14 2 AWG)		
permissible	75 °C		
material of the conductor for supply	AL or CU		
type of electrical connection for load-side outgoing feeder	Screw-type terminals		
tightening torque [lbf·in] for load-side outgoing feeder	20 24 lbf·in		
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	2x (14 10 AWG)		
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C		

material of the conductor for load side outgoing fooder	CU			
material of the conductor for load-side outgoing feeder				
type of electrical connection of magnet coil	Screw-type terminals			
tightening torque [lbf·in] at magnet coil	5 12 lbf·in			
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)			
temperature of the conductor at magnet coil maximum permissible	75 °C			
material of the conductor at magnet coil	CU			
type of electrical connection for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in			
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)			
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C			
material of the conductor at contactor for auxiliary contacts	CU			
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)			
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C			
material of the conductor at overload relay for auxiliary contacts	CU			
Short-circuit current rating				
design of the fuse link for short-circuit protection of the main circuit required	10kA@600V (Class H or K); 100kA@600V (Class R or J)			
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14			
Further information				
Industrial Controls - Product Overview (Catalogs, Brochures,) www.usa.siemens.com/iccatalog				
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:17CUB92NJ10				
Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/US/en/ps/US2:17CUB92NJ10				
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:17CUB92NJ10⟨=en				
Certificates/approvals https://support.industry.siemens.com/cs/US/en/ps/US2:17CUB92NJ10/certificate				

last modified:

1/25/2022 🖸