

SPECIFICATIONS:

ELECTRICAL:

INSULATION RESISTANCE: 1,000 MOhms MIN. **OPERATING TEMPERATURE:** -50°C TO +100°C VOI TAGE: 500 VAC FOR 1 MINUTE

MATERIALS:

INSULATOR: PBT +30% GF, UL94 V-0


PROCESS TEMP: 230°C

SHELL: NICKEL PLATED STEEL

## COMPATIBLE WITH NORCOMP CONTACT PART NUMBERS BELOW:

180-001-170L001 180-101-170L001

\*\*NOTE: CONTACTS MUST BE PURCHASED SEPARATELY\*\*



BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DATE: 07/19/2005


DWG NO.

DO NOT SCALE FROM DRAWING SCALE: SHEET OF NTS 1

**REV** 

24

180-YYY-17YLYY0



DESCRIPTION: MALE // HD DSUB // CRIMP AND POKE