

15DMWE4_1.5 series

15W - Single Output - Wide Input - Isolated & Regulated 1" x 1" DC-DC Converter



DC-DC Converter

15 Watt



High efficiency up to 91%

F Short circuit protection (SCP)

Isolation voltage: 1.5kVDC

 Over-current, over-voltage, under-voltage protection

RoHS compliant

- Operating temperature range: -40°C to +105°C
- Meets CISPR32/EN55032 CLASS A, no external components
- ← International standard pin-out
- Wiring and rail mounting products featuring antireverse connection for input
- F EN62368, UL62368 approved

The 15DMWE4_1.5 series are isolated 15W DC/DC converters with 2:1 input voltage. They feature efficiency up to 91%, 1500VDC isolation, operating temperature of -40°C to +105°C, input under-voltage protection, output over-voltage, output over-current, output short circuit protection and EMI meets CISPR32/EN55032 CLASS A.

They are widely applied in industrial control, electric power, instruments and communication fields. Extension packages with wiring mounting and rail mounting also enable them with reverse voltage protection.







Common specifications	
Short circuit protection:	Hiccup, continuous, self-recovery
Cooling:	Free air convection
Operation temperature range:	• 3.3V/5V output: 40°C~+95°C • others: -40°C~+105°C
Storage temperature range:	-55°C~+125°C
Storage humidity range:	95% MAX
Lead temperature:	300°C MAX, 1.5mm from case for 10 sec
Vibration:	10-150Hz, 5G, 0.75mm. along X, Y and Z
Case material:	Aluminium alloy
MTBF (MIL-HDBK-217F @25°C):	1,000,000 hours
Weight:	15g / 35g (wiring) / 55g (rail) with heatsink: 20g / 40g (wiring) / 60g (rail)

Output specification	ons				
Item	Test condition	Min	Тур	Max	Units
Voltage accuracy			±1	±3	%
Line regulation	Full load , Vmin-Vmax		±0.2	±0.5	%
Load regulation	5% load to full load		±0.5	±1	%
Transient recovery time	25% load step change		300	500	μς
Transient response deviation	25% load step change • 3.3V/5V output • Others		±3 ±3	±7 ±5	% %
Temperature drift	Full load			±0.03	%/°C
Ripple and noise*	20MHz Bandwidth		50	100	mVp-p
Trim	Input voltage range	90		110	%Vo
Over voltage protection	Input voltage range	110		160	%Vo
Over current protection	Input voltage range	110	150	190	%lo

^{* 0%-5%} load ripple&noise is no more than 5%Vo. Ripple and noise are measured by "parallel cable" method.

xample:

15DMWE4_2415S1.5

15 = 15Watt; D = DIP; M = series; W4 = wide input (4:1); E = cost effective; 9-36Vin; 15Vout; S = single output; 1.5 = 1500VDC isolation

Input specifications					
Item	Test condition	Min	Тур	Max	Units
Input current (full load/no load) Nominal input series, nominal input voltage	24VDC • 3.3V output • 5V output • 12V output • 15V output • 24V output		625/30 694/30 694/6 687/6 687/10	640/50 710/50 710/15 703/15 703/20	mA mA mA mA
	48VDC • 3.3V output • 5V output • 12V output • 15V output • 24V output		313/15 348/15 344/3 344/3 344/4	320/30 356/30 352/11 352/11 352/11	mA mA mA mA
Reflected ripple current	Nominal input series		30		mA
Surge voltage (1sec. max)	• 24VDC input • 48VDC input	-0.7 -0.7		50 100	VDC VDC
Starting voltage*	• 24VDC input • 48VDC input			9 18	VDC VDC
Input under-volta- ge protection	• 24VDC input • 48VDC input	5.5 12	6.5 15.5		VDC VDC
Starting time*			10		ms
Input filter	Pi Type				
Hot plug	Unavailable				
Switching frequen- cy (PWM mode)	• 3.3V/5V output • others		300 270		KHz
Ctrl (The voltage of Ctrl pin is relative to	Module switch on Module switch off	Ctrl suspended or connected to TT high level (3.5-12VDC) Ctrl pin connected to GND or low level (0-1.2VDC)			or low
input pin GND)	 Input current when switched off 		2	7	mA

^{*} Nominal input voltage & constant resistance load

Isolation specifications							
Item	Test condition	Min	Тур	Max	Units		
Isolation voltage*	Input/output	1500			VDC		
Isolation voltage*	Input/output case	1000			VDC		
Isolation resistance	Test at 500VDC	1000			ΜΩ		
Isolation capacitance			2000		pF		

^{*} with the test time of 1 minute and the leak current lower than 1mA

15DMWE4 1.5 series

15W - Single Output - Wide Input - Isolated & Regulated 1" \times 1" DC-DC Converter

EMC sp	ecifications			
EMI	CE	CISPR32/EN55032	CLASS A (without external components)/ CLASS B (see EMC solution recommended circuit, ②)	
EMI	RE	CISPR32/EN55032	CLASS A (without external components)/ CLASS B (see EMC solution recommended circuit, ②)	
EMS	ESD	IEC/EN61000-4-2	Contact ±6KV, Air ±8KV	perf. Criteria B
EMS	RS	IEC/EN61000-4-3	10V/m	perf. Criteria A
EMS	EFT	IEC/EN61000-4-4	±2KV (see EMC solution recommended circuit, ①)	perf. Criteria A
EMS	Surge	IEC/EN61000-4-5	line to line $\pm 2 \text{KV}$ (see EMC solution recommended circuit, $\textcircled{1}$)	perf. Criteria B
EMS	CS	IEC/EN61000-4-6	3 Vr.m.s	perf. Criteria A

Part Number	Inpu Nominal	t Voltage [VD0 Range*] Max**	Output Voltage [VDC]	Output Current [mA] Full load	Efficiency [%, Typ.]***	Capacitive load [μF, Max.]
15DMWE4_2403S1.5	24	9-36	40	3.3	4000	88	4700
15DMWE4_2405S1.5	24	9-36	40	5	3000	90	4700
15DMWE4_2412S1.5	24	9-36	40	12	1250	90	1000
15DMWE4_2415S1.5	24	9-36	40	15	1000	91	820
15DMWE4_2424S1.5	24	9-36	40	24	625	91	270
15DMWE4_4803S1.5	48	18-75	80	3.3	4000	88	4700
15DMWE4_4805S1.5	48	18-75	80	5	3000	90	4700
15DMWE4_4812S1.5	48	18-75	80	12	1250	91	1000
15DMWE4_4815S1.5	48	18-75	80	15	1000	91	820
15DMWE4_4824S1.5	48	18-75	80	24	625	91	270


Add suffix H for heatsink, f.ex. 15DMWE4_1203S1.5H, suffix CM for chassis mounting, f.ex. 15DMWE4_1203S1.5CM, or suffix RM for rail mounting, f.ex. 15DMWE4_1203S1.5RM. If the application has a higher requirement for heat dissipation, you can choose modules with heat sink.

- * The minimum input voltage and starting voltage of wring or rail models are 1VDC higher than those of DIP package due to input reverse polarity protection function.
- ** Absolute maximum rating without damage on the converter, but it isn't recommended.
- *** Efficiency is measured in nominal input voltage and rated output load; for wiring and rail mounting models, due to input reverse polarity protection, a minimum efficiency greater than Min.-2 is qualified.

Typical characteristics

Nominal input voltage, 12V, 15V, 24V output


Nominal input voltage, 3.3V, 5V output



15DMWE4 1.5 series

15W - Single Output - Wide Input - Isolated & Regulated 1" \times 1" DC-DC Converter


Efficiency



Typical application


All the DC/DC converters of this series are tested according to the recommended circuit before delivery.

If it is required to further reduce input and output ripple, properly increase the input & output of additional capacitors Cin and Cout or select capacitors of low equivalent impedance provided that the capacitance is no larger than the max. capacitive load of the product.



Vout (VDC)	Cin (µF)	Cout (µF)
3.3/5/12/15	400	100
24	100	47

EMC solution-recommended circuit




Notes: Part 1 is used for EMC test and part 2 for EMI filtering; selected based on needs.

Parameter description:

amotor docomption.					
Vin:24V	Vin:48V				
Choose according to	actual input current				
330µF/50V	330µF/100V				
4.7µF/50V	4.7μF/ 100V				
Refer to the Cout in	typical application				
2.2µH/4A	2.2µH/2A				
1nF/2KV					
	Choose according to 330µF/50V 4.7µF/50V Refer to the Cout in 2.2µH/4A				

Application of trim and calculation of trim resistance



Applied circuits of Trim (Part in broken line is the interior of models)

Calculation formula of Trim resistance:

up:
$$R_T = \frac{\alpha R_2}{R_2 - \alpha} - R_3$$
 $\alpha = \frac{Vref}{Vo' - Vref} R_1$


down:
$$R_T = \frac{\alpha R_1}{R_1 - \alpha} - R_3$$
 $\alpha = \frac{\text{Vo'-Vref}}{\text{Vref}} \cdot R_2$

 R_{T} is Trim resistance a is a self-defined parameter, with no real meaning.

Vout(V)	R1(K Ω)	R2(K Ω)	R3(K Ω)	Vref(V)
3.3	4.801	2.87	15	1.24
5	2.894	2.87	10	2.5
12	11.000	2.87	17.4	2.5
15	14.494	2.87	17.4	2.5
24	24.872	2.87	20	2.5


It is not allowed to connect modules output in parallel to enlarge the power.

Mechanical dimensions and footprint



Note: Unit: mm[inch]

Pin diameter tolerances: ±0.10[±0.004] General tolerances: ±0.50[±0.020]



 Pin-Out

 Pin
 Function

 1
 Ctrl

 2
 GND


 3
 Vin

 4
 +Vo

 5
 Trim


 6
 0V

Mechanical dimensions with heatsink



Unit: mm[inch]


Pin diameter tolerances: ±0.10[±0.004] General tolerances: ±0.50[±0.020]




Note:Grid 2.54*2.54mm

Pin-Out			
Pin	Function		
1	Ctrl		
2	GND		
3	Vin		
4	+Vo		
5	Trim		
6	0V		

Wiring mounting





Pin-Out						
Pin	1	2	3	4	5	6
Function	Ctrl	GND	Vin	+Vo	Trim	οv

THIRD ANGLE PROJECTION (


Note: Unit: mm[inch]

Wire range: 24-12 AWG

Tightening torque: Max 0.4 N·m General tolerances: ±1.00[±0.039]

Wiring mounting with heatsink






		Pin-	Out			
Pin	1	2	3	4	5	6
Function	Ctrl	GND	Vin	+Vo	Trim	0V

Note: Unit: mm[inch] Wire range: 24-12 AWG


Tightening torque: Max 0.4 N·m General tolerances: ±1.00[±0.039]

Rail mounting





		Pin-	Out			
Pin	1	2	3	4	5	6
Function	Ctrl	GND	Vin	+Vo	Trim	0V



Wire range: 24-12 AWG Tightening torque: Max 0.4 N·m

Mounting rail: TS35


Unit: mm[inch]

Note:


General tolerances: ±1.00[±0.039]

Rail mounting with heatsink





		Pin-	Out		9	
Pin	1	2	3	4	5	6
Function	Ctrl	GND	Vin	+Vo	Trim	0V



Note: Unit: mm[inch] Wire range: 24-12 AWG Tightening torque: Max 0.4 N·m General tolerances: ±1.00[±0.039]

Note:

- The maximum capacitive loads offered were tested at input voltage range and full load.
- Only typical model listed. Non-standard models will be different from the above, please contact us for more details.
- 3. All specifications are measured at TA=25°C, humidity<75%, nominal input voltage and rated output load unless otherwise specified.
- 4. In this datasheet, all the test methods of indications are based on corporate standards.
- 5. We can provide product customization service, please contact our technicians directly for specific information.
- 6. Our products shall be classified according to ISO14001 and related environmental laws and regulations, and shall be handled by qualified units.