## SIEMENS

## Data sheet

## US2:17DUA82WE



Non-reversing motor starter, Size 1, Three phase full voltage, Solid-state overload relay, OLR amp range 0.25-1A, Combination type, 30A non-fusible disconnect, Encl NEMA type 4X 304 S-Steel, Water/dust tight noncorrosive, Extra-wide enclosure

Fi	g	ur	e	si	m	il	ar

product brand name	Class 17 & 25				
design of the product	Full-voltage non-reversing motor starter with non-fusible disconnect				
special product feature	ESP200 overload relay				
General technical data					
Height x Width x Depth [in]	24 × 20 × 8 in				
touch protection against electrical shock	(NA for enclosed products)				
installation altitude [ft] at height above sea level maximum	6560 ft				
ambient temperature [°F]					
<ul> <li>during storage</li> </ul>	-22 +149 °F				
during operation	-4 +104 °F				
ambient temperature					
<ul> <li>during storage</li> </ul>	-30 +65 °C				
<ul> <li>during operation</li> </ul>	-20 +40 °C				
Horsepower ratings					
yielded mechanical performance [hp] for 3-phase AC motor					
• at 200/208 V rated value	0.17 hp				
<ul> <li>at 220/230 V rated value</li> </ul>	0.17 hp				
<ul> <li>at 460/480 V rated value</li> </ul>	0.33 hp				
<ul> <li>at 575/600 V rated value</li> </ul>	0.5 hp				
Contactor					
size of contactor	NEMA controller size 1				
number of NO contacts for main contacts	3				
operational current at AC at 600 V rated value	27 A				
mechanical service life (switching cycles) of the main contacts typical	1000000				
Auxiliary contact					
number of NC contacts at contactor for auxiliary contacts	0				
number of NO contacts at contactor for auxiliary contacts	1				
number of total auxiliary contacts maximum	8				
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)				
Coil					
type of voltage of the control supply voltage	AC				
control supply voltage					
• at AC at 50 Hz rated value	550 V				
• at AC at 60 Hz rated value	575 600 V				
holding power at AC minimum	8.6 W				
apparent pick-up power of magnet coil at AC	218 VA				

annerent halding names of second a 11 / 40	25.1/4
apparent holding power of magnet coil at AC	25 VA
operating range factor control supply voltage rated value of magnet coil	0.85 1.1
percental drop-out voltage of magnet coil related to the input voltage	50 %
ON-delay time	19 29 ms
OFF-delay time	10 24 ms
Overload relay	
product function	
<ul> <li>overload protection</li> </ul>	Yes
<ul> <li>phase failure detection</li> </ul>	Yes
<ul> <li>asymmetry detection</li> </ul>	Yes
<ul> <li>ground fault detection</li> </ul>	Yes
test function	Yes
external reset	Yes
reset function	Manual, automatic and remote
trip class	CLASS 5 / 10 / 20 (factory set) / 30
adjustable current response value current of the current- dependent overload release	0.25 1 A
make time with automatic start after power failure maximum	3 s
relative repeat accuracy	1 %
product feature protective coating on printed-circuit board	Yes
number of NC contacts of auxiliary contacts of overload relay	1
number of NO contacts of auxiliary contacts of overload relay	1
operational current of auxiliary contacts of overload relay	
• at AC at 600 V	5 A
● at DC at 250 V	1 A
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)
insulation voltage (Ui)	
<ul> <li>with single-phase operation at AC rated value</li> </ul>	600 V
<ul> <li>with multi-phase operation at AC rated value</li> </ul>	300 V
Disconnect Switch	
response value of switch disconnector	30A / 600V
design of fuse holder	non-fusible
operating class of the fuse link	non-fusible
Enclosure	
degree of protection NEMA rating	4X, 304 stainless steel
design of the housing	Extra-wide
design of the housing	dustproof, waterproof & resistant to corrosion
Mounting/wiring	
mounting position	vertical
fastening method	Surface mounting and installation
type of electrical connection for supply voltage line-side	Box lug
tightening torque [lbf·in] for supply	35 35 lbf·in
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (14 2 AWG)
temperature of the conductor for supply maximum permissible	75 °C
material of the conductor for supply	AL or CU
type of electrical connection for load-side outgoing feeder	Screw-type terminals
tightening torque [lbf·in] for load-side outgoing feeder	20 24 lbf·in
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	2x (14 10 AWG)
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C
material of the conductor for load-side outgoing feeder	CU
type of electrical connection of magnet coil	Screw-type terminals

tightening torque [lbf·in] at magnet coil	5 12 lbf·in			
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)			
temperature of the conductor at magnet coil maximum permissible	75 °C			
material of the conductor at magnet coil	CU			
type of electrical connection for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in			
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)			
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C			
material of the conductor at contactor for auxiliary contacts	CU			
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)			
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C			
material of the conductor at overload relay for auxiliary contacts	CU			
Short-circuit current rating				
design of the fuse link for short-circuit protection of the main circuit required	10kA@600V (Class H or K); 100kA@600V (Class R or J)			
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14			
Further information				
Industrial Controls - Product Overview (Catalogs, Brochures,) www.usa.siemens.com/iccatalog Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:17DUA82WE Service&Support (Manuals, Certificates, Characteristics, FAQs,)				
https://support.industry.siemens.com/cs/US/en/ps/US2:17DUA82WE Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:17DUA82WE⟨=en				
Certificates/approvals				

Certificates/approvals https://support.industry.siemens.com/cs/US/en/ps/US2:17DUA82WE/certificate

last modified:

1/25/2022 🖸