SIEMENS

Data sheet

US2:17DUA82BA10



Non-reversing motor starter, Size 1, Three phase full voltage, Solid-state overload relay, OLR amp range 0.25-1A, Combination type, 30A fusible disconnect, 30A/250V fuse clip, Enclosure NEMA type 1, Indoor general purpose use, Extra-wide enclosure

Fi	g	ur	e	si	m	il	ar

product brand name	Class 17			
design of the product	Non-reversing motor starter with fusible disconnect			
special product feature	ESP200 overload relay; Dual voltage coil			
General technical data				
weight [lb]	47 lb			
Height x Width x Depth [in]	24 × 20 × 8 in			
touch protection against electrical shock	NA for enclosed products			
installation altitude [ft] at height above sea level maximum	6560 ft			
ambient temperature [°F]				
 during storage 	-22 +149 °F			
during operation	-4 +104 °F			
ambient temperature				
 during storage 	-30 +65 °C			
 during operation 	-20 +40 °C			
country of origin	USA			
Horsepower ratings				
yielded mechanical performance [hp] for 3-phase AC motor				
• at 200/208 V rated value	0.17 hp			
 at 220/230 V rated value 	0.17 hp			
 at 460/480 V rated value 	0 hp			
 at 575/600 V rated value 	0 hp			
Contactor				
size of contactor	NEMA controller size 1			
number of NO contacts for main contacts	3			
operating voltage for main current circuit at AC at 60 Hz maximum	600 V			
operational current at AC at 600 V rated value	27 A			
mechanical service life (switching cycles) of the main contacts typical	1000000			
Auxiliary contact				
number of NC contacts at contactor for auxiliary contacts	0			
number of NO contacts at contactor for auxiliary contacts	1			
number of total auxiliary contacts maximum	8			
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)			
Coil				
type of voltage of the control supply voltage	AC			
control supply voltage				

a at A.C. at CO.L.L. rated value	110 240.1/				
at AC at 60 Hz rated value	110 240 V				
holding power at AC minimum	8.6 W				
apparent pick-up power of magnet coil at AC	218 VA				
apparent holding power of magnet coil at AC	25 VA				
operating range factor control supply voltage rated value of magnet coil	0.85 1.1				
percental drop-out voltage of magnet coil related to the input voltage	50 %				
ON-delay time	19 29 ms				
OFF-delay time	10 24 ms				
Overload relay					
product function					
 overload protection 	Yes				
 phase failure detection 	Yes				
 asymmetry detection 	Yes				
ground fault detection	Yes				
test function	Yes				
external reset	Yes				
reset function	Manual, automatic and remote				
trip class	CLASS 5 / 10 / 20 (factory set) / 30				
adjustable current response value current of the current-	0.25 1 A				
dependent overload release					
tripping time at phase-loss maximum	3 s				
relative repeat accuracy	1 %				
product feature protective coating on printed-circuit board	Yes				
number of NC contacts of auxiliary contacts of overload relay	1				
number of NO contacts of auxiliary contacts of overload relay	1				
operational current of auxiliary contacts of overload relay					
• at AC at 600 V	5 A				
• at DC at 250 V	1 A				
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)				
insulation voltage (Ui)					
 with single-phase operation at AC rated value 	600 V				
 with multi-phase operation at AC rated value 	300 V				
Disconnect Switch					
response value of switch disconnector	30A / 250V				
design of fuse holder	Class R fuse clips				
operating class of the fuse link	Class R				
Enclosure					
degree of protection NEMA rating	1				
design of the housing	indoors, usable on a general basis				
5 5	indeere, deable on a general basis				
Mounting/wiring	vartical				
mounting position	vertical				
fastening method	Surface mounting and installation				
type of electrical connection for supply voltage line-side	Box lug				
tightening torque [lbf·in] for supply	35 35 lbf·in				
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (14 2 AWG)				
temperature of the conductor for supply maximum permissible	75 °C				
material of the conductor for supply	AL or CU				
type of electrical connection for load-side outgoing feeder	Screw-type terminals				
tightening torque [lbf·in] for load-side outgoing feeder	20 24 lbf·in				
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	2x (14 10 AWG)				
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C				
material of the conductor for load-side outgoing feeder	CU				

type of electrical connection of magnet coil	Screw-type terminals			
tightening torque [lbf·in] at magnet coil	5 12 lbf·in			
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)			
temperature of the conductor at magnet coil maximum permissible	75 °C			
material of the conductor at magnet coil	CU			
type of electrical connection for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in			
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)			
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C			
material of the conductor at contactor for auxiliary contacts	CU			
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)			
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C			
material of the conductor at overload relay for auxiliary contacts	CU			
Short-circuit current rating				
design of the fuse link for short-circuit protection of the main circuit required	10kA@600V (Class H or K); 100kA@600V (Class R or J)			
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14			
Further information				
Industrial Controls - Product Overview (Catalogs, Brochures,) www.usa.siemens.com/iccatalog Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:17DUA82BA10				
Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/US/en/ps/US2:17DUA82BA10				
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:17DUA82BA10⟨=en				

Certificates/approvals https://support.industry.siemens.com/cs/US/en/ps/US2:17DUA82BA10/certificate

last modified:

1/25/2022 🖸