## SIEMENS

## Data sheet

## US2:17HUG92BA15



Non-reversing motor starter, Size 3, Three phase full voltage, Solid-state overload relay, OLR amp range 25-100A, Combination type, 100A fusible disconnect, 100A/600V fuse clip, Enclosure NEMA type 1, Indoor general purpose use, Standard width enclosure

Fi	a	ur	e	si	m	ii.	ar
	3	~	~	~.			

product brand name	Class 17		
design of the product	Non-reversing motor starter with fusible disconnect		
special product feature	ESP200 overload relay; Dual voltage coil		
General technical data			
weight [lb]	52 lb		
Height x Width x Depth [in]	24 × 20 × 8 in		
touch protection against electrical shock	NA for enclosed products		
installation altitude [ft] at height above sea level maximum	6560 ft		
ambient temperature [°F]			
during storage	-22 +149 °F		
during operation	-4 +104 °F		
ambient temperature			
during storage	-30 +65 °C		
during operation	-20 +40 °C		
country of origin	USA		
Horsepower ratings			
yielded mechanical performance [hp] for 3-phase AC motor			
• at 200/208 V rated value	0 hp		
<ul> <li>at 220/230 V rated value</li> </ul>	0 hp		
<ul> <li>at 460/480 V rated value</li> </ul>	50 hp		
<ul> <li>at 575/600 V rated value</li> </ul>	50 hp		
Contactor			
size of contactor	NEMA controller size 3		
number of NO contacts for main contacts	3		
operating voltage for main current circuit at AC at 60 Hz maximum	600 V		
operational current at AC at 600 V rated value	90 A		
mechanical service life (switching cycles) of the main contacts typical	500000		
Auxiliary contact			
number of NC contacts at contactor for auxiliary contacts	0		
number of NO contacts at contactor for auxiliary contacts	1		
number of total auxiliary contacts maximum	7		
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)		
Coil			
type of voltage of the control supply voltage	AC		
control supply voltage			

• at AC at 60 Hz rated value         110 240 V           holding power at AC minimum         14 W           apparent pick-up power of magnet coil at AC         310 VA           apparent holding power of magnet coil at AC         26 VA           operating range factor control supply voltage rated value         0.85 1.1	
apparent pick-up power of magnet coil at AC       310 VA         apparent holding power of magnet coil at AC       26 VA	
apparent holding power of magnet coil at AC 26 VA	
of magnet coil	
percental drop-out voltage of magnet coil related to the 50 %	
ON-delay time 26 41 ms	
OFF-delay time 14 19 ms	
Overload relay	
product function	
overload protection     Yes	
phase failure detection     Yes	
asymmetry detection Yes	
ground fault detection     Yes	
test function     Yes	
external reset     Yes	
reset function Manual, automatic and remote	
trip class CLASS 5 / 10 / 20 (factory set) / 30	
adjustable current response value current of the current- dependent overload release 25 100 A	
tripping time at phase-loss maximum 3 s	
relative repeat accuracy 1 %	
product feature protective coating on printed-circuit board Yes	
number of NC contacts of auxiliary contacts of overload 1 relay	
number of NO contacts of auxiliary contacts of overload 1 relay	
operational current of auxiliary contacts of overload relay	
• at AC at 600 V 5 A	
• at DC at 250 V 1 A	
contact rating of auxiliary contacts of overload relay according to UL 5A@600VAC (B600), 1A@250VDC (R300)	
insulation voltage (Ui)	
with single-phase operation at AC rated value     600 V	
with multi-phase operation at AC rated value     300 V	
Disconnect Switch	
response value of switch disconnector 100A / 600V	
design of fuse holder Class R fuse clips	
operating class of the fuse link Class R	
Enclosure	
degree of protection NEMA rating 1	
design of the housing indoors, usable on a general basis	
Mounting/wiring	
mounting position vertical	
fastening method Surface mounting and installation	
type of electrical connection for supply voltage line-side     Box lug       tightening torgue [lbf·in] for supply     120 120 lbf·in	
type of connectable conductor cross-sections at line-side 1x (14 1/0 AWG)	
at AWG cables single or multi-stranded       temperature of the conductor for supply maximum       permissible	
material of the conductor for supply	
material of the conductor for supply     AL or CU       type of electrical connection for load-side outgoing feeder     Box lug	
type of electrical connection for load-side outgoing feeder Box lug	
type of electrical connection for load-side outgoing feederBox lugtightening torque [lbf·in] for load-side outgoing feeder120 120 lbf·in	
type of electrical connection for load-side outgoing feeder Box lug	
type of electrical connection for load-side outgoing feederBox lugtightening torque [lbf·in] for load-side outgoing feeder120 120 lbf·intype of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi-1x (14 2/0 AWG)	

type of electrical connection of magnet coil	Screw-type terminals			
	Screw-type terminals 5 12 lbf-in			
tightening torque [lbf·in] at magnet coil				
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2x (16 12 AWG)			
temperature of the conductor at magnet coil maximum permissible	75 °C			
material of the conductor at magnet coil	CU			
type of electrical connection for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in			
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)			
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C			
material of the conductor at contactor for auxiliary contacts	CU			
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals			
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in			
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)			
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C			
material of the conductor at overload relay for auxiliary contacts	CU			
Short-circuit current rating				
design of the fuse link for short-circuit protection of the main circuit required	10kA@600V (Class H or K); 100kA@600V (Class R or J)			
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14			
Further information				
Industrial Controls - Product Overview (Catalogs, Brochu www.usa.siemens.com/iccatalog Industry Mall (Online ordering system)				
https://mall.industry.siemens.com/mall/en/us/Catalog/product	<u>t?mlfb=US2:17HUG92BA15</u>			


nup siemens JIII/IIIai <u>15</u>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/US/en/ps/US2:17HUG92BA15

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=US2:17HUG92BA15&lang=en Certificates/approvals

https://support.industry.siemens.com/cs/US/en/ps/US2:17HUG92BA15/certificate



D68782001

last modified:

1/25/2022 🖸