## SIEMENS

## Data sheet

## US2:26DUD92NF



Reversing motor starter, Size 1, Three phase full voltage, Solid-state overload relay, OLR amp range 5.5-22A, 110V 50Hz / 120V 60Hz coil, Combination type, 25A circuit breaker, Enclosure NEMA type 4/12, Water/dust tight for outdoors

Figur	esi	milar	

product brand name	Class 18 & 26	
design of the product	Full-voltage reversing motor starter with motor circuit protector	
special product feature	ESP200 overload relay	
General technical data		
Height x Width x Depth [in]	24 × 20 × 8 in	
touch protection against electrical shock	NA for enclosed products	
installation altitude [ft] at height above sea level maximum	6560 ft	
ambient temperature [°F]		
<ul> <li>during storage</li> </ul>	-22 +149 °F	
during operation	-4 +104 °F	
ambient temperature		
<ul> <li>during storage</li> </ul>	-30 +65 °C	
during operation	-20 +40 °C	
Horsepower ratings		
yielded mechanical performance [hp] for 3-phase AC motor		
• at 200/208 V rated value	3 hp	
<ul> <li>at 220/230 V rated value</li> </ul>	3 hp	
<ul> <li>at 460/480 V rated value</li> </ul>	7.5 hp	
<ul> <li>at 575/600 V rated value</li> </ul>	10 hp	
Contactor		
size of contactor	NEMA controller size 1	
number of NO contacts for main contacts	3	
operating voltage for main current circuit at AC at 60 Hz maximum	600 V	
operational current at AC at 600 V rated value	27 A	
mechanical service life (switching cycles) of the main contacts typical	1000000	
Auxiliary contact		
number of NC contacts at contactor for auxiliary contacts	2	
number of NO contacts at contactor for auxiliary contacts	2	
number of total auxiliary contacts maximum	8	
contact rating of auxiliary contacts of contactor according to UL	10A@600VAC (A600), 5A@600VDC (P600)	
Coil		
type of voltage of the control supply voltage	AC	
control supply voltage		
<ul> <li>at AC at 50 Hz rated value</li> </ul>	110 V	
• at AC at 60 Hz rated value	120 V	

holding power at AC minimum	8.6 W
apparent pick-up power of magnet coil at AC	218 VA
apparent holding power of magnet coil at AC	25 VA
operating range factor control supply voltage rated value of magnet coil	0.85 1.1
percental drop-out voltage of magnet coil related to the input voltage	50 %
ON-delay time	19 29 ms
OFF-delay time	10 24 ms
Overload relay	
product function	
<ul> <li>overload protection</li> </ul>	Yes
<ul> <li>phase failure detection</li> </ul>	Yes
<ul> <li>asymmetry detection</li> </ul>	Yes
<ul> <li>ground fault detection</li> </ul>	Yes
test function	Yes
external reset	Yes
reset function	Manual, automatic and remote
trip class	CLASS 5 / 10 / 20 (factory set) / 30
adjustable current response value current of the current- dependent overload release	5.5 22 A
make time with automatic start after power failure maximum	3 s
relative repeat accuracy	1 %
product feature protective coating on printed-circuit board	Yes
number of NC contacts of auxiliary contacts of overload relay	1
number of NO contacts of auxiliary contacts of overload relay	1
operational current of auxiliary contacts of overload relay	
• at AC at 600 V	5 A
• at DC at 250 V	
contact rating of auxiliary contacts of overload relay according to UL	5A@600VAC (B600), 1A@250VDC (R300)
insulation voltage (Ui)	600.1/
<ul> <li>with single-phase operation at AC rated value</li> <li>with multi-phase operation at AC rated value</li> </ul>	600 V 300 V
Enclosure	300 V
	4.40
degree of protection NEMA rating design of the housing	4, 12 dustproof, waterproof & weatherproof
5 5	dustproof, waterproof & weatherproof
Circuit Breaker	Motor circuit protector (magnetic trip only)
type of the motor protection	Motor circuit protector (magnetic trip only) 25 A
operational current of motor circuit breaker rated value adjustable current response value current of	25 A 55 180 A
instantaneous short-circuit trip unit	
Mounting/wiring	
mounting position	Vertical
fastening method	Surface mounting and installation
type of electrical connection for supply voltage line-side	Box lug
type of connectable conductor cross-sections at line-side at AWG cables single or multi-stranded	1x (14 AWG 10 AWG) or 1x (12 AWG 10 AWG)
temperature of the conductor for supply maximum permissible	75 °C
material of the conductor for supply	AL or CU
type of electrical connection for load-side outgoing feeder	Screw-type terminals
tightening torque [lbf·in] for load-side outgoing feeder	35 35 lbf·in
type of connectable conductor cross-sections at AWG cables for load-side outgoing feeder single or multi- stranded	1x (14 2 AWG)
temperature of the conductor for load-side outgoing feeder maximum permissible	75 °C
material of the conductor for load-side outgoing feeder	AL or CU
type of electrical connection of magnet coil	Screw-type terminals

tightening torque [[hf.in] at magnet coil	5 12 lbf·in	
tightening torque [lbf·in] at magnet coil	2x (16 12 AWG)	
type of connectable conductor cross-sections of magnet coil at AWG cables single or multi-stranded	2X (16 12 AWG)	
temperature of the conductor at magnet coil maximum permissible	75 °C	
material of the conductor at magnet coil	CU	
type of electrical connection for auxiliary contacts	Screw-type terminals	
tightening torque [lbf·in] at contactor for auxiliary contacts	10 15 lbf·in	
type of connectable conductor cross-sections at contactor at AWG cables for auxiliary contacts single or multi- stranded	1x (12 AWG), 2x (16 14 AWG), 2x (18 16 AWG)	
temperature of the conductor at contactor for auxiliary contacts maximum permissible	75 °C	
material of the conductor at contactor for auxiliary contacts	CU	
type of electrical connection at overload relay for auxiliary contacts	Screw-type terminals	
tightening torque [lbf·in] at overload relay for auxiliary contacts	7 10 lbf·in	
type of connectable conductor cross-sections at overload relay at AWG cables for auxiliary contacts single or multi- stranded	2x (20 14 AWG)	
temperature of the conductor at overload relay for auxiliary contacts maximum permissible	75 °C	
material of the conductor at overload relay for auxiliary contacts	CU	
Short-circuit current rating		
design of the short-circuit trip	Instantaneous trip circuit breaker	
breaking capacity maximum short-circuit current (Icu)		
• at 240 V	100 kA	
• at 480 V	100 kA	
• at 600 V	25 kA	
certificate of suitability	NEMA ICS 2; UL 508; CSA 22.2, No.14	
Further information		
Industrial Controls - Product Overview (Catalogs, Brochures,) www.usa.siemens.com/iccatalog Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:26DUD92NF Service&Support (Manuals, Certificates, Characteristics, FAQs,) https://support.industry.siemens.com/cs/US/en/ps/US2:26DUD92NF		
Inttps://support.industry.siemens.com/cs/US/en/ps/US2:26DUD92NF Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros,) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=US2:26DUD92NF⟨=en Certificates/approvals https://support.industry.siemens.com/cs/US/en/ps/US2:26DUD92NF/certificate		

last modified:

1/25/2022 🖸