


General Description

These dual N Channel enhancement mode power fieldeffect transistors are using trench DMOS technology. This advanced technology has been especially tailored to minimize on-state resistance, provide superior switching performance, and withstand high energypulse in the avalanche and commutation mode. These devices are well suited for high efficiency fast switchingapplications.

BVDSS	RDS(ON)	ID
20V	22mΩ	6.5A

DFN2X2 Dual 2EP Pin Configuration



Features

- Fast switching
- Green Device Available
- Suit for 1.8V Gate Drive Applications
- Marking : WA

Applications

- Notebook
- Load Switch
- Networking
- Hand-held Instruments

Absolute Maximum Ratings $T_c=25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	20	V
V_{GS}	Gate-Source Voltage	± 12	V
I_D	Drain Current - Continuous ($T_c=25^\circ\text{C}$)	6.5	A
	Drain Current - Continuous ($T_c=100^\circ\text{C}$)	4.3	A
I_{DM}	Drain Current - Pulsed	20.8	A
P_D	Power Dissipation ($T_c=25^\circ\text{C}$)	1.78	W
	Power Dissipation - Derate above 25°C	0.02	W/ $^\circ\text{C}$
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 150	$^\circ\text{C}$

Thermal Characteristics

Symbol	Parameter	Typ.	Max.	Unit
$R_{\theta JA}$	Thermal Resistance Junction to Ambient		100	$^\circ\text{C}/\text{W}$

Electrical Characteristics ($T_J=25^\circ\text{C}$, unless otherwise noted)
Off Characteristics

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D=250\mu\text{A}$	20			V
$\frac{\partial B}{\partial T} V_{DSS}$	BV_{DSS} Temperature Coefficient	Reference to $25^\circ\text{C}, I_D=1\text{mA}$		0.02		$\text{V}/^\circ\text{C}$
I_{DSS}	Drain-Source Leakage Current	$V_{DS}=20\text{V}, V_{GS}=0\text{V}, T_J=25^\circ\text{C}$			1	μA
		$V_{DS}=16\text{V}, V_{GS}=0\text{V}, T_J=125^\circ\text{C}$			10	μA
I_{GSS}	Gate-Source Leakage Current	$V_{GS}=\pm 10\text{V}, V_{DS}=0\text{V}$			± 100	nA

On Characteristics

$R_{DS(\text{ON})}$	Static Drain-Source On-Resistance	$V_{GS}=4.5\text{V}, I_D=3\text{A}$		22	25	$\text{m}\Omega$
		$V_{GS}=2.5\text{V}, I_D=2\text{A}$		26	30	$\text{m}\Omega$
		$V_{GS}=1.8\text{V}, I_D=1.5\text{A}$		40	45	$\text{m}\Omega$
$V_{GS(\text{th})}$	Gate Threshold Voltage	$V_{GS}=V_{DS}, I_D=250\mu\text{A}$	0.3	0.6	1	V
				-2		$\text{mV}/^\circ\text{C}$
g_f	Forward Transconductance	$V_{DS}=10\text{V}, I_D=2\text{A}$		4.4		S

Dynamic and switching Characteristics

Q_g	Total Gate Charge _{2,3}	$V_{DS}=10\text{V}, V_{GS}=4.5\text{V}, I_D=3\text{A}$		5.8	10	nC
Q_{gs}	Gate-Source Charge _{2,3}			0.6	1.5	
Q_{gd}	Gate-Drain Charge _{2,3}			1.5	3	
$T_{d(on)}$	Turn-On Delay Time _{2,3}	$V_{DD}=10\text{V}, V_{GS}=4.5\text{V}, R_G=25\text{ }\Omega, I_D=1\text{A}$	---	2.9	6	ns
T_r	Rise Time _{2,3}			8.4	16	
$T_{d(off)}$	Turn-Off Delay Time _{2,3}			19.2	38	
T_f	Fall Time _{2,3}			5.6	12	
C_{iss}	Input Capacitance			315	600	pF
C_{oss}	Output Capacitance	$V_{DS}=15\text{V}, V_{GS}=0\text{V}, F=1\text{MHz}$	---	50	80	
C_{rss}	Reverse Transfer Capacitance			40	60	


Drain-Source Diode Characteristics and Maximum Ratings

Symbol	Parameter	Conditions	Min.	Typ.	Max.	Unit
I_s	Continuous Source Current	$V_G=V_D=0\text{V}$, Force Current			3.8	A
					7.6	A
I_{SM}	Pulsed Source Current					
V_{SD}	Diode Forward Voltage	$V_{GS}=0\text{V}, I_s=1\text{A}, T_J=25^\circ\text{C}$			1	V

Note :

1. Repetitive Rating : Pulsed width limited by maximum junction temperature.
2. The data tested by pulsed , pulse width $\leq 300\mu\text{s}$, duty cycle $\leq 2\%$.
3. Essentially independent of operating temperature.


I_D, Continuous Drain Current(A)



T_C , Case Temperature (°C)

Fig.1 Continuous Drain Current vs. T_C


Normalized Gate Threshold Voltage(V)



T_J , Junction Temperature (°C)

Fig.3 Normalized V_{th} vs. T_J


Normalized Thermal Response(R_θ JA)



Square Wave Pulse Duration (s)

Fig.5 Normalized Transient Impedance


No rmalizedOnResistance(m)



T_J , Junction Temperature (°C)

Fig.2 Normalized RDSON vs. T_J


V_{G_S}, Gate to Source Voltage(V)



Q_G , Gate Charge (nC)

Fig.4 Gate Charge Waveform

I_D, Continuous Drain Current(A)



10us 100us 1ms 10ms 100ms DC

Fig.6 Maximum Safe Operation Area




Fig.7 Switching Time Waveform






Fig.8 EAS Waveform


PPAK2X2 Dual 2EP PACKAGE INFORMATION



BOTTOM VIEW



TOP VIEW



SIDE VIEW

COMMON DIMENSIONS
(UNITS OF MEASURE=MILLIMETER)

SYMBOL	MIN	TYP	MAX
A	0.70	0.75	0.80
A1	0.00	0.02	0.05
A2			0.203
b	0.20	0.25	0.30
D	1.95	2.00	2.05
D1	0.50	0.55	0.60
E	1.95	2.00	2.05
E1	0.85	0.90	0.95
e			0.65BSC
L	0.27	0.32	0.37
J	0.40BSC		
K	0.20MIN		
N	6		
aaa	0.08		
bbb	0.10		