

FEATURES

Complementary Pair.

One 3904-Type NPN.

One 3906-Type PNP.

Epitaxial Planar Die Construction.


Ideal for Low Power Amplification and Switching.

Package Marking and Ordering Information

Product ID	Pack	Marking	Qty(PCS)
MMDT3946	SOT-363	K46	3000



Pin 1 SOT-363



MAXIMUM RATINGS (Ta=25 unless otherwise noted)

Pin 1

Symbol	Parameter	Value	Unit
V _{CBO}	Collector-Base Voltage	60	V
V _{CEO}	Collector-Emitter Voltage	40	V
V _{EBO}	Emitter-Base Voltage	5	V
Ic	Collector Current	200	mA
Pc	Collector Power Dissipation	200	mW
R⊝JA	Thermal Resistance From Junction To Ambient	625	°C/W
T _J ,T _{stg}	Operation Junction And Storage Temperature Range	-55~+150	$^{\circ}$

NPN 3904 ELECTRICAL CHARACTERISTICS(Ta=25 unless otherwise noted)

Symbol	Parameter	Test conditions M		Тур	Max	Unit
V _{(BR)CBO}	Collector-base breakdown voltage	I _C =10μA, I _E =0 60				V
V _{(BR)CEO}	Collector-emitter breakdown voltage	I _C =1mA, I _B =0	40			\ \
V _{(BR)EBO}	Emitter-base breakdown voltage	I _E =10μΑ, I _C =0	5			V
I _{CEO}	Collector cut-off current	V _{CE} =30V, I _B =0			50	nA
I _{CBO}	Collector cut-off current	V _{CB} =30V, I _E =0			50	nA
I _{EBO}	Emitter cut-off current	V _{EB} =5V, I _C =0			50	nA
h _{FE} (1)	DC current gain(1)	V _{CE} =1V, I _C =100μA	40			
h _{FE} (2)	DC current gain(2)	V _{CE} =1V, I _C =1mA	70			
h _{FE} (3)	DC current gain(3)	V _{CE} =1V, I _C =10mA	100		300	
h _{FE} (4)	DC current gain(4)	V _{CE} =1V, I _C =50mA	60			
h _{FE} (5)	DC current gain(5)	V _{CE} =1V, I _C =100mA	30			
N/	Callector amitter est mation valtage	I _C =10mA, I _B =1mA			0.2	\ \
V _{CE(sat)}	Collector-emitter saturation voltage	I _C =50mA, I _B =5mA			0.3	V
.,	D	I _C =10mA, I _B =1mA	0.65		0.85	V
V _{BE(sat)}	Base-emitter saturation voltage	I _C =50mA, I _B =5mA			0.95	V
f⊤	Transition frequency	V _{CE} =20V, I _C =10mA, f=100MHz	300			MHz
Cob	Collector output capacitance	V _{CB} =5V, I _E =0, f=1MHz			4	pF
NF	Noise figure	V_{CE} =5V,Ic=0.1mA,f=1kHz,Rg=1K Ω			5	dB
t _d	Delay time	V _{CC} =3V, V _{BE(off)} =0.5V,			35	ns
t _r	Rise time	I _C =10mA, I _{B1} =I _{B2} =1mA			35	ns
ts	Storage time	V _{CC} =3V, I _C =10mA,			225	ns
t _f	Fall time	I _{B1} =I _{B2} =1mA			75	ns



MAXIMUM RATINGS (Ta=25 unless otherwise noted)

Symbol	Parameter	Value	Unit
V _{CBO}	Collector-Base Voltage	-40	V
V _{CEO}	Collector-Emitter Voltage	-40	V
V _{EBO}	Emitter-Base Voltage	-5	V
Ic	Collector Current	-200	mA
Pc	Collector Power Dissipation	200	mW
R⊝JA	Thermal Resistance From Junction To Ambient	625	°C/W
T _J ,T _{stg}	Operation Junction And Storage Temperature Range	-55∼+150	${\mathbb C}$


PNP 3906 ELECTRICAL CHARACTERISTICS(Ta=25 unless otherwise noted)


W 3300 ELECTRICAL CHARACTERIOTICO (Tu-20 unicas otherwise noted)						
Symbol	Parameter	Test conditions	Min	Тур	Max	Unit
V _{(BR)CBO} *	Collector-base breakdown voltage	I _C =-10μA, I _E =0	-40			V
V _{(BR)CEO} *	Collector-emitter breakdown voltage	I _C =-1mA, I _B =0	-40			V
$V_{(BR)EBO}{}^{\star}$	Emitter-base breakdown voltage	I _E =-10μΑ, I _C =0	-5	-5		V
I _{CEX} *	Collector cut-off current	V _{CE} =-30V, V _{EB(off)} =-3V			-50	nA
I _{CBO}	Collector cut-off current	V _{CB} =-30V, I _E =0			-50	nA
I _{EBO}	Base cut-off current	V _{EB} =-5V,I _E =0			-50	nA
h _{FE} (1)*	DC current gain(1)	V _{CE} =-1V, I _C =-100 μ A	60			
h _{FE} (2)*	DC current gain(2)	V _{CE} =-1V, I _C =-1mA	80			
h _{FE} (3)*	DC current gain(3)	V _{CE} =-1V, I _C =-10mA	100		300	
h _{FE} (4)*	DC current gain(4)	V _{CE} =-1V, I _C =-50mA	60			
h _{FE} (5)*	DC current gain(5)	V _{CE} =-1V, I _C =-100mA	30			
V _{CE(sat)} *	Collector-emitter saturation voltage	Ic=-10mA, I _B =-1mA			-0.25	V
		I _C =-50mA, I _B =-5mA			-0.4	V
., .	Base-emitter saturation voltage	I _C =-10mA, I _B =-1mA	-0.65		-0.85	V
$V_{BE(sat)}^*$		I _C =-50mA, I _B =-5mA			-0.95	V
f⊤	Transition frequency	V _{CE} =-20V, I _C =-10mA, f=100MHz	250			MHz
Cob	Collector output capacitance	V _{CB} =-5V, I _E =0, f=1MHz			4.5	pF
NF	Noise figure	VCE=-5V,lc=-0.1mA,f=1kHz,Rg=1KΩ	2		4	dB
t _d	Delay time	V _{CC} =-3V, V _{BE(off)} =-0.5V,			35	ns
t _r	Rise time	I _C =-10mA, I _{B1} =I _{B2} =-1mA			35	ns
t _s	Storage time	V _{CC} =-3V, I _C =-10mA,			225	ns
t _f	Fall time	I _{B1} =I _{B2} =-1mA			75	ns


^{*}Pulse test: pulse width ≤300µs, duty cycle≤ 2.0%.



SOT-363 Package Outline Dimensions








Symbol	Dimensions In Millimeters		Dimensions In Inches		
Syllibol	Min	Max	Min	Max	
Α	0.900	1.100	0.035	0.043	
A1	0.000	0.100	0.000	0.004	
A2	0.900	1.000	0.035	0.039	
р	0.150	0.350	0.006	0.014	
С	0.100	0.150	0.004	0.006	
D	2.000	2.200	0.079	0.087	
Е	1.150	1.350	0.045	0.053	
E1	2.150	2.400	0.085	0.094	
е	0.650 TYP		0.026 TYP		
e1	1.200	1.400	0.047	0.055	
L	0.525 REF		0.021 REF		
L1	0.260	0.460	0.010	0.018	
θ	0°	8°	0°	8°	

SOT-363 Suggested Pad Layout



Note:

- 1.Controlling dimension:in millimeters.
- 2.General tolerance:± 0.05mm.
- 3. The pad layout is for reference purposes only.



Attention

- Any and all HUA XUAN YANG ELECTRONICS products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your HUA XUAN YANG ELECTRONICS representative nearest you before using any HUA XUAN YANG ELECTRONICS products described or contained herein in such applications.
- HUA XUAN YANG ELECTRONICS assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein.
- Specifications of any and all HUA XUAN YANG ELECTRONICS products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- HUA XUAN YANG ELECTRONICS CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all HUA XUAN YANG ELECTRONICS products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of HUA XUAN YANG ELECTRONICS CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production.

 HUA XUAN YANG ELECTRONICS believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc.

 When designing equipment, refer to the "Delivery Specification" for the HUA XUAN YANG ELECTRONICS product that you intend to use.