

# DATA SHEET

## CEMENT RESISTORS

High Power, Vertical Mount

SQM Series

NSM Series

$\pm 1\%$ ,  $\pm 5\%$

2W to 10W

RoHS compliant & Halogen Free





## APPLICATIONS

- Power applications
- Home appliance
- Industry

## FEATURES

- High power rating
- Excellent pulse load capability
- Axial terminal
- Flameproof ceramic case
- RoHS compliant and halogen free

## ORDERING INFORMATION

Part number of the vertical mount cement resistor are identified by the series, power rating, tolerance, packing, temperature coefficient and resistance value.

## PART NUMBER

**SQM**    **200**    **J**    **B**    **-**    **100R**  
 (1)        (2)        (3)        (4)        (5)        (6)

### (1) SERIES

SQM = General Purpose

NSM = Non-Inductive

### (2) POWER RATING

200 = 2W	500 = 5W	10A = 10W
300 = 3W	700 = 7W	10S = 10W

### (3) TOLERANCE

F =  $\pm 1\%$

J =  $\pm 5\%$

### (4) PACKAGING

B = Bulk for wirewound or metal oxide or fiberglass element

W = Bulk for wirewound element

M = Bulk for metal oxide element

F = Bulk for fiberglass element

### (5) TEMPERATURE COEFFICIENT OF RESISTANCE

F =  $\pm 100\text{ppm}/^\circ\text{C}$

- = Based on spec

### (6) RESISTANCE VALUE


E24 & E96 Series

Example:

1R = 1 $\Omega$ , 10R = 10 $\Omega$ , 100R = 100 $\Omega$



**DIMENSIONS**

Unit: mm




Normal	Non-Inductive	H	W	S	P
SQM200	NSM200	$20 \pm 1.5$	$11.0 \pm 1.0$	$7.0 \pm 1.0$	$5^{+2-1}$
SQM300	NSM300	$25 \pm 1.5$	$12.0 \pm 1.0$	$8.0 \pm 1.0$	$5^{+2-1}$
SQM500	NSM500	$25 \pm 1.5$	$13.0 \pm 1.0$	$9.0 \pm 1.0$	$5^{+2-1}$
SQM700	NSM700	$39 \pm 1.5$	$13.0 \pm 1.0$	$9.0 \pm 1.0$	$5^{+2-1}$
SQM10A	NSM10A	$51 \pm 1.5$	$13.0 \pm 1.0$	$9.0 \pm 1.0$	$5^{+2-1}$
SQM10S	NSM10S	$35 \pm 1.5$	$16.0 \pm 1.0$	$12.0 \pm 1.0$	$7^{+2-1}$

**DERATING CURVE**



**TEMPERATURE RISE**



**ELECTRICAL CHARACTERISTICS**

CHARACTERISTICS	SQM200	SQM300	SQM500	SQM700	SQM10A	SQM10S
Power Rating at 40 °C		3W	5W	7W	10W	10W
Power Rating at 70 °C	2W					
Maximum Working Voltage	250V	350V	350V	500V	500V	500V
Maximum Overload Voltage	500V	700V	700V	1000V	1000V	1000V
Voltage Proof on Insulation	500V	700V	700V	1000V	1000V	1000V
Resistance Range (Ceramic based wirewound)	0.1Ω~36Ω	0.1Ω~68Ω	0.1Ω~130Ω	0.1Ω~330Ω	0.1Ω~510Ω	0.1Ω~270Ω
Resistance Range (Metal Oxide Film)	39Ω~1MΩ	75Ω~1MΩ	150Ω~1MΩ	360Ω~1MΩ	560Ω~1MΩ	300Ω~1MΩ
Resistance Range (Fiberglass based wirewound)	0.1Ω~1KΩ	0.1Ω~4.7KΩ	0.1Ω~4.7KΩ	0.1Ω~4.7KΩ	0.1Ω~5.6KΩ	0.1Ω~4.7KΩ
Operating Temp. Range	- 55°C to +155°C					
Temperature Coefficient	Wirewound: ±100ppm/°C , ±300ppm/°C, Film:±300ppm/°C					

CHARACTERISTICS	NSM200	NSM300	NSM500	NSM700	NSM10A	NSM10S
Power Rating at 40 °C		3W	5W	7W	10W	10W
Power Rating at 70 °C	2W					
Maximum Working Voltage	√(P X R)					
Voltage Proof on Insulation	500V	700V	700V	1000V	1000V	1000V
Resistance Range (Ceramic based wirewound)	0.1Ω~10Ω	0.1Ω~30Ω	0.15Ω~65Ω	0.27Ω~100Ω	0.27Ω~100Ω	0.27Ω~100Ω
Operating Temp. Range	- 55°C to +155°C					
Temperature Coefficient	±300ppm/°C					

Note: For resistance value out of above range is by request.

**TEST AND REQUIREMENTS**

TEST	TEST METHOD	PROCEDURE	APPRAISE
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV for 5 sec.(Not more than maximum overload voltage)	±2%+0.05Ω
Voltage Proof on Insulation	IEC 60115-1 4.7	In V-Block for 60 sec. test voltage as above table	No Breakdown
Temperature Coefficient	IEC 60115-1 4.8	Between -55°C to +155°C	By Type
Insulation Resistance	IEC 60115-1 4.6	In V-Block for 60 sec.	>1,000MΩ
Solderability	IEC 60115-1 4.17	245±5°C for 3±0.5 Sec.	95% Min. coverage
Solvent Resistance of Marking	IEC 60115-1 4.30	IPA for 5±0.5 Min. with ultrasonic	No deterioration of coatings and markings
Robustness of Terminations	IEC 60115-1 4.16	Direct load for 10 Sec. in the direction of the terminal leads	≥2.5Kg(24.5N)
Periodic-pulse Overload	IEC 60115-1 4.39	4 times RCWV(or Umax., whichever less) 10,000 cycles (1 Sec. on, 25 Sec.off)	±2.0%+0.05Ω
Damp Heat Steady State	IEC 60115-1 4.24	40±2°C,90-95% RH for 56 days, loaded with 0.1 times RCWV(or Umax., whichever less)	±5.0%+0.05Ω
Endurance at 70°C	IEC 60115-1 4.25	70±2°C at RCWV(or Umax., whichever less) for 1,000 Hr.(1.5 Hr.on,0.5 Hr. off)	±5.0%+0.05Ω
Temperature Cycling	IEC 60115-1 4.19	-55°C → Room Temp. → +155°C → Room Temp.(5 cycles)	±2.0%+0.05Ω
Resistance to Soldering Heat	IEC 60115-1 4.18	260±3°C for 10±1 Sec., immersed to a point 3±0.5mm from the body	±1.0%+0.05Ω

Note:.

**RCWV (Rated Continuous Working Voltage ):**

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V=\sqrt{(P \times R)}$$

or max. working voltage whichever is less

Where

V=Continuous rated DC or  
AC (rms) working voltage (V)


P=Rated power (W)

R=Resistance value (Ω)

**BULK PACKING**

<b>Miniature</b>	<b>Non-Inductive</b>	<b>Piece/Per Inner Box</b>
SQM200	NSM200	1,600
SQM300	NSM300	1,000
SQM500	NSM500	1,000
SQM700	NSM700	700
SQM10A	NSM10A	500
SQM10S	NSM10S	500

**MARKING**



**Example:**

- 
- YAGEO = Brand
  - 1439 = Date code
  - 7W = Power rating
  - N = Non-inductive
  - 100R = Resistance
  - J = Tolerance
  - F = Fiberglass
-

**REVISION HISTORY**

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 2	Sep.7, 2023	-	- Updated legal disclaimer and footer versions numbers
Version 1	Aug.24, 2023	-	- Update copper wire dimensions and add temperature rise curves
Version 0	Aug.2, 2021	-	- First issue of this specification

*“ Yageo reserves all the rights for revising the content of this datasheet without further notification, as long as the products itse If are unchanged. Any product change will be announced by PCN.”*

## LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non-infringement and merchantability.

YAGEO products are designed for general purpose applications under normal operation and usage conditions. Please contact YAGEO for the applications listed below which require especially high reliability for the prevention of defects which might directly cause damage to the third party's life, body or property: Aerospace equipment (artificial satellite, rocket, etc.), Atomic energy-related equipment, Aviation equipment, Disaster prevention equipment, crime prevention equipment, Electric heating apparatus, burning equipment, Highly public information network equipment, data-processing equipment, Medical devices, Military equipment, Power generation control equipment, Safety equipment, Traffic signal equipment, Transportation equipment and Undersea equipment, or for any other application or use in which the failure of YAGEO products could result in personal injury or death, or serious property damage. Particularly **YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.**

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.