## **SIEMENS**

Data sheet 3RW5248-6AC05



SIRIUS soft starter 200-600 V 570 A, 24 V AC/DC Screw terminals Analog output

product brand name	SIRIUS
product category	Hybrid switching devices
product designation	Soft starter
product type designation	3RW52
manufacturer's article number	
<ul> <li>of standard HMI module usable</li> </ul>	3RW5980-0HS00
<ul> <li>of high feature HMI module usable</li> </ul>	3RW5980-0HF00
<ul> <li>of communication module PROFINET standard usable</li> </ul>	3RW5980-0CS00
<ul> <li>of communication module PROFIBUS usable</li> </ul>	3RW5980-0CP00
<ul> <li>of communication module Modbus TCP usable</li> </ul>	3RW5980-0CT00
<ul> <li>of communication module Modbus RTU usable</li> </ul>	3RW5980-0CR00
<ul> <li>of communication module Ethernet/IP</li> </ul>	3RW5980-0CE00
<ul> <li>of circuit breaker usable at 400 V</li> </ul>	3VA2580-6HN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
<ul> <li>of circuit breaker usable at 500 V</li> </ul>	3VA2580-6HN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
<ul> <li>of circuit breaker usable at 400 V at inside-delta circuit</li> </ul>	3VA2510-6HN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
<ul> <li>of circuit breaker usable at 500 V at inside-delta circuit</li> </ul>	3VA2510-6HN32-0AA0; Type of coordination 1, Iq = 65 kA, CLASS 10
<ul> <li>of the gG fuse usable up to 690 V</li> </ul>	2x3NA3365-6; Type of coordination 1, Iq = 65 kA
<ul> <li>of the gG fuse usable at inside-delta circuit up to 500 V</li> </ul>	2x3NA3365-6; Type of coordination 1, Iq = 65 kA
<ul> <li>of full range R fuse link for semiconductor protection usable up to 690 V</li> </ul>	3NE1437-2; Type of coordination 2, Iq = 65 kA
<ul> <li>of back-up R fuse link for semiconductor protection usable up to 690 V</li> </ul>	3NE3340-8; Type of coordination 2, Iq = 65 kA

General technical data	
starting voltage [%]	30 100 %
stopping voltage [%]	50 %; non-adjustable
start-up ramp time of soft starter	0 20 s
current limiting value [%] adjustable	130 700 %
certificate of suitability	
<ul> <li>CE marking</li> </ul>	Yes
UL approval	Yes
CSA approval	Yes
product component	
HMI-High Feature	No
<ul> <li>is supported HMI-Standard</li> </ul>	Yes
is supported HMI-High Feature	Yes
product feature integrated bypass contact system	Yes
number of controlled phases	3

trin class	CLASS 10A (default) / 10E / 20E; 200, to IEC 60047 4.3
trip class	CLASS 10A (default) / 10E / 20E; acc. to IEC 60947-4-2
buffering time in the event of power failure	100 mg
for main current circuit     for control circuit	100 ms
• for control circuit	100 ms
insulation voltage rated value	600 V
degree of pollution	3, acc. to IEC 60947-4-2
impulse voltage rated value	6 kV
blocking voltage of the thyristor maximum	1 600 V
service factor	1
surge voltage resistance rated value	6 kV
maximum permissible voltage for safe isolation	000.17
between main and auxiliary circuit	600 V
shock resistance	15 g / 11 ms, from 12 g / 11 ms with potential contact lifting
vibration resistance	15 mm to 6 Hz; 2g to 500 Hz
utilization category according to IEC 60947-4-2	AC 53a
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	02/15/2018
product function	
• ramp-up (soft starting)	Yes
• ramp-down (soft stop)	Yes
Soft Torque	Yes
adjustable current limitation	Yes
• pump ramp down	Yes
intrinsic device protection	Yes
motor overload protection	Yes; Electronic motor overload protection
evaluation of thermistor motor protection	No
• inside-delta circuit	Yes
• auto-RESET	Yes
• manual RESET	Yes
remote reset	Yes; By turning off the control supply voltage
communication function	Yes
operating measured value display	Yes; Only in conjunction with special accessories
• error logbook	Yes; Only in conjunction with special accessories
via software parameterizable	No
via software configurable	Yes
PROFlenergy	Yes; in connection with the PROFINET Standard communication module
• firmware update	Yes
<ul> <li>removable terminal for control circuit</li> </ul>	Yes
torque control	No
analog output	Yes; 4 20 mA (default) / 0 10 V (parameterizable with High Feature HMI)
Power Electronics	
operational current	
at 40 °C rated value	570 A
at 50 °C rated value	504 A
at 60 °C rated value	460 A
operational current at inside-delta circuit	
at 40 °C rated value	987 A
at 50 °C rated value	873 A
at 60 °C rated value	796 A
operating voltage	
rated value	200 600 V
at inside-delta circuit rated value	200 600 V
relative negative tolerance of the operating voltage	45.07
	-15 %
relative positive tolerance of the operating voltage	10 %
relative positive tolerance of the operating voltage relative negative tolerance of the operating voltage at inside-delta circuit	
relative negative tolerance of the operating voltage at	10 %

-t 000 V -t 40 °Ct-dl	400 130
• at 230 V at 40 °C rated value	160 kW
• at 230 V at inside-delta circuit at 40 °C rated value	315 kW
• at 400 V at 40 °C rated value	315 kW
<ul> <li>at 400 V at inside-delta circuit at 40 °C rated value</li> </ul>	560 kW
<ul> <li>at 500 V at 40 °C rated value</li> </ul>	355 kW
at 500 V at inside-delta circuit at 40 °C rated value	630 kW
Operating frequency 1 rated value	50 Hz
Operating frequency 2 rated value	60 Hz
relative negative tolerance of the operating frequency	-10 %
relative positive tolerance of the operating frequency	10 %
adjustable motor current	
<ul> <li>at rotary coding switch on switch position 1</li> </ul>	240 A
<ul> <li>at rotary coding switch on switch position 2</li> </ul>	262 A
<ul> <li>at rotary coding switch on switch position 3</li> </ul>	284 A
<ul> <li>at rotary coding switch on switch position 4</li> </ul>	306 A
<ul> <li>at rotary coding switch on switch position 5</li> </ul>	328 A
<ul> <li>at rotary coding switch on switch position 6</li> </ul>	350 A
<ul> <li>at rotary coding switch on switch position 7</li> </ul>	372 A
<ul> <li>at rotary coding switch on switch position 8</li> </ul>	394 A
<ul> <li>at rotary coding switch on switch position 9</li> </ul>	416 A
<ul> <li>at rotary coding switch on switch position 10</li> </ul>	438 A
<ul> <li>at rotary coding switch on switch position 11</li> </ul>	460 A
<ul> <li>at rotary coding switch on switch position 12</li> </ul>	482 A
<ul> <li>at rotary coding switch on switch position 13</li> </ul>	504 A
<ul> <li>at rotary coding switch on switch position 14</li> </ul>	526 A
<ul> <li>at rotary coding switch on switch position 15</li> </ul>	548 A
<ul> <li>at rotary coding switch on switch position 16</li> </ul>	570 A
• minimum	240 A
adjustable motor current	
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 1</li> </ul>	416 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 2</li> </ul>	454 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 3</li> </ul>	492 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 4</li> </ul>	530 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 5</li> </ul>	568 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 6</li> </ul>	606 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 7</li> </ul>	644 A
for inside-delta circuit at rotary coding switch on switch position 8      for inside delta circuit at retery coding switch on	682 A
for inside-delta circuit at rotary coding switch on switch position 9      for inside delta circuit at rotary coding switch on	721 A
for inside-delta circuit at rotary coding switch on switch position 10     for inside delta circuit at rotary coding switch on	759 A
for inside-delta circuit at rotary coding switch on switch position 11     for inside delta circuit at rotary coding switch on	797 A
for inside-delta circuit at rotary coding switch on switch position 12     for inside-delta circuit at rotary coding switch on	835 A 873 A
for inside-delta circuit at rotary coding switch on switch position 13     for inside delta circuit at rotary coding switch on	
for inside-delta circuit at rotary coding switch on switch position 14     for inside delta circuit at rotary coding switch on	911 A
<ul> <li>for inside-delta circuit at rotary coding switch on switch position 15</li> <li>for inside-delta circuit at rotary coding switch on</li> </ul>	949 A 987 A
switch position 16  • at inside-delta circuit minimum	416 A
minimum load [%]	15 %; Relative to smallest settable le
	10 70, Melative to sitialical settable le
power loss [W] for rated value of the current at AC	

<ul> <li>at 40 °C after startup</li> </ul>	183 W
<ul> <li>at 50 °C after startup</li> </ul>	163 W
at 60 °C after startup	153 W
power loss [W] at AC at current limitation 350 %	
<ul> <li>at 40 °C during startup</li> </ul>	10 241 W
at 50 °C during startup	8 500 W
at 60 °C during startup	7 663 W
<u> </u>	7 000 11
Control circuit/ Control	40/00
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
<ul> <li>at 50 Hz rated value</li> </ul>	24 V
at 60 Hz rated value	24 V
relative negative tolerance of the control supply voltage at AC at 50 Hz	-20 %
relative positive tolerance of the control supply voltage at AC at 50 Hz	20 %
relative negative tolerance of the control supply voltage at AC at 60 Hz	-20 %
relative positive tolerance of the control supply voltage at AC at 60 Hz	20 %
control supply voltage frequency	50 60 Hz
relative negative tolerance of the control supply voltage frequency	-10 %
relative positive tolerance of the control supply voltage frequency	10 %
control supply voltage	
at DC rated value	24 V
relative negative tolerance of the control supply voltage at DC	-20 %
relative positive tolerance of the control supply voltage at DC	20 %
control supply current in standby mode rated value	160 mA
holding current in bypass operation rated value	470 mA
locked-rotor current at close of bypass contact maximum	7.6 A
inrush current peak at application of control supply voltage maximum	3.3 A
duration of inrush current peak at application of control supply voltage	12.1 ms
design of the overvoltage protection	Varistor
design of short-circuit protection for control circuit	4 A gG fuse (Icu=1 kA), 6 A quick-acting fuse (Icu=1 kA), C1 miniature circuit breaker (Icu= 600 A), C6 miniature circuit breaker (Icu= 300 A); Is not part of scope of supply
Inputs/ Outputs	
number of digital inputs	1
number of digital outputs	3
not parameterizable	2
digital output version	2 normally-open contacts (NO) / 1 changeover contact (CO)
number of analog outputs	1
switching capacity current of the relay outputs	
• at AC-15 at 250 V rated value	3 A
at DC-13 at 250 V rated value     at DC-13 at 24 V rated value	1A
	173
Installation/ mounting/ dimensions	with vertical recording out 1/000t-t-bla 1/1 // //
mounting position	with vertical mounting surface +/-90° rotatable, with vertical mounting surface +/- 22.5° tiltable to the front and back
fastening method	screw fixing
height	393 mm
width	210 mm
depth	203 mm
required spacing with side-by-side mounting	
<ul><li>forwards</li></ul>	10 mm
<ul><li>backwards</li></ul>	0 mm
• upwards	100 mm
•	

<ul><li>downwards</li></ul>	75 mm
at the side	5 mm
weight without packaging	10.6 kg
Connections/ Terminals	
type of electrical connection	
<ul> <li>for main current circuit</li> </ul>	busbar connection
for control circuit	screw-type terminals
width of connection bar maximum	45 mm
type of connectable conductor cross-sections	
<ul> <li>for DIN cable lug for main contacts stranded</li> </ul>	2x (50 240 mm²)
for DIN cable lug for main contacts finely stranded	2x (70 240 mm²)
type of connectable conductor cross-sections	
for control circuit solid	1x (0.5 4.0 mm²), 2x (0.5 2.5 mm²)
<ul> <li>for control circuit finely stranded with core end processing</li> </ul>	1x (0.5 2.5 mm²), 2x (0.5 1.5 mm²)
at AWG cables for control circuit solid	1x (20 12), 2x (20 14)
wire length	
between soft starter and motor maximum	800 m
at the digital inputs at AC maximum	100 m
at the digital inputs at DC maximum	1 000 m
tightening torque	
for main contacts with screw-type terminals	14 24 N·m
for auxiliary and control contacts with screw-type terminals	0.8 1.2 N·m
tightening torque [lbf·in]	404 040    61
for main contacts with screw-type terminals	124 210 lbf·in
for auxiliary and control contacts with screw-type terminals	7 10.3 lbf·in
Ambient conditions	
installation altitude at height above sea level maximum	5 000 m; Derating as of 1000 m, see catalog
ambient temperature	
<ul><li>during operation</li></ul>	-25 +60 °C; Please observe derating at temperatures of 40 °C or above
during storage and transport	-40 +80 °C
environmental category	
<ul> <li>during operation according to IEC 60721</li> </ul>	3K6 (no ice formation, only occasional condensation), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
<ul> <li>during storage according to IEC 60721</li> </ul>	1K6 (only occasional condensation), 1C2 (no salt mist), 1S2 (sand must not get inside the devices), 1M4
<ul> <li>during transport according to IEC 60721</li> </ul>	2K2, 2C1, 2S1, 2M2 (max. fall height 0.3 m)
EMC emitted interference	acc. to IEC 60947-4-2: Class A
Communication/ Protocol	
communication module is supported	
PROFINET standard	Yes
• EtherNet/IP	Yes
Modbus RTU	Yes
Modbus TCP	Yes
• PROFIBUS	Yes
UL/CSA ratings	
manufacturer's article number	
of the fuse	
<ul> <li>usable for Standard Faults up to 575/600 V according to UL</li> </ul>	Type: Class J / L, max. 1600 A; Iq = 30 kA
usable for High Faults up to 575/600 V  according to UL	Type: Class J / L, max. 1200 A; Iq = 100 kA
<ul> <li>usable for Standard Faults at inside-delta circuit up to 575/600 V according to UL</li> </ul>	Type: Class J / L, max. 1600 A; Iq = 30 kA
<ul> <li>usable for High Faults at inside-delta circuit up to 575/600 V according to UL</li> </ul>	Type: Class J / L, max. 1200 A; Iq = 100 kA
operating power [hp] for 3-phase motors	
<ul> <li>at 200/208 V at 50 °C rated value</li> </ul>	150 hp
● at 220/230 V at 50 °C rated value	200 hp

<ul> <li>at 460/480 V at 50 °C rated value</li> </ul>	400 hp
<ul> <li>at 575/600 V at 50 °C rated value</li> </ul>	500 hp
<ul> <li>at 200/208 V at inside-delta circuit at 50 °C rated value</li> </ul>	300 hp
<ul> <li>at 220/230 V at inside-delta circuit at 50 °C rated value</li> </ul>	350 hp
<ul> <li>at 460/480 V at inside-delta circuit at 50 °C rated value</li> </ul>	750 hp
<ul> <li>at 575/600 V at inside-delta circuit at 50 °C rated value</li> </ul>	950 hp
contact rating of auxiliary contacts according to UL	R300-B300
Safety related data	
protection class IP on the front according to IEC 60529	IP00; IP20 with cover
touch protection on the front according to IEC 60529	finger-safe, for vertical contact from the front with cover
electromagnetic compatibility	in accordance with IEC 60947-4-2
Certificates/ approvals	

**General Product Approval** 

**EMC** 





Confirmation







**Declaration of Conformity** 

**Test Certificates** 

Marine / Shipping





Type Test Certificates/Test Report







Marine / Shipping

other





Confirmation

## **Further information**

Information- and Downloadcenter (Catalogs, Brochures,...)

https://www.siemens.com/ic10

Industry Mall (Online ordering system)

https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RW5248-6AC05

Cax online generator

http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RW5248-6AC05

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

https://support.industry.siemens.com/cs/ww/en/ps/3RW5248-6AC05

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax\_de.aspx?mlfb=3RW5248-6AC05&lang=en

Characteristic: Tripping characteristics, I2t, Let-through current

https://support.industry.siemens.com/cs/ww/en/ps/3RW5248-6AC05/char

Characteristic: Installation altitude

Simulation Tool for Soft Starters (STS)

https://support.industry.siemens.com/cs/ww/en/view/101494917

last modified:

4/10/2022

