SIEMENS

Data sheet

3SU1200-2PT10-1AA0



Potentiometer, compact, 22 mm, round, plastic, black, 47k ohm, with holder, screw terminal

product brand name	SIRIUS ACT
product designation	Potentiometers
design of the product	Compact unit
product type designation	3SU1
product line	Plastic, black, 22 mm
manufacturer's article number of the supplied holder	<u>3SU1550-0AA10-0AA0</u>
Enclosure	
number of command points	1
Actuator	
design of the actuating element	Rotary knob
principle of operation of the actuating element	Infinitely variable adjustment, angle of rotation 280°
color of the actuating element	black
material of the actuating element	plastic
shape of the actuating element	round
outer diameter of the actuating element	30 mm
Maximum deflection angle [°]	280°
Front ring	
product component front ring	No
Holder	
material of the holder	Plastic
General technical data	
General technical data insulation voltage rated value	500 V
	500 V 3
insulation voltage rated value	
insulation voltage rated value degree of pollution	3
insulation voltage rated value degree of pollution protection class IP	3 IP66, IP67, IP69(IP69K)
insulation voltage rated value degree of pollution protection class IP • of the terminal	3 IP66, IP67, IP69(IP69K) IP20, clamping screw tightened
insulation voltage rated value degree of pollution protection class IP • of the terminal degree of protection NEMA rating	3 IP66, IP67, IP69(IP69K) IP20, clamping screw tightened
insulation voltage rated value degree of pollution protection class IP • of the terminal degree of protection NEMA rating shock resistance	3 IP66, IP67, IP69(IP69K) IP20, clamping screw tightened 1, 2, 3, 3R, 4, 4X, 12, 13
insulation voltage rated value degree of pollution protection class IP • of the terminal degree of protection NEMA rating shock resistance • according to IEC 60068-2-27 • for railway applications according to EN 61373 vibration resistance	3 IP66, IP67, IP69(IP69K) IP20, clamping screw tightened 1, 2, 3, 3R, 4, 4X, 12, 13 sinusoidal half-wave 15g / 11 ms
insulation voltage rated value degree of pollution protection class IP • of the terminal degree of protection NEMA rating shock resistance • according to IEC 60068-2-27 • for railway applications according to EN 61373	3 IP66, IP67, IP69(IP69K) IP20, clamping screw tightened 1, 2, 3, 3R, 4, 4X, 12, 13 sinusoidal half-wave 15g / 11 ms
insulation voltage rated value degree of pollution protection class IP • of the terminal degree of protection NEMA rating shock resistance • according to IEC 60068-2-27 • for railway applications according to EN 61373 vibration resistance • according to IEC 60068-2-6 • for railway applications according to EN 61373	3 IP66, IP67, IP69(IP69K) IP20, clamping screw tightened 1, 2, 3, 3R, 4, 4X, 12, 13 sinusoidal half-wave 15g / 11 ms Category 1, Class B 10 500 Hz: 5g Category 1, Class B
insulation voltage rated value degree of pollution protection class IP • of the terminal degree of protection NEMA rating shock resistance • according to IEC 60068-2-27 • for railway applications according to EN 61373 vibration resistance • according to IEC 60068-2-6 • for railway applications according to EN 61373 mechanical service life (switching cycles) typical	3 IP66, IP67, IP69(IP69K) IP20, clamping screw tightened 1, 2, 3, 3R, 4, 4X, 12, 13 sinusoidal half-wave 15g / 11 ms Category 1, Class B 10 500 Hz: 5g Category 1, Class B 25 000
insulation voltage rated value degree of pollution protection class IP • of the terminal degree of protection NEMA rating shock resistance • according to IEC 60068-2-27 • for railway applications according to EN 61373 vibration resistance • according to IEC 60068-2-6 • for railway applications according to EN 61373 mechanical service life (switching cycles) typical reference code according to IEC 81346-2	3 IP66, IP67, IP69(IP69K) IP20, clamping screw tightened 1, 2, 3, 3R, 4, 4X, 12, 13 sinusoidal half-wave 15g / 11 ms Category 1, Class B 10 500 Hz: 5g Category 1, Class B 25 000 S
insulation voltage rated value degree of pollution protection class IP • of the terminal degree of protection NEMA rating shock resistance • according to IEC 60068-2-27 • for railway applications according to EN 61373 vibration resistance • according to IEC 60068-2-6 • for railway applications according to EN 61373 mechanical service life (switching cycles) typical reference code according to IEC 81346-2 Substance Prohibitance (Date)	3 IP66, IP67, IP69(IP69K) IP20, clamping screw tightened 1, 2, 3, 3R, 4, 4X, 12, 13 sinusoidal half-wave 15g / 11 ms Category 1, Class B 10 500 Hz: 5g Category 1, Class B 25 000
insulation voltage rated value degree of pollution protection class IP • of the terminal degree of protection NEMA rating shock resistance • according to IEC 60068-2-27 • for railway applications according to EN 61373 vibration resistance • according to IEC 60068-2-6 • for railway applications according to EN 61373 mechanical service life (switching cycles) typical reference code according to IEC 81346-2	3 IP66, IP67, IP69(IP69K) IP20, clamping screw tightened 1, 2, 3, 3R, 4, 4X, 12, 13 sinusoidal half-wave 15g / 11 ms Category 1, Class B 10 500 Hz: 5g Category 1, Class B 25 000 S
insulation voltage rated value degree of pollution protection class IP • of the terminal degree of protection NEMA rating shock resistance • according to IEC 60068-2-27 • for railway applications according to EN 61373 vibration resistance • according to IEC 60068-2-6 • for railway applications according to EN 61373 mechanical service life (switching cycles) typical reference code according to IEC 81346-2 Substance Prohibitance (Date) Connections/ Terminals type of electrical connection	3 IP66, IP67, IP69(IP69K) IP20, clamping screw tightened 1, 2, 3, 3R, 4, 4X, 12, 13 sinusoidal half-wave 15g / 11 ms Category 1, Class B 10 500 Hz: 5g Category 1, Class B 25 000 S
insulation voltage rated value degree of pollution protection class IP • of the terminal degree of protection NEMA rating shock resistance • according to IEC 60068-2-27 • for railway applications according to EN 61373 vibration resistance • according to IEC 60068-2-6 • for railway applications according to EN 61373 mechanical service life (switching cycles) typical reference code according to IEC 81346-2 Substance Prohibitance (Date) Connections/ Terminals	3 IP66, IP67, IP69(IP69K) IP20, clamping screw tightened 1, 2, 3, 3R, 4, 4X, 12, 13 sinusoidal half-wave 15g / 11 ms Category 1, Class B 10 500 Hz: 5g Category 1, Class B 25 000 S 01/01/2016

 solid without core end processing 	2x (1.0 1.5 mm²)
 finely stranded with core end processing 	2x (0.5 1.5 mm²)
 finely stranded without core end processing 	2x (1,0 1,5 mm²)
at AWG cables	2x (18 14)
tightening torque of the screws in the bracket	1 1.2 N·m
tightening torque with screw-type terminals	0.8 1 N·m
Ambient conditions	
ambient temperature	
 during operation 	-25 +70 °C
during storage	-40 +80 °C
environmental category during operation according to IEC 60721	3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 95%, no condensation in operation permitted for all devices behind front panel)
Installation/ mounting/ dimensions	
height	40 mm
width	30 mm
shape of the installation opening	round
mounting diameter	22.3 mm
positive tolerance of installation diameter	0.4 mm
mounting height	19.4 mm
installation width	30 mm
installation depth	46 mm
Certificates/ approvals	
General Product Approval	Declaration of Conformity
Confirmation	rnr UK cc
(JM) (UI)	











CA

Test Certificates	other	
Type Test Certific- ates/Test Report	Confirmation	Environmental Con- firmations

Further information

Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10

Industry Mall (Online ordering system)


https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1200-2PT10-1AA0


Cax online generator


http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1200-2PT10-1AA0


Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3SU1200-2PT10-1AA0

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1200-2PT10-1AA0&lang=en









last modified:

1/27/2022 🖸