
Ŧ	۵	п –	m	0







LAYOUT SHOWN AS

Keying Shown as example

## CHARACTERISTICS

BASIC SERIES:

SHELL SIZE : 13

PLATING : F = Nickel

Н

SHELL TYPE : Square Flange Receptacle

CONTACT TYPE : Standard Crimp Contact

ယ

-Standard : Based on MIL-DTL-38999 Series III

	-Shell Material	: Aluminium	$\vdash$
	-Shell Plating	: Nickel	F
	-Insulator	: Thermoplastic	
	-Contacts	: Copper Alloy	
	-Seals & Grommet	: Silicon Elastomer	$\vdash$
N	-Contact Plating	: Gold over copper Alloy 0.8µm minimum	
	-Durability	: 500 Mating cycles	
	-Delivered with Souria	u contacts and Accessories	
	-Temperature Range	: -65°C to +200°C	
	-Salt Spray	: 48 hours	
	-Mass	: 20.37 g ± 10%	

8D 0

G

13

F

98

В

F

А

Dim	Nominal		
Р	3.25±0.2		
PP	4.93±0.2		
R1	23.01		
R2	20.62		
S	28.6±0.3		
V	20.83+0/-1.25		
W	2.1/2.5		
Z	31.5 Max		
VV THREAD	M18x1-6g		

**ORIENTATION : A** 

CONTACT LAYOUT : 13-98

CONTACT TYPE : SOCKET(500 Matings)

Е

SOURIAU shall not be liable for a due to a use of the Products the Specifications issued by either (professional recommend



σ		Þ			
			4		
AS EXAMPLE			3		
r any non-conformin s which does not co er of the Parties or I ndation, technical n	mply with by a third party otice.)	+			
Intry Jurisc FR	liction & Control Lis Not Listed		2		
3F98BA					
		MOD N°			
	CUSTOMER DRA				
um Receptacle 8D series					
ar :	NPRDS / PROJ <b>859</b>	ECT	1		
.COM This document is the property of SOURIAU it must not be reproduced or communicated without permission					
U DRG N°					
F98BA-C		A 1/2	J		
0	I				

		۵	г т	m	D		0	
		Contact Layout						Panel Cutou
4		$X \begin{pmatrix} \bullet & \bullet \\ $				SQUAR	RE FLANGE RECEPTACLE REAR MOUNTING R1	(TYPE 0)
	Cont positio A B CC D E E F G G H J J K	n ID (mm) (mm)   + 000 (0.00) + 195 (4.95)   + 1.25 (3.18) + 150 (3.81)   + 1.25 (3.18) + 0.00 (0.76)   + 1.04 (4.17) - 105 (2.67)   + 1.90 (0.00) - 135 (3.43)   - 1.164 (4.17) - 105 (2.67)   + 1.90 (0.00) - 135 (3.43)   - 1.164 (4.17) - 105 (2.67)   + 1.91 (3.90) + 0.00 (0.76)   + 1.92 (3.18) + 1.90 (3.81)   + 0.05 (1.65) - 0.15 (0.38)						
ω	Shell Arrangement N size no. cr	Number of contacts Size rating Contact location Supersedes   10 20 I All MS20051-98						Dim ØA ØAA R1 ØT
	_							
							due to a use the Specification	not be liable for any of the Products whi s issued by either of ional recommendati
N								Country FR
							I	PN: 8D013F
	-				A S ISS Designed		irst Release Latest modificati Date:	
						TITLE	Date.	Aluminium
<u> </u>					SCALE		$\exists \bigoplus$	General linear Tolerances: ±
					SOL	JRIAU	WWW	SOURIAU.C
					FORMA A3			SOURIAU 8D013F9
	Н	G	F	E	D		С	

