

## **Data sheet for SINAMICS G120X**

Article No.: 6SL3220-1YH36-0AF0

Client order no. : Order no. : Offer no. :

Rated data				
Input				
Number of phases	3 AC			
Line voltage	500 690 V +	10 % -20 %		
Line frequency	47 63 Hz			
Rated voltage	690V IEC	600V NEC		
Rated current (LO)	40.00 A	40.00 A		
Rated current (HO)	36.60 A	36.60 A		
Output				
Number of phases	3 AC			
Rated voltage	690V IEC	600V NEC 1)		
Rated power (LO)	37.00 kW	40.00 hp		
Rated power (HO)	30.00 kW	30.00 hp		
Rated current (LO)	42.00 A	42.00 A		
Rated current (HO)	35.00 A	35.00 A		
Rated current (IN)	43.00 A			
Max. output current	57.00 A			
Pulse frequency	2 kHz			
Output frequency for vector control	0 200 Hz			
Output frequency for V/f control	0 550 Hz			
Overload capability				
Low Overload (LO)				

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

 $150\%\,x$  base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.90 0.95	
Offset factor $\cos\phi$	0.99	
Efficiency η	0.98	
Sound pressure level (1m)	70 dB	
Power loss 3)	0.980 kW	
Filter class (integrated)	RFI suppression filter for Category C2	
EMC category (with accessories)	Category C2	
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)	
Communication		

Communication PROFINET, EtherNet/IP

Error: No CAD-Data available for this configuration.

Figure similar

Item no. : Consignment no. : Project :

Inputs / outputs				
Standard digital inputs				
Number	6			
Switching level: $0 \rightarrow 1$	11 V			
Switching level: $1 \rightarrow 0$	5 V			
Max. inrush current	15 mA			
Fail-safe digital inputs				
Number	1			
Digital outputs				
Number as relay changeover contact	2			
Output (resistive load)	DC 30 V, 5.0 A			
Number as transistor	0			
Analog / digital inputs				
Number	2 (Differential input)			
Resolution	10 bit			
Switching threshold as digital input				
0 → 1	4 V			
1 → 0	1.6 V			
Analog outputs				
Number	1 (Non-isolated output)			
PTC/ KTV interface				

## PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy  $\pm 5\,^{\circ}\text{C}$ 

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No




## **Data sheet for SINAMICS G120X**

Article No.: 6SL3220-1YH36-0AF0

Ambient conditions		
Standard board coating type	Class 3C2, according to IEC 60721-3-3: 2002	
Cooling	Air cooling using an integrated fan	
Cooling air requirement	0.055 m³/s (1.942 ft³/s)	
Installation altitude	1,000 m (3,280.84 ft)	
Ambient temperature		
Operation	-20 45 °C (-4 113 °F)	
Transport	-40 70 °C (-40 158 °F)	
Storage	-25 55 °C (-13 131 °F)	
Relative humidity		
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible	
Co	onnections	
Signal cable		
Conductor cross-section	0.15 1.50 mm <sup>2</sup> (AWG 24 AWG 16)	
Line side		
Version	screw-type terminal	
Conductor cross-section	10.00 35.00 mm <sup>2</sup> (AWG 8 AWG 2)	
Motor end		
Version	Screw-type terminals	
Conductor cross-section	10.00 35.00 mm <sup>2</sup> (AWG 8 AWG 2)	
DC link (for braking resistor)		
PE connection	Screw-type terminals	
Max. motor cable length		
Shielded	100 m (328.08 ft)	

Mechanical data				
Degree of protection		IP20 / UL open type		
Frame size		FSD		
Net weight		19.5 kg (42.99 lb)		
Dimensions				
	Width	200 mm (7.87 in)		
	Height	472 mm (18.58 in)		
	Depth	248 mm (9.76 in)		
Standards				
Compliance with standards		UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH		
CE marking		EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC		

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	41.1 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

\*converted values

<sup>1)</sup> The output current and HP ratings are valid for the voltage range 550V-600V

<sup>&</sup>lt;sup>3)</sup>Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.