

MESSRS.

SPECIFICATION FOR APPROVAL**承 认 书**

Product	动态式扬声器 DYNAMIC SPEAKER
Part No.	HDK-241508EA-11C (RoHS)
Customer	
Customer Part No.	QR68

Approved By	Checked By	Made By
王台平 APR-16-2018	曹丽萍 APR-16-2018	LILY APR-16-2018

常州华龙电子有限公司**DRAGONSTATE ELECTRONIC CORPORATION**

中国江苏省常州市新区电子园新四路 36 号

Tel: +86-519-85110078. 86-519-85106698, Fax: +86-519-85101081

EDITION:1.1

1.Specification

HDK-241508EA-11C(RoHS)

ITEM		SPECIFICATIONS	
01	Type 屬性	Dynamic speaker 动态式扬声器	
02	Dimension 尺寸	External diameter 24*15mm 外径 24*15mm	
03	Rated Input Power 额定输入功率	1.5W	
04	Max. Input Power 最大输入功率	1.7W for 1 minute 1.0W 在内 1 分钟	
05	Impedance 阻抗	8 ohm \pm 15% at 2500Hz 1.0V	
06	Resonance Frequency (Fo) 谐振频率	1050Hz \pm 20% at Fo 1V	
07	Sensitivity (S.P.L.)灵敏度	96dB (1.0W / 0.1m) \pm 3 dB	at AVE K, 1.0K, 1.2K, 1.5KHz
08	Frequency Range 频率范围	Fo – 20KHz	
09	Total Harmonics Distortion 谐波失真	Max 8 % at 1 KHz, 1.0W.	
10	Voice Coil 音圈	Diameter 8.5 mm	
11	Magnet 磁铁	Rare earth permanent (Nd-Fe-B) magnet Φ 8.0*1.0mm 钕铁硼材质外径 Φ 8.0*1.0 mm	
12	Weight 重量	2.8g \pm 0.2g	
13	Appearance 外观	Should not exist any obstacle to be harmful to normal operation; damages, cracks, rusts and distortions, etc. 沒有會影響功能的:損壞,裂痕,鏽跡,變型等	
14	Operation Test 工作测试	Must be normal at program source – 1.5W 测试的工作功率為 1.5W	
15	Buzz, Rattle, etc.异音测试	Should not be audible at 3.46V sine Wave between Fo to 20KHz 加電壓 3.46V 频率 Fo 到 20KHz 的正旋波時不會聽到任何杂音	
16	Polarity 极性	When positive voltage is applied to the terminal marked (+), diaphragm should move to the front. 正電壓接至(+)極時,音膜振動是朝向喇叭前方	
17	Terminal Strength 端子强度	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection. 能夠承受 1kg 負載達 30 秒不會造成任何損壞	
18	Temperature 温度	Operating temperature: -20°C to +70°C 工作溫度 : -20°C to +70°C Storage temperature: -30°C to +80°C 儲存溫度 : -30°C to +80°C	

2-1. Test Condition 测试条件

Standard 标准测试

Temperature 温度 : 15 ~ 35°C

Relative humidity 相对湿度 : 25% ~ 85%,

Atmospheric pressure 大气压力 : 860mbar to 1060mbar.

Basic 基本测试

Temperature 温度: 20±3°C

Relative humidity 相对湿度: 60% ~ 70%,

Atmospheric pressure 大气压力: 860mbar to 1060mbar

2-2. Standard Test Fixture 标准测试设备


1. Input Power 输入功率: 0.8W (2.53V)

2. Zero Level : -dB


3. Mode 模式: SPEAKER 喇叭

4. potentiometer Range : 50dB


5. Sweep Time 扫描时间: 0.5sec




2.3 Frequency Response Curve 频响曲线



3.Dimension 尺寸



4. Reliability Test 可靠性测试

Items.		Specifications
01	High temp. Test 高温测试	Keep 96 hours at +70°C±3°C and leave 3 hours in normal temperature and then check +70°C±3°C持续 96 小时, 在常温下存放 3 小时后测试
02	Low temp. Test 低温测试	Keep 96 hours at -20°C±3°C and leave 3 hours in normal temperature and then check -20°C±3°C持续 96 小时, 在常温下存放 3 小时后测试
03	Humidity test 湿度测试	Keep 96 hours at +40°C±3°C relative humidity 95% and leave 3 hours in normal temperature and then checked. +40°C±3°C相对湿度 95%持续 96 小时, 在常温下存放 3 小时后测试
04	Temp./Humidity cycle 温湿度循环测试	The part shall be subjected 5 cycles. One cycle shall be 12 hours and consist of; 在以下条件 5 次循环, 每次 12 小时, 在常温下存放 3 小时后测试 
05	Thermal cycle test. 热循环测试	Low temperature: -30°C±3°C, temperature: +70°C±3°C, cycle: 1 hour/cycle each, and then keep 5 cycles in a room. 低温-30°C±3°C高温+70°C±3°C一小时一个周期, 同一个试验箱 5 个周期
06	Vibration 振动测试	10~200~10Hz sin-wave sweep 15min. 5G(constant) X,Y, Z 3 direction. 2 hours each, total 6 hours. 10~200~10Hz 正弦波振动 15 分钟, X,Y, Z 三个面, 2 小时一次, 共 6 小时
07	Fix drop test 固定跌落测试	Fix on jig. Then drop from 152cm height to the concrete floor X, y, z 6 direction. 5 times each, total 30 times. 固定夹具中, 152cm 跌落水泥地, X,Y, Z 六个面, 每面 5 次, 共 30 次
08	Free drop test 自由跌落测试	Free drop from 100cm height to the concrete floor X, y, z 6 direction. 1 times each, total 6 times. 100cm 跌落水泥地, X,Y, Z 六个面, 每面 1 次, 共 6 次
09	Rated Power test 额定功率测试	Rated Power white noise is applied for 96 hours 额定功率白噪声持续 96 hours
10	Max Power test 最大功率测试	Max power 1 min on – 2 min off 10 cycles. 最大功率 1 分钟通, 停 2 分钟, 10 次循环
11	Terminal strength test 拉力测试	Capable of withstand 1kg load for 30 seconds without resulting in any damage or rejection 1kg 拉力 30 秒, 没有导致产品损坏
<p>Criterion: After these test , the change of S.P.L shall be within ±3 dB . 所有试验后, 音压都在 ±3 dB 之内</p>		

Soldering Condition 焊接条件

Recommend using constant branding iron in 15 ~ 30W, and in temperature range 350±10°C. Soldering time not over 3 seconds.

