SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-1YH24-0UP0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Rated data			
Input			
Number of phases	3 AC		
Line voltage	500 690 V +10 % -20 %		
Line frequency	47 63 Hz		
Rated voltage	690V IEC	600V NEC	
Rated current (LO)	11.00 A	11.00 A	
Rated current (HO)	9.90 A	9.90 A	
Output			
Number of phases	3 AC		
Rated voltage	690V IEC	600V NEC ¹⁾	
Rated power (LO)	7.50 kW	10.00 hp	
Rated power (HO)	5.50 kW	7.50 hp	
Rated current (LO)	11.00 A	11.00 A	
Rated current (HO)	9.00 A	9.00 A	
Rated current (IN)	12.00 A		
Max. output current	15.00 A		
Pulse frequency	2 kHz		
Output frequency for vector control	0 200 Hz		
Output frequency for V/f control	0 550 Hz		

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.90 0.95	
Offset factor $\cos \phi$	0.99	
Efficiency η	0.97	
Sound pressure level (1m)	70 dB	
Power loss ³⁾	0.306 kW	
Filter class (integrated)	Unfiltered	
EMC category (with accessories)	without	
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)	
Communication		
Communication	PROFIBUS DP	

ltem no. : Consignment no. : Project :

Inputs / outputs			
Standard digital inputs			
Number	6		
Switching level: $0 \rightarrow 1$	11 V		
Switching level: $1 \rightarrow 0$	5 V		
Max. inrush current	15 mA		
Fail-safe digital inputs			
Number	1		
Digital outputs			
Number as relay changeover contact	2		
Output (resistive load)	DC 30 V, 5.0 A		
Number as transistor	0		
Analog / digital inputs			
Number	2 (Differential input)		
Resolution	10 bit		
Switching threshold as digital input			
$0 \rightarrow 1$	4 V		
$1 \rightarrow 0$	1.6 V		
Analog outputs			
Number	1 (Non-isolated output)		
PTC/ KTY interface			
1 motor temperature sensor input, sen Thermo-Click, accuracy ±5 °C	nsors that can be connected PTC, KTY and		

Closed-loop control techniques		
V/f linear / square-law / parameterizable	Yes	
V/f with flux current control (FCC)	Yes	
V/f ECO linear / square-law	Yes	
Sensorless vector control	Yes	
Vector control, with sensor	No	
Encoderless torque control	No	
Torque control, with encoder	No	

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-1YH24-0UP0

Ambient conditions			
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002		
Cooling	Air cooling using an integrated fan		
Cooling air requirement	0.055 m³/s (1.942 ft³/s)		
Installation altitude	1,000 m (3,280.84 ft)		
Ambient temperature			
Operation	-20 45 °C (-4 113 °F)		
Transport	-40 70 °C (-40 158 °F)		
Storage	-25 55 °C (-13 131 °F)		
Relative humidity			
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible		
Connections			
Signal cable			
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)		
Line side			
Version	screw-type terminal		
Conductor cross-section	10.00 35.00 mm² (AWG 8 AWG 2)		
Motor end			
Version	Screw-type terminals		
Conductor cross-section	10.00 35.00 mm² (AWG 8 AWG 2)		
DC link (for braking resistor)			
PE connection	Screw-type terminals		
Max. motor cable length			
Max. motor cable length Shielded	200 m (656.17 ft)		

	Me	echanical data		
Degree	e of protection	IP20 / UL open	type	
Frame size FSD				
Net weight		16.6 kg (36.60 lb)		
Dimen	isions			
Widt	h	200 mm (7.87	in)	
Height		472 mm (18.5	8 in)	
Depth		248 mm (9.76	248 mm (9.76 in)	
		Standards		
Compliance with standards UL, cUL, CE, C-Tick (RCM), EAC, K SEMI F47, REACH				
CE mar	E marking EMC Directive 2004/108/EC, Low Voltage Directive 2006/95/EC			
	Converter l	osses to IEC61800-	9-2*	
Efficiency class IE2				
Comparison with the reference converter (90% / 100%)		42.8 %		
I 100%	274.0 W (2.1 %)	287.0 W (2.2 %)	306.0 W (2.3 %)	
	ſ	Ť	T	
	215.0 W (1.6 %)	220.0 W (1.7 %)	227.0 W (1.7 %)	
50%			•	
	193.0 W (1.5 %)	195.0 W (1.5 %)		

215.0 W (1.6 %) 220.0 W (1.7 %) 227.0 W (1.7 %) 193.0 W (1.5 %) 195.0 W (1.5 %) 50% 90% **f**

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾The output current and HP ratings are valid for the voltage range 550V-600V

³⁾Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.