SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-1YH38-0UB0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Rated data			
Input			
Number of phases	3 AC		
Line voltage	500 690 V +10 % -20 %		
Line frequency	47 63 Hz		
Rated voltage	690V IEC	600V NEC	
Rated current (LO)	50.00 A	50.00 A	
Rated current (HO)	44.40 A	44.40 A	
Output			
Number of phases	3 AC		
Rated voltage	690V IEC	600V NEC ¹⁾	
Rated power (LO)	45.00 kW	50.00 hp	
Rated power (HO)	37.00 kW	40.00 hp	
Rated current (LO)	52.00 A	52.00 A	
Rated current (HO)	42.00 A	42.00 A	
Rated current (IN)	54.00 A		
Max. output current	71.00 A		
Pulse frequency	2 kHz		
Output frequency for vector control	0 200 Hz		
Output frequency for V/f control	0 550 Hz		
Overlead capability			

Overload capability

Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications			
Power factor λ	0.90 0.95		
Offset factor $\cos \phi$	0.99		
Efficiency η	0.98		
Sound pressure level (1m)	70 dB		
Power loss 3)	1.120 kW		
Filter class (integrated)	Unfiltered		
EMC category (with accessories)	without		
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)		
Communication			

Communication

USS, Modbus RTU, BACnet MS/TP

ltem no. : Consignment no. : Project :

Inputs / outputs			
Standard digital inputs			
Number	6		
Switching level: $0 \rightarrow 1$	11 V		
Switching level: $1 \rightarrow 0$	5 V		
Max. inrush current	15 mA		
Fail-safe digital inputs			
Number	1		
Digital outputs			
Number as relay changeover contact	2		
Output (resistive load)	DC 30 V, 5.0 A		
Number as transistor	0		
Analog / digital inputs			
Number	2 (Differential input)		
Resolution	10 bit		
Switching threshold as digital input			
0 → 1	4 V		
$1 \rightarrow 0$	1.6 V		
Analog outputs			
Number	1 (Non-isolated output)		
PTC/ KTY interface			
1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5~^\circ\text{C}$			
Closed-loop co	ntrol techniques		

Closed-loop control techniques			
V/f linear / square-law / parameterizable	Yes		
V/f with flux current control (FCC)	Yes		
V/f ECO linear / square-law	Yes		
Sensorless vector control	Yes		
Vector control, with sensor	No		
Encoderless torque control	No		
Torque control, with encoder	No		

SIEMENS

Data sheet for SINAMICS G120X

Article No. :

6SL3230-1YH38-0UB0

Ambient conditions			
Standard board coating type	Class 3C3, according to IEC 60721-3-3: 2002		
Cooling	Air cooling using an integrated fan		
Cooling air requirement	0.083 m³/s (2.931 ft³/s)		
Installation altitude	1,000 m (3,280.84 ft)		
Ambient temperature			
Operation	-20 45 °C (-4 113 °F)		
Transport	-40 70 °C (-40 158 °F)		
Storage	-25 55 °C (-13 131 °F)		
Relative humidity			
Max. operation	95 % At 40 °C (104 °F), condensation and icing not permissible		
Connections			
Signal cable			
Conductor cross-section	0.15 1.50 mm² (AWG 24 AWG 16)		
Line side			
Version	screw-type terminal		
Conductor cross-section	25.00 70.00 mm² (AWG 6 AWG 3/0)		
Motor end			
Version	Screw-type terminals		
Conductor cross-section	25.00 70.00 mm² (AWG 6 AWG 3/0)		
DC link (for braking resistor)			
PE connection	Screw-type terminals		
Max. motor cable length			
Shielded	300 m (984.25 ft)		
Unshielded	450 m (1,476.38 ft)		

Ме	chanical data		
Degree of protection	IP20 / UL open	type	
Frame size	FSE	FSE	
Net weight	26.7 kg (58.86	26.7 kg (58.86 lb)	
Dimensions			
Width	275 mm (10.8	275 mm (10.83 in)	
Height	551 mm (21.6	551 mm (21.69 in)	
Depth	248 mm (9.76	248 mm (9.76 in)	
Standards			
Compliance with standards	UL, cUL, CE, C- SEMI F47, REA	Tick (RCM), EAC, KCC, CH	
CE marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC		
Converter losses to IEC61800-9-2*			
Efficiency class	IE2		
Comparison with the reference converter (90% / 100%)	37.8 %		
↓ 856.0 W (1.4 %)	950.0 W (1.5 %)	1,110.0 W (1.8 %)	
100% •	•	•	
533.0 W (0.9 %)	567.0 W (0.9 %)	619.0 W (1.0 %)	
50% •	··••	•	

25% 416.0 W (0.7 %) 431.0 W (0.7 %) 50% 90% **f**

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾The output current and HP ratings are valid for the voltage range 550V-600V

³⁾ Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.