


Data sheet for SINAMICS G120X

Article No.: 6SL3230-2YH42-0UF0

Client order no. : Order no. : Offer no. : Remarks :



Low Overload (LO)

110% base load current IL for 60 s in a 300 s cycle time

High Overload (HO)

150% x base load current IH for 60 s within a 600 s cycle time

General tech. specifications		
Power factor λ	0.90 0.95	
Offset factor $\cos\phi$	0.99	
Efficiency η	0.98	
Sound pressure level (1m)	72 dB	
Power loss ³⁾	1.410 kW	
Filter class (integrated)	Unfiltered	
EMC category (with accessories)	without	
Safety function "Safe Torque Off"	without SIRIUS device (e.g. via S7- 1500F)	

Com	mur	nica	tion
COIII	mu	IICu	CIOII

Communication PROFINET, EtherNet/IP



Item no. : Consignment no. : Project :

Inputs / outputs	
Standard digital inputs	
Number	6
Switching level: $0 \rightarrow 1$	11 V
Switching level: $1 \rightarrow 0$	5 V
Max. inrush current	15 mA
Fail-safe digital inputs	
Number	1
Digital outputs	
Number as relay changeover contact	2
Output (resistive load)	DC 30 V, 5.0 A
Number as transistor	0
Analog / digital inputs	
Number	2 (Differential input)
Resolution	10 bit
Switching threshold as digital input	
0 → 1	4 V
1 → 0	1.6 V
Analog outputs	
Number	1 (Non-isolated output)

PTC/ KTY interface

1 motor temperature sensor input, sensors that can be connected PTC, KTY and Thermo-Click, accuracy $\pm 5\,^{\circ}\text{C}$

Closed-loop control techniques	
V/f linear / square-law / parameterizable	Yes
V/f with flux current control (FCC)	Yes
V/f ECO linear / square-law	Yes
Sensorless vector control	Yes
Vector control, with sensor	No
Encoderless torque control	No
Torque control, with encoder	No




Data sheet for SINAMICS G120X

Article No.: 6SL3230-2YH42-0UF0

Class 3C3, according to IEC 6072 2002 Cooling Air cooling using an integrated far Cooling air requirement 0.153 m³/s (5.403 ft³/s) Installation altitude 1,000 m (3,280.84 ft) Ambient temperature Operation -20 45 °C (-4 113 °F) Transport -40 70 °C (-40 158 °F) Storage -25 55 °C (-13 131 °F) Relative humidity Max. operation 95 % At 40 °C (104 °F), condensational icing not permissible Connections Signal cable 0.15 1.50 mm²	n
Cooling air requirement 0.153 m³/s (5.403 ft³/s) Installation altitude 1,000 m (3,280.84 ft) Ambient temperature Operation -20 45 °C (-4 113 °F) Transport -40 70 °C (-40 158 °F) Storage -25 55 °C (-13 131 °F) Relative humidity Max. operation 95 % At 40 °C (104 °F), condensation and icing not permissible Connections Signal cable	
Installation altitude 1,000 m (3,280.84 ft) Ambient temperature Operation -20 45 °C (-4 113 °F) Transport -40 70 °C (-40 158 °F) Storage -25 55 °C (-13 131 °F) Relative humidity Max. operation 95 % At 40 °C (104 °F), condensational icing not permissible Connections Signal cable	tion
Ambient temperature Operation -20 45 °C (-4 113 °F) Transport -40 70 °C (-40 158 °F) Storage -25 55 °C (-13 131 °F) Relative humidity Max. operation 95 % At 40 °C (104 °F), condensational icing not permissible Connections Signal cable	tion
Operation -20 45 °C (-4 113 °F) Transport -40 70 °C (-40 158 °F) Storage -25 55 °C (-13 131 °F) Relative humidity Max. operation 95 % At 40 °C (104 °F), condensational icing not permissible Connections Signal cable	tion
Transport -40 70 °C (-40 158 °F) Storage -25 55 °C (-13 131 °F) Relative humidity Max. operation 95 % At 40 °C (104 °F), condensation and icing not permissible Connections Signal cable	tion
Storage -25 55 °C (-13 131 °F) Relative humidity Max. operation 95 % At 40 °C (104 °F), condensation and icing not permissible Connections Signal cable	tion
Relative humidity Max. operation 95 % At 40 °C (104 °F), condensation and icing not permissible Connections Signal cable	tion
Max. operation 95 % At 40 °C (104 °F), condensation and icing not permissible Connections Signal cable	tion
Connections Signal cable 0.15 1.50 mm ²	tion
Signal cable	
0.15 1.50 mm ²	
0.15 1.50 mm ²	
Conductor cross-section (AWG 24 AWG 16)	
Line side	
Version M10 screw	
Conductor cross-section 35.00 2 x 120.00 mm ² (AWG 1 AWG 2 x 4/0)	
Motor end	
Version M10 screw	
Conductor cross-section $ 35.00 \dots 2 \times 120.00 \text{ mm}^2 $ (AWG 1 AWG 2 x 4/0)	
DC link (for braking resistor)	
PE connection M10 screw	
Max. motor cable length	
Shielded 300 m (984.25 ft)	

Mechanical data		
Degree of protection	IP20 / UL open type	
Frame size	FSF	
Net weight	61 kg (134.48 lb)	
Dimensions		
Width	305 mm (12.01 in)	
Height	709 mm (27.91 in)	
Depth	369 mm (14.53 in)	
Standards		
Compliance with standards	UL, cUL, CE, C-Tick (RCM), EAC, KCC, SEMI F47, REACH	
CE marking	EMC Directive 2004/108/EC, Low- Voltage Directive 2006/95/EC	

Converter losses to IEC61800-9-2*	
Efficiency class	IE2
Comparison with the reference converter (90% / 100%)	31.5 %



The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*converted values

¹⁾ The output current and HP ratings are valid for the voltage range 550V-600V

³⁾ Typical value. More information can be found in the element group "Converter losses to IEC 61800-9-2" in this datasheet.



Data sheet for SINAMICS G120X

Article No.: 6SL3230-2YH42-0UF0

	Operator pane	l: Basic Operator Panel (BOP-2)
	Screen	
Display design	LCD, monochrome	Ambient temperature
	Mechanical data	Operation
Degree of protection	IP55 / UL type 12	Storage
Net weight	0.140 kg (0.31 lb)	Transport Relative humidity at 25
Dimensions		Max. operation
Width	70.00 mm (2.76 in)	iviax. operation
Height	106.85 mm (4.21 in)	
Depth	19.60 mm (0.77 in)	Certificate of suitability

Ambient conditions		
Ambient temperature		
Operation	0 50 °C (32 122 °F)	
Storage	-40 70 °C (-40 158 °F)	
Transport	-40 70 °C (-40 158 °F)	
Relative humidity at 25°C during		
Max. operation	95 %	
Approvals		
Certificate of suitability	CE, cULus, EAC, KCC, RCM	