


NUMBER	825435
USED FOR	E 75-9233
WAS	-

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F1	NOTE 1 0.76μm PLATING UPDATE (PdNi+AuFLASH)	13JUL2023	BGC	PS

POS.	L±0.5	PART NO
-	-	-
2	5.08	825435 -2
3	7.62	-3 ³ / ₃
4	10.16	-4
5	12.70	-5 ³ / ₃
6	15.24	-6 ³ / ₃
7	17.78	-7
8	20.32	-8 ³ / ₃
9	22.86	-9 ³ / ₃
10	25.40	-0 ³ / ₃
11	27.94	1-
12	30.48	1-
13	33.02	1-
14	35.56	1- -4 ³ / ₃
15	38.10	1-
16	40.64	1-
17	43.18	1-
18	45.72	1-
19	48.26	1-
20	50.80	-2- -0 ³ / ₃
21	53.34	-2- -1 ² / ₂
22	55.88	-2- -2 ³ / ₃
23	58.42	2-
24	60.96	2-
25	63.50	2-
26	66.04	2-
27	68.58	2- 7 ³ / ₃
28	71.12	2-
29	73.66	2- 9 ³ / ₃
30	76.20	3- 0 ³ / ₃
31	78.74	3- -1
32	81.28	3- -2
33	83.82	3- -3
34	86.36	3- -4
35	88.90	3- -5
36	91.44	3- -6
37	93.98	3- -7 ³ / ₃
38	96.52	3- -8
39	99.06	3- -9
40	101.60	4- -0
41	104.14	4- -1
42	106.68	4- -2
43	109.22	4- -3
44	111.76	4- -4
45	114.30	4- -5
46	116.84	4- -6
47	119.38	4- -7
48	121.92	4- -8
49	124.46	4- -9
50	127.00	5- 825435 -0



- ① MATING SIDE: Min 0.76μm (PdNi + Au FLASH) IN ZONE "F" OVER Min 1.27μm Ni
(Alternative plating - Min 0.76μm Au OVER Min 1.27μm Ni)
SOLDER SIDE: 3-5μm TIN OVER Min 1.27μm NICKEL
- ② OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- ③ OBSOLETE

CONTACT PIN	CuZn	①
PEN HOUSING	PBT GV	GREEN
DESCRIPTION	MATERIAL	SURFACE COLOR

TE Connectivity. All Rights Reserved.

DIMENSIONS: mm	DWN	A.HO	11APR1984	MATERIAL	-	FINISH	-
	CHK	M.SCHAARSCHMIDT	11APR1984	TE Connectivity			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2mm	APVD	-	PRODUCT SPEC				
0 PLC ± -	PRODUCT SPEC	108-18012		AMP MODU II PIN HEADER, SINGLE ROW			
1 PLC ± -	APPLICATION SPEC	-		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
2 PLC ± -	WEIGHT	-		A4	00779	①-825435	-
3 PLC ± -	CUSTOMER DRAWING						
4 PLC ± -	SCALE		4:1		SHEET		1 OF 1
ANGLES ± -	REV		F1				